

N-Channel 100-V (D-S) MOSFET

PRODUCT SUMMARY					
V _{DS} (V)	$R_{DS(on)}(\Omega)$	I _D (A) ^a	Q _g (Typ.)		
100	0.0185 at V _{GS} = 10 V	45	38 nC		


FEATURES


- TrenchFET® Power MOSFET
- 100 % R_q and UIS Tested





- Primary Side Switch
- Isolated DC/DC Converter





N-Channel MOSFET

Parameter		Symbol	Limit	Unit	
Drain-Source Voltage		V _{DS}	100	v	
Gate-Source Voltage		V _{GS}	± 20		
	T _C = 25 °C		45 ^a		
Continuous Drain Current /T = 150 °C	T _C = 100 °C		30		
Continuous Drain Current (T _J = 150 °C)	T _A = 25 °C	I _D	9.2 ^b		
	T _A = 100 °C		6.8 ^b		
Pulsed Drain Current		I _{DM}	140	Α	
Continuous Source-Drain Diode Current	T _C = 25 °C	1	45 ^a	7	
Continuous Source-Diam blode Current	T _A = 25 °C	I _S	2 ^b		
Single Pulse Avalanche Current	L = 0.1 mH	I _{AS}	35		
Avalanche Energy	L=0.1 IIII	E _{AS}	101	mJ	
Maximum Power Dissipation	T _C = 25 °C		136.4	w	
	T _C = 100 °C	В	68.2		
	T _A = 25 °C	P _D	3 ^b		
	T _A = 100 °C		1.5 ^b		
Operating Junction and Storage Temperature Ra	T _J , T _{stg}	- 55 to 175	°C		

THERMAL RESISTANCE RATINGS					
Parameter		Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ^b	Steady State	R _{thJA}	40	50	°C/W
Maximum Junction-to-Case	Sieauy State	R _{thJC}	0.85	1.1	C/VV

Notes:

- a. Package limited.
- b. Surface mounted on 1" x 1" FR4 board.

服务热线:400-655-8788

1




Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit
Static						
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$	100			V
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$	I _D = 250 μA		110		mV/°C
V _{GS(th)} Temperature Coefficient	$\Delta V_{GS(th)}/T_J$			- 12.5		
Gate-Source Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}, I_D = 250 \mu A$	2.5		5	V
Gate-Source Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 20 \text{ V}$			± 100	nA
Zana Oata Walkana Busin Oan	I _{DSS}	V _{DS} = 100 V, V _{GS} = 0 V			1	
Zero Gate Voltage Drain Current		V _{DS} = 100 V, V _{GS} = 0 V, T _J = 125 °C			50	μΑ
On-State Drain Current ^a	I _{D(on)}	$V_{DS} \ge 5 \text{ V}, V_{GS} = 10 \text{ V}$	30			Α
Drain-Source On-State Resistance ^a	R _{DS(on)}	V _{GS} = 10 V, I _D = 15 A		0.0185		Ω
Forward Transconductance ^a	9 _{fs}	V _{DS} = 15 V, I _D = 15 A		33		S
Dynamic ^b						
Input Capacitance	C _{iss}			2400		pF
Output Capacitance	C _{oss}	$V_{DS} = 50 \text{ V}, V_{GS} = 0 \text{ V}, f = 1 \text{ MHz}$		230		
Reverse Transfer Capacitance	C _{rss}			80		
Total Gate Charge	Q_g			38	70	nC
Gate-Source Charge	Q _{gs}	$V_{DS} = 50 \text{ V}, V_{GS} = 10 \text{ V}, I_{D} = 50 \text{ A}$		14		
Gate-Drain Charge	Q _{gd}			12		
Gate Resistance	R_g	f = 1 MHz		1.6	2.5	Ω
Turn-On Delay Time				12	20	
Rise Time t ₁		$V_{DD} = 50 \text{ V}, R_L = 1 \Omega$		10	20	ne
Turn-Off Delay Time	t _{d(off)}	$I_D \cong 50 \text{ A}, V_{GEN} = 10 \text{ V}, R_g = 1 \Omega$		18	35	- ns
Fall Time	t _f			8	15	
Drain-Source Body Diode Characteris	stics					
Continuous Source-Drain Diode	I _S	T _C = 25 °C			35	A
Pulse Diode Forward Current ^a	I _{SM}	-			100	
Body Diode Voltage	V_{SD}	I _S = 15 A		0.85	1.5	V
Body Diode Reverse Recovery Time t _{rr}				80	120	ns
Body Diode Reverse Recovery Charge	Q _{rr}	$I_F = 50 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, T_J = 25 ^{\circ}\text{C}$		160	240	nC
Reverse Recovery Fall Time	t _a			57		ns
Reverse Recovery Rise Time	t _b			23		

Notes:


- a. Pulse test; pulse width \leq 300 μ s, duty cycle \leq 2 %.
- b. Guaranteed by design, not subject to production testing.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.



















On-Resistance vs. Junction Temperature




Threshold Voltage




Single Pulse Power, Junction-to-Case











Current Derating**, Junction-to-Ambient





Safe Operating Area, Junction-to-Case



^{**} The power dissipation P_D is based on $T_{J(max.)}$ = 175 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.








Power Derating**, Junction-to-Ambient


Power Derating**, Junction-to-Case

^{**} The power dissipation P_D is based on $T_{J(max)}$ = 175 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.





Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

服务热线:400-655-8788

7



Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be oHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.