

# APTF1616SEEZGQBDC

1.6 x 1.6 mm Full-Color Surface Mount LED



## **DESCRIPTIONS**

- The Hyper Red source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- The Green source color devices are made with InGaN on Sapphire Light Emitting Diode
- The Blue source color devices are made with InGaN Light Emitting Diode
- · Electrostatic discharge and power surge could damage the LEDs
- . It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

#### **FEATURES**

- 1.6 mm x 1.6 mm SMD LED, 0.7 mm thickness
- · Low power consumption
- · Can produce any color in visible spectrum, including white light
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- · RoHS compliant

# **APPLICATIONS**


- Backlight
- · Status indicator
- Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

## **ATTENTION**

Observe precautions for handling electrostatic discharge sensitive devices




## **PACKAGE DIMENSIONS**



### **RECOMMENDED SOLDERING PATTERN**

(units: mm; tolerance: ± 0.1)



- 1. All dimensions are in millimeters (inches).
  2. Tolerance is +0.2(0.000") units
- 3. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
- 4. The device has a single mounting surface. The device must be mounted according to the specifications.

## **SELECTION GUIDE**

Part Number	Emitting Color (Material)	Lens Type	Iv (mcd) @ 20mA [2]		Viewing Angle [1]	
			Min.	Тур.	201/2	
APTF1616SEEZGQBDC	■ Hyper Red (AlGaInP)	Water Clear	55	110		
	■ Green (InGaN)		300	400	130°	
	■ Blue (InGaN)		40	70		

Notes.

1. 61/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.

2. Luminous intensity / luminous flux: +/-15%.

3. Luminous intensity value is traceable to CIE127-2007 standards.





# ELECTRICAL / OPTICAL CHARACTERISTICS at T<sub>A</sub>=25°C

Parameter	Symbol	Emitting Color	Value		Unit
Parameter	Symbol	Emitting Color	Тур.	Max.	
Wavelength at Peak Emission I <sub>F</sub> = 20mA	$\lambda_{peak}$	Hyper Red Green Blue	630 515 460	-	nm
Dominant Wavelength I <sub>F</sub> = 20mA	λ <sub>dom</sub> <sup>[1]</sup>	Hyper Red Green Blue	621 525 465	-	nm
Spectral Bandwidth at 50% $\Phi$ REL MAX $\Delta\lambda$ Hyper Red Green Blue		20 35 25	-	nm	
Capacitance	С	Hyper Red Green Blue	25 45 100	-	pF
Forward Voltage I <sub>F</sub> = 20mA	V <sub>F</sub> <sup>[2]</sup>	Hyper Red Green Blue	2.0 3.3 3.3	2.5 4.1 4.0	V
Reverse Current (V <sub>R</sub> = 5V)	I <sub>R</sub>	Hyper Red Green Blue	-	10 50 50	μА
Temperature Coefficient of $\lambda_{peak}$ $I_F$ = 20mA, -10°C $\leq$ T $\leq$ 85°C	$TC_{\lambdapeak}$	Hyper Red Green Blue	0.13 0.05 0.04	-	nm/°C
Temperature Coefficient of $\lambda_{dom}$ $I_F$ = 20mA, -10°C $\leq$ T $\leq$ 85°C	$TC_{\lambdadom}$	Hyper Red Green Blue	0.06 0.03 0.03	-	nm/°C
Temperature Coefficient of $V_F$		Hyper Red Green Blue	-2.0 -3.0 -3.0	-	mV/°C

# ABSOLUTE MAXIMUM RATINGS at T<sub>A</sub>=25°C

Powers et au	Symbol	Value			11-24
Parameter		Hyper Red	Green	Blue	Unit
Power Dissipation	$P_D$	75	102.5	120	mW
Reverse Voltage	V <sub>R</sub>	5	5	5	V
Junction Temperature	Tj	115	115	115	°C
Operating Temperature	T <sub>op</sub>	-40 to +85			°C
Storage Temperature	orage Temperature T <sub>stg</sub> -40 to +85				°C
DC Forward Current	I <sub>F</sub>	30	25	30	mA
Peak Forward Current	I <sub>FM</sub> <sup>[1]</sup>	195	150	150	mA
Electrostatic Discharge Threshold (HBM)	-	3000	450	250	V
Thermal Resistance (Junction / Ambient)	R <sub>th JA</sub> [2]	780	790	790	°C/W
Thermal Resistance (Junction / Solder point)	R <sub>th JS</sub> [2]	640	650	650	°C/W

Notes:
1. 1/10 Duty Cycle, 0.1ms Pulse Width.
2.  $R_{h,M}$ ,  $R_{h$ 




The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd: ±1nm.)
 Forward voltage: ±0.1V.
 Wavelength value is traceable to CIE127-2007 standards.
 Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.




## **TECHNICAL DATA**

# **RELATIVE INTENSITY vs. WAVELENGTH**





#### **SPATIAL DISTRIBUTION**




## **HYPER RED**


Forward Current vs. Forward Voltage T<sub>a</sub> = 25 °C Forward current (mA) 40 30 20 10 1.9 2.3 2.5 1.5 1.7 2.1 Forward voltage (V)










# **GREEN**













## **BLUE**













#### **REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS**

#### 300 above 255°C (°C) 260°C max. 30s max. 10s max. 250 3°C/s max. 6°C/s max. 200 150 Temperature pre-heating 100 150~200°C above 217°C 60~150s 60~120s 50 0 50 100 150 200 250 300 (sec) Time -

# **REEL DIMENSION** (units: mm)




TAPE SPECIFICATIONS (units:mm)



- 1. Don't cause stress to the LEDs while it is exposed to high temperature.
  2. The maximum number of reflow soldering passes is 2 times.
  3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.

#### **PACKING & LABEL SPECIFICATIONS**



#### **PRECAUTIONARY NOTES**

- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.

  When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If
- customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright
- All design applications should refer to Kingbright application notes available at https://www.Kingbright.

