

M2-JODY-W3 module



M.2 card with JODY-W3 Wi-Fi 6 and Bluetooth 5.3 module

Module featuring IEEE 802.11ax and Bluetooth Low Energy 5.3

- M.2 Type 2230 Key E form factor
- Concurrent dual Wi-Fi 2.4 and 5 GHz, 2x2 MIMO (5 GHz), dual MAC
- Dual-mode Bluetooth 5.3 BR/EDR and LE, including long range
- Simultaneous access point (AP), station (STA), Wi-Fi Direct (P2P)
- Optimized for parallel operation of Wi-Fi and Bluetooth
- Compatible with NXP i.MX evaluation and development boards



22.0 × 30.0 × 4.2 mm



Product description

The M2-JODY-W3 card module combines the maximum performance of the JODY-W3 Wi-Fi 6 and Bluetooth 5.3 connectivity module with the flexibility and ease of use of an M.2 card. The card supports all features of the JODY-W377 module and delivers the highest data rates in Wi-Fi using the most advanced Wi-Fi 802.11ax technology. It can operate in concurrent dual Wi-Fi (2.4 GHz and 5 GHz), dual-MAC, and in 2x2 MIMO on 5 GHz. It supports Bluetooth LE/Bluetooth LE 5.3 features such as a data rate of 2 Mbit/s (PHY), extended advertising, and long range.

The M2-JODY-W3 card module is based on the NXP Q9098 chip. It requires a host processor running a Linux or Android operating system. The M.2 Key E form factor gives access to all supported JODY-W3 interfaces, such as PCIe, SDIO, high speed UART, PCM, and I2S.

Key features

- M.2 type 2230 Key E form factor
- 2x2 MIMO 802.11ax 5 GHz, beamforming
- Wi-Fi concurrent dual band 2.4 and 5 GHz
- Wi-Fi data rates (PHY): Up to 1.2 Gbit/s (5 GHz)
- Wi-Fi 20, 40, and 80 MHz channels
- DFS master zero-wait
- Multi-role operation: AP, STA, P2P
- WPA3: all common methods of security and encryption
- Bluetooth LE physical layer (PHY) data rates up to 2 Mbit/s
- Bluetooth long range
- Advertising extension, high duty cycle directed advertising
- Bluetooth LE isochronous channels
- All standard pairing, authentication, link key, and encryption operation
- Chipset qualified according to AEC-Q100 (card module is standard grade)

M2-JODY-W377

Grade	
Automotive	
Professional	
Standard	•
Radio	
Bluetooth qualification	v5.3
Bluetooth profiles	HCI
Bluetooth BR/EDR	•
Bluetooth Low Energy	•
Wi-Fi IEEE 802.11 standards	Wi-Fi 6 (802.11ax)
Wi-Fi 2.4 / 5 [GHz]	2.4 and 5
LTE filter	o
Bluetooth output power conducted [dBm]	10
Wi-Fi output power conducted [dBm]	19
Antenna type	3 U.FL connectors
OS support	
Android / Linux drivers (from u-blox)	•
Interfaces	
UART ^B	1
PCIe ^W	1
SDIO [version]	v3 *
PCM / I2S (Bluetooth audio)	1
Features	
Concurrent dual band	•
Micro Access Point [max connects]	64
AES hardware support	•
Wi-Fi direct	•
RF parameters in OTP memory	•
MAC addresses in OTP memory	•

B = For Bluetooth only
W = For Wi-Fi only

* = Requires a minor hardware modification

M2-JODY-W3 module



Features

Wi-Fi standards	IEEE 802.11 a/b/g/n/ac/ax IEEE 802.11 d/e/h/i/k/r/u/v/w/mc
Wi-Fi channels	2.4 GHz: 1-13 5 GHz: 36-165
Bluetooth	v5.3 (Bluetooth Low Energy and Bluetooth with EDR) Class 1 and 2 transmission Bluetooth Low Energy long range
Antenna connectors	U,FL 1: 2.4 GHz and 5 GHz Wi-Fi U,FL 2: 2.4 GHz and 5 GHz Wi-Fi U,FL 3: Bluetooth
Output power	Wi-Fi: TBD Bluetooth BR/EDR: TBD Bluetooth LE: TBD
Security	Hardware encryption engine: AES-CCMP, AES-GCMP, TKIP WPA/WPA2/WPA3, WAPI, WEP 128-bit AES hardware support

Software features

RF parameters	Available in on-board OTP memory
MAC addresses	Available in on-board OTP memory
Operation modes	Station (STA) Access Point (AP) Wi-Fi Direct P2P Combinations of STA, AP, P2P
Driver support	Linux drivers in source code

Interfaces

Wi-Fi	PCIe (default) SDIO v3.0 ¹
Bluetooth	High-speed UART, 4-wire (default) SDIO v3.0 ¹
Bluetooth audio	PCM audio I2S
Other interfaces	GPIOs

¹ = Upon request; requires minor hardware modification

Package

Dimensions	22.0 × 30.0 × 4.2 mm
Mounting	M.2 Key-E connector 2199230-4 on host platform

Environmental data, quality & reliability

Operating temperature	-40 °C to +85 °C
Standard qualification	

Electrical data

Power supply	3.3 V (from M.2 card voltage pin) 1.8 V (generated by on-card DCDC)
I/O power supply	3.3 V or 1.8 V (default: 1.8 V)

Certifications and approvals

Type approvals	TBD
Bluetooth qualification	TBD

Product variants

M2-JODY-W377	Standard grade M.2 card module with three antenna pins and concurrent dual band 2x2 2.4 GHz and 5 GHz 802.11ax, BT/BLE 5.3. NXP chipset 88Q9098
--------------	---

Further information

For contact information, see www.u-blox.com/contact-u-blox.

For more product details and ordering information, see the [product data sheet](#).

Legal Notice:

u-blox reserves all rights to this document and the information contained herein. Products, names, logos and designs described herein may in whole or in part be subject to intellectual property rights. Reproduction, use, modification or disclosure to third parties of this document or any part thereof without the express permission of u-blox is strictly prohibited.

The information contained herein is provided "as is". No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose or content of this document. This document may be revised by u-blox at any time. For most recent documents, please visit www.u-blox.com.
Copyright © 2022, u-blox AG