



1 2 3 4 5 6 7 8 9

F






NOTES:

CURRENT RATING:3A AC/DC.
 VOLTAGE RATING:250V AC/DC
 TEMPERATURE RANGE:-40°C~+105°C.
 CONTACT RESISTANCE:30mΩ Max.
 INSULATION RESISTANCE:1000MΩ Min.
 WITHSTANDING VOLTAGE: 1000V AC/MINUTE.

MATERIAL:

HOUSING:LCP UL94V-0
 CONTACT: COPPER ALLOY


E




No. of pin/row	Dimensions(mm)	
	L	M
02	8.00	2.00
03	10.00	4.00
04	12.00	6.00
05	14.00	8.00
06	16.00	10.00
07	18.00	12.00
08	20.00	14.00
09	22.00	16.00
10	24.00	18.00
11	26.00	20.00
12	28.00	22.00
13	30.00	24.00
14	32.00	26.00
15	34.00	28.00
16	36.00	30.00

D

C



PCB LAYOUT



Ordering Information

G WFC112-XX XX A 002 C X B X

No. of Pins per Row 02~16 Standard Plating 01=Tin, 02=Gold Flash, 22=Matte Tin, ...
 Color 1=Black, 2=White, ... Standard Packing D=Tape&Reel, Selective Packing B=Tray, ...

B

A

<p>Website:www.greenconn.com E-mail:sales@greenconn.com</p>			3RD.ANG PROJ. 	GENERAL TOLERANCE		DESIGNED: CHECKED: APPROVED:	DATE: DATE: DATE:	DWG. NO.	TITLE.
				X'±3.0'	X.±/			GWFC112-CA002	
REV.	UNIT.	SCALE.	PAGE.	.X'±2.0'	.X±0.30		PART NO.	2.00mm pitch wafer SMT	
A	mm	1:1	1/1	.XX'±1.5'	.XX±0.25		GWFC112-XXXXA002CXBX		
				.XXX'±1.0'	.XXX±0.15				

1 2 3 4 5 6 7 8 9