





1 2 3 4 5 6 7 8 9

F
E
D
C
B
A

F
E
D
C
B
A



Specifications
 Current Rating:2Amp AC/DC
 Voltage Rating:100V AC/DC
 Contact Resistance:10mΩ Max.
 Insulation Resistance:1000MΩ Min.
 Dielectric Withstanding Voltage:800VAC
 Temperature Range:-40°C to +105°C
 Materials
 Contact Material:Brass
 Insulator Material:PA66 UL 94V-0
 All materials must meet GREENCONN
 hazardous substances control standards.



CIRCUITS	L	M	CIRCUITS	L	M
02	6.00	2.00	10	22.00	18.00
03	8.00	4.00	11	24.00	20.00
04	10.00	6.00	12	26.00	22.00
05	12.00	8.00	13	28.00	24.00
06	14.00	10.00	14	30.00	26.00
07	16.00	12.00	15	32.00	28.00
08	18.00	14.00	16	34.00	30.00
09	20.00	16.00			

Ordering Information

G WFB123 - XX XX A 001 E X Z X-9B

No. of Pins per Row 02~16 Standard Plating 01=Tin

Color 1=Black 2=White Standard Packing N=PE Bag Standard Packing D=Tape&Reel

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE

X:±	X.±
.X'±	.X±0.25
.XX'±	.XX±0.20
.XXX'±	.XXX±0.10

DESIGNED:	DATE:
CHECKED:	DATE:
APPROVED:	DATE:

DWG. NO.	GWFB123-CA1EZ
PART NO.	GWFB123-XXXXA001EXZX-9B






TITLE.
 2.0mm pitch 90° DIP type

REV. B	UNIT. mm	SCALE. 1:1	PAGE. 1/1	
--------	----------	------------	-----------	--

1 2 3 4 5 6 7 8 9

1 2 3 4 5 6 7 8 9

F
E
D
C
B
A



Specifications
 Voltage rating:100V AC/DC
 Current Rating:2A AC/DC
 Withstanding Voltage:800V AC
 Insulation Resistance:1000MΩ Min.
 Contact Resistance:20mΩ Max.
 After environmental testing: ≤20mΩ
 Operating Temperature:-25°C to +85°C
 Materials
 Insulator Material:PA66 94V-0
 All materials must meet GREENCONN
 hazardous substances control standards.

Pins	Dimensions(mm)	
	M	L
2	2.00	4.60
3	4.00	6.60
4	6.00	8.60
5	8.00	10.60
6	10.00	12.60
7	12.00	14.60
8	14.00	16.60
9	16.00	18.60
10	18.00	20.60
11	20.00	22.60
12	22.00	24.60
13	24.00	26.60
14	26.00	28.60
15	28.00	30.60
16	30.00	32.60

Ordering Information

GWF181 - XX A XX

No. of Pins Materials /Color
 02-16 M=YN66/White
 M1=YN66/Black



格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE X:± X.± .X'±2.0' .X±0.30 .XX'±1.0' .XX±0.20 .XXX'± .XXX±0.10				DESIGNED: CHECKED: APPROVED:	DATE: DATE: DATE:	DWG. NO. GWF181-HA PART NO. GWF181-XXAXX	TITLE. Pitch 2.0 Housing
REV. A UNIT. mm SCALE. 1:1 PAGE. 1/1							

1 2 3 4 5 6 7 8 9

1 2 3 4 5 6 7 8 9

F




Materials
 Insulator Material: Phosphor Bronze
 Finish: Tin-plated
 wire range: AWG#24-32
 All materials must meet GREENCONN
 hazardous substances control standards.


E

D


C



SECTION A-A



SECTION B-B



SECTION C-C

Ordering Information

GRF143 - 01 XX XX

Standard Plating
 01= Tin
 02= Gold Flash

Materials
 AB= Phosphor bronze

A

格稜股份有限公司
Greenconn Corporation

GENERAL TOLERANCE	
X: ±	X, ±/
.X' ±	.X ±0.40
.XX' ±	.XX ±0.35
.XXX' ±	.XXX ±0.15

DESIGNED:	DATE:
CHECKED:	DATE:
APPROVED:	DATE:

DWG. NO.	GRF143-T1
PART NO.	GRF143-01XXXX

TITLE:
 Pitch 2.00mm Crimp Style
 Connectors

REV. B	UNIT. mm	SCALE. 1:1	PAGE. 1/1	
--------	----------	------------	-----------	--

1 2 3 4 5 6 7 8 9

F

E

D

C

B

A