

N-Channel 60-V (D-S) MOSFET

PRODUCT SUMMARY							
V _{DS} (V)	$R_{DS(on)}\left(\Omega\right)$	$I_D(\Omega)$ $I_D(A)^a$ Q_g					
60	0.076 at V _{GS} = 10 V	5.5	29 nC				
	0.088 at V _{GS} = 4.5 V	4.5	29110				


FEATURES


- · Halogen-free
- TrenchFET® Power MOSFET



APPLICATIONS

· Load Switches for Portable Devices





N-Channel MOSFET

Parameter	Symbol	Limit	Unit		
Drain-Source Voltage	V_{DS}	60			
Gate-Source Voltage	V_{GS}	± 20			
	T _C = 25 °C		5.5 ^a		
Continuous Drain Current (T _{.1} = 150 °C)	T _C = 70 °C	I_	4 ^a		
Continuous Brain Current (1) = 130 °C)	T _A = 25 °C	l _D	4.7 ^{a, b, c}	A	
	T _A = 70 °C		4 ^{a, b, c}		
Pulsed Drain Current	I _{DM}	20			
Continuous Source-Drain Diode Current	T _C = 25 °C	I _S	5.2		
Continuous Source-Diam Diode Current	T _A = 25 °C	'S	5.1 ^{b, c}		
	T _C = 25 °C		5.3		
Maximum Power Dissipation	T _C = 70 °C	P _D	4	W	
	T _A = 25 °C	' Б	2.5 ^{b, c}	VV	
	T _A = 70 °C		1.6 ^{b, c}		
Operating Junction and Storage Temperatur	T _J , T _{stg}	- 55 to 150	°C		
Soldering Recommendations (Peak Tempera	ature) ^{e, f}		260		

THERMAL RESISTANCE RATINGS								
Parameter	Symbol	Typical	Maximum	Unit				
Maximum Junction-to-Ambient ^{a, c, d}	t ≤ 5 s	R _{thJA}	40	50	°C/W			
Maximum Junction-to-Foot (Drain)	Steady State	R_{thJF}	15	20]			

- a. Package limited, T_C = 25 °C.
 b. Surface Mounted on 1" x 1" FR4 board.
- d. Maximum under Steady State conditions is 95 °C/W.
- e. See Reliability Manual for profile. The ChipFET is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection.
- f. Rework Conditions: manual soldering with a soldering iron is not recommended for leadless components.




Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit	
Static	<u> </u>		L		L		
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0 \text{ V}, I_D = 250 \mu\text{A}$	60			V	
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$	I _D = 250 μA		25			
V _{GS(th)} Temperature Coefficient	$\Delta V_{GS(th)}/T_{J}$	I _D = 250 μA		- 4.0		mV/°C	
Gate-Source Threshold Voltage	V _{GS(th)}	$V_{DS} = V_{GS}$, $I_{D} = 250 \mu A$	1.5		3.0	V	
Gate-Source Leakage	I _{GSS}	$V_{DS} = 0 \text{ V}, V_{GS} = \pm 12 \text{ V}$			± 100	nA	
Zana Oata Wallana Basia Oamaal	,	$V_{DS} = 60 \text{ V}, V_{GS} = 0 \text{ V}$			1		
Zero Gate Voltage Drain Current	DSS	V _{DS} = 60 V, V _{GS} = 0 V, T _J = 55 °C			10	μΑ	
On-State Drain Current ^a	I _{D(on)}	$V_{DS} \ge 5 \text{ V}, V_{GS} = 4.5 \text{ V}$	25			Α	
		$V_{GS} = 4.5 \text{ V}, I_D = 3.3 \text{ A}$		0.088		Ω	
Drain-Source On-State Resistance ^a	R _{DS(on)}	V _{GS} = 10 V, I _D = 4.5 A		0.076			
Forward Transconductance ^a	g _{fs}	V _{DS} = 10 V, I _D = 4.3 A		45		S	
Dynamic ^b	<u> </u>					1	
Input Capacitance	C _{iss}			800			
Output Capacitance	C _{oss}	V _{DS} = 10 V, V _{GS} = 0 V, f = 1 MHz		120		pF	
Reverse Transfer Capacitance	C _{rss}			100			
T. (10) (1)	Qg	$V_{DS} = 10 \text{ V}, V_{GS} = 10 \text{ V}, I_{D} = 6.3 \text{ A}$		22	33	nC	
Total Gate Charge				10	15		
Gate-Source Charge	Q_{gs}	$V_{DS} = 10 \text{ V}, V_{GS} = 4.5 \text{ V}, I_D = 6.3 \text{ A}$		2.5			
Gate-Drain Charge	Q_{gd}			1.7		1	
Gate Resistance	R_g	f = 1 MHz		2.4		Ω	
Turn-on Delay Time	t _{d(on)}			15	25		
Rise Time	t _r	$V_{DD} = 10 \text{ V, R}_{L} = 1.5 \Omega$		10	15		
Turn-Off Delay Time	t _{d(off)}	$I_D\cong 6.7~A,~V_{GEN}$ = 4.5 V, R_g = 1 Ω		35	55		
Fall Time	t _f			12	20	1	
Turn-on Delay Time	t _{d(on)}			10	15	ns	
Rise Time	t _r	V_{DD} = 10 V, R_L = 1.5 Ω		12	20		
Turn-Off Delay Time	t _{d(off)}	$I_D\cong 6.7$ A, V_{GEN} = 10 V, R_g = 1 Ω		25	40	1	
Fall Time	t _f			10	15	1	
Drain-Source Body Diode Characteristic	:S		I.		<u>I</u>		
Continuous Source-Drain Diode Current	I _S	T _C = 25 °C			7.2	^	
Pulse Diode Forward Current	I _{SM}				25	A	
Body Diode Voltage	V_{SD}	$I_S = 6.7 \text{ A}, V_{GS} = 0 \text{ V}$		0.8	1.2	V	
Body Diode Reverse Recovery Time	t _{rr}			20	40	ns	
Body Diode Reverse Recovery Charge	Q _{rr}	L = 6.7 A dl/dt = 100 A/va T = 05.90		10	20	nC	
Reverse Recovery Fall Time	t _a	$I_F = 6.7 \text{ A}, \text{ dI/dt} = 100 \text{ A/}\mu\text{s}, T_J = 25 ^{\circ}\text{C}$		10			
Reverse Recovery Rise Time	t _b			10		ns	


- a. Pulse test; pulse width \leq 300 µs, duty cycle \leq 2 % b. Guaranteed by design, not subject to production testing.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.














V_{GS} - Gate-to-Source Voltage (V)

0.050

On-Resistance vs. Gate-to-Source Voltage









* V_{GS} > minimum V_{GS} at which $R_{DS(on)}$ is specified

Safe Operating Area, Junction-to-Ambient









^{*} The power dissipation P_D is based on $T_{J(max)} = 150$ °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.






Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Foot



Package outline - SOT89



DIM	DIM Millimeters		Inches		DIM	Millimeters		Inches	
	Min	Max	Min	Max		Min	Max	Min	Max
Α	1.40	1.60	0.550	0.630	Е	2.29	2.60	0.090	0.102
В	0.44	0.56	0.017	0.022	E1	2.13	2.29	0.084	0.090
B1	0.36	0.48	0.014	0.019	е	1.50 BSC		0.059 BSC	
С	0.35	0.44	0.014	0.017	e1	3.00 BSC		0.118 BSC	
D	4.40	4.60	0.173	0.181	Н	3.94	4.25	0.155	0.167
D1	1.62	1.83	0.064	0.072	L	0.89	1.20	0.035	0.047

Note: Controlling dimensions are in millimeters. Approximate dimensions are provided in inches

服务热线:400-655-8788

7



Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.