## SIEMENS

## Data sheet

## 3LD3348-1TL51



Load disconnector 3LD3, lu 40 A Main switch 3-pole + N Rated operating capacity at AC-23 A at 400 V 18.5 kW floor mounting Basic switch with door coupling Central hole mounting 22.5mm Rotating drive black 66 x 66 mm with auxiliary switch 10E + 1S

Model		
product brand name	SENTRON	
product designation	3LD Switch disconnector	
design of the product	Main switch	
display version / for switch position indicator manual operation	1 ON - 0 OFF	
design of the actuating element	Short rotary knob	
design of handle	rotary operating mechanism, black	
General technical data		
number of poles	4	
number of poles / note	4	
type of device	fixed mounting	
type of switch	Floor mounting with door coupling	
mechanical service life (switching cycles) / typical	100 000	
electrical endurance (switching cycles)		
• at AC-23 A / at 690 V	6 000	
l2t value / with closed switch / at 690 V / for combination switch + gG fuse / maximum	15 kA2.s	
let-through I2t value / with closed switch / at 440 V / for combination switch + gG fuse / maximum	15 kA2.s	
operating frequency / maximum	50 1/h	
Voltage		
insulation voltage / rated value	690 V	
surge voltage resistance / rated value	6 kV	
Protection class		
protection class IP	IP65	
degree of protection NEMA rating	1, 3R, 4X, 12	
protection class IP / on the front	IP65	
Dissipation		
power loss [W]		
<ul> <li>for rated value of the current / at AC / in hot operating state / per pole</li> </ul>	2.5 W	
<ul> <li>per conductor / typical</li> </ul>	2 W	
Current		
operational current		
• at 40 °C / rated value	40 A	
• at 45 °C / rated value	40 A	
• at 50 °C / rated value	40 A	
• at 55 °C / rated value	40 A	
• at AC / rated value	40 A	

• at AC-23 A / at 400 V / rated value	36 A
• at AC-21 / at 690 V / rated value	40 A
at AC-21 A / at 240 V / rated value	40 A
at AC-21 A / at 440 V / rated value	40 A
operational current / of upstream fuse / rated value	40 A
let-through current / with closed switch	
<ul> <li>at 440 V / for combination switch + gG fuse / maximum</li> </ul>	5 kA
<ul> <li>at 690 V / for combination switch + gG fuse / maximum permissible</li> </ul>	5 kA
Main circuit	
operating power	
• at AC-23 A / at 240 V / rated value	7.5 kW
<ul> <li>at AC-23 A / at 400 V / rated value</li> </ul>	19 kW
<ul> <li>at AC-23 A / at 440 V / rated value</li> </ul>	15 kW
<ul> <li>at AC-23 A / at 690 V / rated value</li> </ul>	15 kW
<ul> <li>at AC-3 / at 240 V / rated value</li> </ul>	7.5 kW
<ul> <li>at AC-3 / at 400 V / rated value</li> </ul>	12 kW
• at AC-3 / at 690 V / rated value	11.5 kW
operational current / rated value	40 A
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
number of NC contacts / for auxiliary contacts	1
number of NO contacts / for auxiliary contacts	1
operating voltage / of auxiliary contacts / at AC / maximum	500 V
	10 A
continuous current / of the auxiliary contact / rated value	500 V
insulation voltage / of the auxiliary switch / rated value	500 V
Suitability	
suitability for use	
• main switch	Yes
switch disconnector	Yes
EMERGENCY OFF switch	No
safety switch	Yes
maintenance/repair switch	Yes
Appearance	
color / of the actuating element	black
Product details	
product feature	
can be locked into OFF position	Yes
number of bracket locks / maximum	2
hasp thickness / of the bracket locks / minimum	4 mm
hasp thickness / of the bracket locks / maximum	6 mm
special product feature	Can be locked in zero position
product extension / optional	
motor drive	No
<ul> <li>voltage trigger</li> </ul>	No
Short circuit	
conditional short-circuit current / with line-side fuse protection	
<ul> <li>at 440 V / by gG fuse / rated value</li> </ul>	10 kA
• at 690 V / by gG fuse / rated value	6 kA
according UL	
operational current / at AC / according to UL 508/UL 60947-4-1 / rated value	40 A
operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value	600 V
active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value	20
active power [hp] / at AC / at 600 V / according to UL 508/UL 60947-4-1 / rated value	20
short-time withstand current (SCCR) / at 600 V / according	5 kA

to UL 508/UL 60947-4-1	
continuous current / of upstream fuse / according to UL / rated value	50 A
type of fuse / according to UL	RK5
Number	
number of connectable NC contacts / for auxiliary contacts / attachable / maximum	2
number of connectable NO contacts / for auxiliary contacts / attachable / maximum	4
number of connectable CO contacts / for auxiliary contacts / attachable / maximum	0
Connections	
AWG number / as coded connectable conductor cross section / solid	
• maximum	6
• minimum	14
type of connectable conductor cross-sections / for copper conductor	
• solid	1x (2.5 to 16 mm²)
<ul> <li>finely stranded / with core end processing</li> </ul>	1x (2.516 mm <sup>2</sup> )
• stranded	1x (2.5 to 16 mm <sup>2</sup> )
type of connectable conductor cross-sections / for auxiliary contacts	
• solid	2x (0.75 2.5 mm²), 1x 4 mm²
<ul> <li>finely stranded / with core end processing</li> </ul>	2x (0.75 1.5 mm²), 1x 2.5 mm²
• stranded	2x (0.75 2.5 mm²), 1x 4 mm²
type of electrical connection	
for main current circuit	box terminal
<ul> <li>for auxiliary contacts</li> </ul>	Box terminals
Requirements	
design of the fuse link	
<ul> <li>for short-circuit protection of the main circuit / required</li> </ul>	fuse gL/gG: 40 A
<ul> <li>for short-circuit protection of the auxiliary switch / required</li> </ul>	fuse gL/gG: 10 A
Mechanical Design	
height	60 mm
width	60 mm
depth	380 mm
fastening method	Built-in unit fixed-mounted version
fastening method	
• 4-hole front mounting	No
<ul> <li>front mounting with central attachment</li> </ul>	Yes
rail mounting	Yes
net weight	300 g
Environmental conditions	
ambient temperature / during operation	
• minimum	-25 °C
• maximum	55 °C
ambient temperature / during storage / minimum	-25 °C
General Product Approval	Declaration of Conformity
<u>Confirmation</u>	FAL AR CE


other

**Miscellaneous** 

## Further information Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3348-1TL51 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3LD3348-1TL51 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax\_en.aspx?mlfb=3LD3348-1TL51 CAx-Online-Generator http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications





Ø

7/8/2022