SIEMENS

Data sheet 3LD3248-1TK53



Load disconnector 3LD3, lu 32 A Main switch 3-pole Rated operating capacity for AC-23 A at 400V 11.5kW floor mounting Basic switch with door coupling Central hole mounting 22.5mm Rotary actuator red / yellow 66 x 66 mm with auxiliary switch 10E + 1S

Model		
product brand name	SENTRON	
product designation	3LD Switch disconnector	
design of the product	EMERGENCY-STOP switch	
display version / for switch position indicator manual operation	1 ON - 0 OFF	
design of the actuating element	Short rotary knob	
design of handle	rotary operating mechanism, red/yellow	
type of the driving mechanism / motor drive	No	
General technical data		
number of poles	3	
number of poles / note	3	
type of device	fixed mounting	
type of switch	Floor mounting with door coupling	
mechanical service life (switching cycles) / typical	100 000	
electrical endurance (switching cycles)		
• at AC-23 A / at 690 V	6 000	
I2t value / with closed switch / at 690 V / for combination switch + gG fuse / maximum	9 kA2.s	
let-through I2t value / with closed switch / at 440 V / for combination switch + gG fuse / maximum	9 kA2.s	
operating frequency / maximum	50 1/h	
Voltage		
insulation voltage / rated value	690 V	
surge voltage resistance / rated value	6 kV	
Protection class		
protection class IP	IP65	
degree of protection NEMA rating	1, 3R, 4X, 12	
protection class IP / on the front	IP65	
Dissipation		
power loss [W]		
 for rated value of the current / at AC / in hot operating state / per pole 	1.8 W	
per conductor / typical	2 W	
Current		
operational current		
• at 40 °C / rated value	32 A	
 at 45 °C / rated value 	32 A	
 at 50 °C / rated value 	32 A	
• at 55 °C / rated value	32 A	

	22 A
• at AC 23.4 / at 400 V / retail value	32 A 22 A
• at AC-23 A / at 400 V / rated value	
• at AC-21 / at 690 V / rated value	32 A
• at AC-21 A / at 240 V / rated value	32 A
at AC-21 A / at 440 V / rated value	32 A
operational current / of upstream fuse / rated value	32 A
let-through current / with closed switch	4514
 at 440 V / for combination switch + gG fuse / maximum 	4.5 kA
• at 690 V / for combination switch + gG fuse /	5 kA
maximum permissible	O IVI
Main circuit	
operating power	
at AC-23 A / at 240 V / rated value	6 kW
• at AC-23 A / at 400 V / rated value	12 kW
 at AC-23 A / at 440 V / rated value 	11.5 kW
• at AC-23 A / at 690 V / rated value	12 kW
• at AC-3 / at 240 V / rated value	5.5 kW
• at AC-3 / at 400 V / rated value	10 kW
• at AC-3 / at 400 V / rated value	9.5 kW
operational current / rated value	32 A
Auxiliary circuit	
	0
number of CO contacts / for auxiliary contacts	1
number of NC contacts / for auxiliary contacts	1
number of NO contacts / for auxiliary contacts	
operating voltage / of auxiliary contacts / at AC / maximum	500 V
continuous current / of the auxiliary contact / rated value	10 A
insulation voltage / of the auxiliary switch / rated value	500 V
Suitability	
suitability for use	
main switch	Yes
switch disconnector	Yes
EMERGENCY OFF switch	Yes
safety switch	Yes
maintenance/repair switch	Yes
Appearance	
color / of the actuating element	red
Product details	
product feature	
can be locked into OFF position	Yes
can be locked into OFF position number of bracket locks / maximum	Yes 3
·	
number of bracket locks / maximum	3
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum	3 4 mm
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum	3 4 mm 8 mm
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature	3 4 mm 8 mm
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional • motor drive	3 4 mm 8 mm Can be locked in zero position
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position No No
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position No No
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position No No
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position No No 10 kA 6 kA
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position No No 10 kA 6 kA
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position No No 10 kA 6 kA
number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum special product feature product extension / optional	3 4 mm 8 mm Can be locked in zero position No No 10 kA 6 kA 32 A 600 V

short-time withstand current (SCCR) / at 600 V / according to UL 508/UL 60947-4-1	5 kA
continuous current / of upstream fuse / according to UL / rated value	50 A
type of fuse / according to UL	RK5
Number	
number of connectable NC contacts / for auxiliary contacts / attachable / maximum	2
number of connectable NO contacts / for auxiliary contacts / attachable / maximum	4
number of connectable CO contacts / for auxiliary contacts / attachable / maximum	0
Connections	
AWG number / as coded connectable conductor cross section / solid	
• maximum	6
• minimum	14
type of connectable conductor cross-sections / for copper conductor	
• solid	1x (2.5 to 16 mm²)
finely stranded / with core end processing	1x (2.516 mm²)
stranded	1x (2.5 to 16 mm²)
type of connectable conductor cross-sections / for auxiliary contacts	
• solid	2x (0.75 2.5 mm²), 1x 4 mm²
finely stranded / with core end processing	2x (0.75 1.5 mm²), 1x 2.5 mm²
stranded	2x (0.75 2.5 mm²), 1x 4 mm²
type of electrical connection	
for main current circuit	box terminal
for auxiliary contacts	Box terminals
Requirements	
design of the fuse link	
 for short-circuit protection of the main circuit / required 	fuse gL/gG: 40 A
 for short-circuit protection of the auxiliary switch / required 	fuse gL/gG: 10 A
Mechanical Design	
height	60 mm
width	47 mm
depth	380 mm
fastening method	Built-in unit fixed-mounted version
fastening method	
 4-hole front mounting 	No
 front mounting with central attachment 	Yes
rail mounting	Yes
net weight	300 g
Environmental conditions	
ambient temperature / during operation	
• minimum	-25 °C
maximum	55 °C
ambient temperature / during storage / minimum	-25 °C
General Product Approval	Declaration of Conformity
Confirmation	



Confirmation









other

Miscellaneous

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3248-1TK53

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3LD3248-1TK53

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD3248-1TK53

CAx-Online-Generator

http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications

