SIEMENS

Data sheet

3LD2866-0TB53-0US2



SENTRON, Switch disconnector 3LD, emergency switching-off switch, 3-pole, Iu: 125 A, operating power / at AC-23 A 400 V: 45 kW, Molded plastic encapsulation for inch cable gland, rotary operating mechanism, red/yellow

Model		
product brand name	SENTRON	
product designation	3LD Switch disconnector	
design of the product	EMERGENCY-STOP switch	
display version / for switch position indicator manual operation	1 ON - 0 OFF	
design of the actuating element	Short rotary knob	
design of handle	rotary operating mechanism, red/yellow	
type of the driving mechanism / motor drive	No	
General technical data		
number of poles	3	
number of poles / note	N + PE	
type of device	fixed mounting	
type of switch	Molded-plastic enclosure for inch threaded joint	
size of switch disconnector	4	
mechanical service life (switching cycles) / typical	100 000	
electrical endurance (switching cycles)		
• at AC-23 A / at 690 V	6 000	
I2t value / with closed switch / at 690 V / for combination switch + gG fuse / maximum	104 kA2.s	
let-through I2t value / with closed switch / at 440 V / for combination switch + gG fuse / maximum	104 kA2.s	
operating frequency / maximum	50 1/h	
Voltage		
insulation voltage / rated value	690 V	
surge voltage resistance / rated value	6 kV	
Protection class		
protection class IP	IP65	
degree of protection NEMA rating	1, 4X, 12	
protection class IP / on the front	IP65	
Dissipation		
power loss [W]		
 for rated value of the current / at AC / in hot operating state / per pole 	12 W	
per conductor / typical	12 W	
Current		
operational current		
at 40 °C / rated value	125 A	
• at 45 °C / rated value	125 A	
• at 50 °C / rated value	125 A	

and EE °C / restand value	40F A
• at 55 °C / rated value	125 A
at AC / rated value	125 A
• at AC-23 A / at 400 V / rated value	80 A
• at AC-21 / at 690 V / rated value	125 A
• at AC-21 A / at 240 V / rated value	125 A 125 A
at AC-21 A / at 440 V / rated value operational current / of upstream fuse / rated value	125 A
let-through current / with closed switch	125 A
• at 440 V / for combination switch + gG fuse /	10 kA
maximum	
 at 690 V / for combination switch + gG fuse / 	10 kA
maximum permissible	
Main circuit	
operating power	
at AC-23 A / at 240 V / rated value	22 kW
at AC-23 A / at 400 V / rated value	45 kW
at AC-23 A / at 440 V / rated value	45 kW
• at AC-23 A / at 690 V / rated value	37 kW
at AC-3 / at 240 V / rated value	22 kW
• at AC-3 / at 400 V / rated value	37 kW
at AC-3 / at 690 V / rated value	30 kW
operational current / rated value	125 A
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
number of NC contacts / for auxiliary contacts	0
number of NO contacts / for auxiliary contacts	0
operating voltage / of auxiliary contacts / at AC / maximum	500 V
continuous current / of the auxiliary contact / rated value	10 A
insulation voltage / of the auxiliary switch / rated value	500 V
Suitability	
suitability for use	v.
• main switch	Yes
switch disconnector SMED OF NOV OFF	Yes
EMERGENCY OFF switch	Yes
• safety switch	Yes
maintenance/repair switch	Yes
Appearance	
color / of the actuating element	red
Product details	
product feature	
can be locked into OFF position	Yes
number of bracket locks / maximum	3
hasp thickness / of the bracket locks / minimum	4 mm
hasp thickness / of the bracket locks / maximum	8 mm
product extension / optional	N ₂
• motor drive	No
voltage trigger	No
Short circuit	
conditional short-circuit current / with line-side fuse protection	
• at 690 V / by gG fuse / rated value	20 kA
according UL	20 10 1
operational current / at AC / according to UL 508/UL	125 A
60947-4-1 / rated value	120 //
operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value	600 V
active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value	75
active power [hp] / at AC / at 600 V / according to UL 508/UL 60947-4-1 / rated value	100
short-time withstand current (SCCR) / at 600 V / according	10 kA

to UL 508/UL 60947-4-1	000 A
continuous current / of upstream fuse / according to UL / rated value	200 A
type of fuse / according to UL	RK5
Number	
number of connectable NC contacts / for auxiliary contacts / attachable / maximum	3
number of connectable NO contacts / for auxiliary contacts / attachable / maximum	5
number of connectable CO contacts / for auxiliary contacts / attachable / maximum	0
Connections	
AWG number / as coded connectable conductor cross section / solid	
• maximum	1
• minimum	12
type of connectable conductor cross-sections / for copper conductor	
• solid	1x (450mm²)
 finely stranded / with core end processing 	1x (435mm²)
• stranded	1x (450mm²)
type of connectable conductor cross-sections / for auxiliary contacts	
• solid	lateral auxiliary switch 2x (0,75 2,5mm²), 1x 4mm²; front auxiliary switch 1x (0,75 2,5mm²)
• finely stranded / with core end processing	lateral auxiliary switch 2x (0,75 1,5mm²), 1x 2,5mm²; front auxiliary switch 1x 2,5mm²
• stranded	lateral auxiliary switch 2x (0,75 2,5mm²), 1x 4mm²; front auxiliary switch 1x (0,75 2,5mm²)
type of electrical connection	
 for main current circuit 	box terminal
 for auxiliary contacts 	connection terminals
Requirements	
design of the fuse link	
 for short-circuit protection of the main circuit / required 	fuse gL/gG: 125 A
 for short-circuit protection of the auxiliary switch / required 	fuse gL/gG: 10 A
Mechanical Design	
height	302 mm
width	212 mm
depth	181 mm
fastening method	Complete unit in enclosure
fastening method	
 4-hole front mounting 	No
 front mounting with central attachment 	Yes
rail mounting	No
net weight	1 919 g
Environmental conditions	
ambient temperature / during operation	
• minimum	-25 °C
• maximum	55 °C
ambient temperature / during storage / minimum	-25 °C
General Product Approval	



Confirmation







Miscellaneous

General Product Declaration of Conformity Test Certificates Marine / Shipping





Special Test Certificate

Miscellaneous



other

Environmental Confirmations Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD2866-0TB53-0US2

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3LD2866-0TB53-0US2

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD2866-0TB53-0US2

CAx-Online-Generator

http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications

