# **SIEMENS**

#### **Data sheet**

Model

## 3VA5120-5EC36-1AA0



circuit breaker 3VA5 UL frame 125 breaking capacity class M 35kA @ 480 V 3-pole, line protection TM230, FTAM, In=20A overload protection Ir=20A fixed short-circuit protection Ii=7.5...15 x In UL489 SB (naval), 50 deg. cel. cable connection on both sides

Model		
product brand name	SENTRON	
product designation	Molded-case circuit breaker	
product designation / according to UL file	MEAM	
Product version	System protection	
design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type)	Yes	
design of the load switch / according to UL 489 / High- Intensity-Discharge circuit breaker (HID Type)	Yes	
design of the load switch / according to UL 489 / Switching Duty circuit breaker (SWD Type)	Yes	
design of the overcurrent release	TM230	
protection function of the overcurrent release	LI	
number of poles	3	
General technical data		
operating voltage / at AC / rated value	690 V	
power loss [W] / maximum	12.2 W	
Active power loss / for rated value of the current / at AC / in hot operating state / per pole	4.07 W	
mechanical service life (switching cycles) / typical	20 000	
Electrical endurance (switching cycles) / at AC-1 / at 380/415 V 50/60 Hz	8 000	
Electrical endurance (switching cycles) / at AC-1 / at 690 V 50/60 Hz	4 000	
electrical endurance (switching cycles) / at 480 V	8 000	
electrical endurance (switching cycles) / at 600 V	4 000	
Neutral conductors / upgradeable/retrofittable	No	
ground-fault monitoring version	without	
product function		
<ul> <li>communication function</li> </ul>	No	
<ul> <li>other measurement function</li> </ul>	No	
Net Weight	0.934 kg	
Current		
marking / according to UL 489 / 100%-rated breaker	No	
operational current		
• at 40 °C	20 A	
● at 45 °C	20 A	
● at 50 °C	19 A	
● at 55 °C	19 A	
● at 60 °C	19 A	
• at 65 °C	18 A	
● at 70 °C	18 A	

Switching capacity according to IEC 60947	
switching capacity class of the circuit breaker	M
design of short-circuit protection	For switching power values in DC networks, see the 3VA molded case circuit breaker device manual; link to be found under Service & Support in the last chapter
witching capacity according to UL 489	
breaking capacity current	
• at 240 V	85 kA
• at 480 V	35 kA
• at 600 Y/347 V	18 kA
djustable parameters	
product feature / for L-tripping / selectable characteristic function	No
type of value list setting current (Ir) / for L-tripping / with I2t characteristic	Fest
reference value setting current (Ir) / for L-tripping / with I2t characteristic	x In
set values setting current (Ir) / for L-tripping / with I2t characteristic	1
adjustable response factor setting current (Ir) / for L-tripping / with I2t characteristic / minimum	1
adjustable response factor setting current (Ir) / for L- tripping / with I2t characteristic / maximum	1
adjustable response value setting current (Ir) / of the L-trip / with I2t characteristic / minimum	20 A
adjustable response value setting current (Ir) / of the L-trip / with I2t characteristic / maximum type of value list delay time (tr) / for L-tripping / with I2t	20 A Fest
characteristic reference value delay time (tr) / for L-tripping / with I2t	S
characteristic set values delay time (tr) / for L-tripping / with I2t	1
characteristic adjustable response value delay time (tr) / for L-tripping /	1 s
with I2t characteristic / minimum adjustable response value delay time (tr) / for L-tripping /	1 s
with I2t characteristic / maximum product feature / for S-tripping / independent of direction /	No
selectable characteristic function product feature / for I-tripping / can be switched on/off	No
design of I-trip / adjustable	Yes
reference value setting current (li) / for I-tripping	x In
set values setting current (Ii) / for I-tripping adjustable response factor setting current (Ii) / for I- tripping / minimum	7.5;9;10.5;12;13.5;15 7.5
adjustable response factor setting current (li) / for l- tripping / maximum	15
adjustable response value setting current (li) / for l-tripping / minimum	150 A
adjustable response value setting current (li) / for l-tripping / maximum	300 A
product feature / for G-tripping / selectable characteristic function	No
product feature / with neutral conductor protection / can be switched on/off	No
product feature / with neutral conductor protection / adjustable	Yes
type of value list setting current (InN) / for N-tripping	St
reference value setting current (InN) / for N-tripping	x In
adjustable absolute value setting current (InN) / for N-ripping / minimum	0 A
adjustable absolute value setting current (InN) / for N-tripping / maximum	0 A
tripping characteristic / of the lower tolerance band	AK_3VA5_1_20A_TM2_SuMuH_uT
tripping characteristic / of the upper tolerance band	AK_3VA5_1_20A_TM2_SuMuH_oT
let-through energy characteristic / at 240 V	DE_3VA5_1_20A_TM_line u starter_3u4p_240V
let-through energy characteristic / at 415 V let-through energy characteristic / at 690 V	DE_3VA5_1_20A_TM_line u starter_3u4p_415V DE_3VA5_1_20A_TM_line u starter_3u4p_690V

type of value list setting current (li) / for I-tripping	St
tripping characteristic / of the let-through current characteristic / at 240 V	DS_3VA5_1_20A_TM_line u starter_3u4p_240V
tripping characteristic / of the let-through current characteristic / at 415 V	DS_3VA5_1_20A_TM_line u starter_3u4p_415V
tripping characteristic / of the let-through current characteristic / at 690 V	DS_3VA5_1_20A_TM_line u starter_3u4p_690V
Adjustable response value current / lg min.	20 A
adjustable current response value current / of the current- dependent overload release / full-scale value	20 A
Ground fault protection / tripping switchable / I2t=ON/OFF	No
Mechanical Design	
product component	
<ul> <li>undervoltage release</li> </ul>	No
<ul> <li>voltage trigger</li> </ul>	No

Mechanical Design	
product component	
<ul> <li>undervoltage release</li> </ul>	No
<ul> <li>voltage trigger</li> </ul>	No
trip indicator	No
height [in]	5.51 in
Height	140 mm
width [in]	3 in
Type of connectable conductor cross-section, round conductor terminal, stranded	1 x (8 AWG - 3/0)
Width	76.2 mm
depth [in]	3.01 in
depth	76.5 mm
Connections	
arrangement of electrical connectors / for main current circuit	Front connection
type of electrical connection / for main current circuit	circular conductor terminal on both sides
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
Accessories	
product extension / optional / motor drive	Yes
Environmental conditions	
protection class IP / on the front	IP40
ambient temperature	
<ul><li>during operation / minimum</li></ul>	-25 °C
<ul><li>during operation / maximum</li></ul>	70 °C
<ul> <li>during storage / minimum</li> </ul>	-40 °C
<ul> <li>during storage / maximum</li> </ul>	80 °C
Certificates	
certificate of suitability / as approval for NAVAL (no combat vessels) / supplement SB	Yes

## Confirmation

**General Product Approval** 









Miscellaneous

EMC Declaration of Conformity Marine / Shipping other











Miscellaneous

#### Further informatior

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA5120-5EC36-1AA0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3VA5120-5EC36-1AA0


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) <a href="http://www.automation.siemens.com/bilddb/cax">http://www.automation.siemens.com/bilddb/cax</a> en.aspx?mlfb=3VA5120-5EC36-1AA0


**CAx-Online-Generator** 


http://www.siemens.com/cax


**Tender specifications** 


http://www.siemens.com/specifications














last modified: 7/14/2022 🖸