




# 1.FIGURE AND DIMENSIONS(视图及尺寸)



XXXXXT-PXX-AXXXXXX-LXXX-XXXXXT-X  
 ① ② ③ ④ ⑤ ⑥

- ① 系列 (Series No)
- ② 材质 (Material) :P-PSN(磷铜先冲后镀锡)
- ③ 线规线色 (Wire gauge line color) A: (AWG32-AWG28)  
 Circuit: R (red) / B (black) / Y (yellow) / G (green) / L (blue) / P (purple) / YR (orange) / W (white)
- ④ 线长 (Line length) L: (可定制长度)
- ⑤ 系列 (Series No)
- ⑥ 正反接 (Positive and negative) Z (反接) / F (正接)

## 2. CIRCUIT DIAGRAM(接线图)

A	颜色	B
Circuit1	红色	Circuit10
Circuit2	黄色	Circuit9
Circuit3	黄色	Circuit8
Circuit4	黄色	Circuit7
Circuit5	黄色	Circuit6
Circuit6	黄色	Circuit5
Circuit7	黄色	Circuit4
Circuit8	黄色	Circuit3
Circuit9	黄色	Circuit2
Circuit10	黑色	Circuit1

## 3. MATERIAL(材料)

标志	料号	单用量	备注	总用量
1	X1002H-10L-N OHF	2PCS		
2	X1002T-PSN2	20PCS		
3	UL1007/28AWG. 红. 黑. 黄色	红. 黑色 各1PCS 黄色 8PCS	200MM	
总量				

					ANGLAR	±5°	<b>XKIB</b>	DSND		SCALE: N/A	DRAWING NO.			
					L ≤ 4	±0.2		DWN		VIEW:	X1002LT-PSN-A28RYYYYYYB-L200-X1002LT-F			
					4 < L ≤ 16	±0.3		CHKD		UNIT: mm/in	PART NO.:			
					16 < L ≤ 63	±0.4		APPD		SIZE: A4	DWG NO.:			
MARK	DESCRIPTION				DATE	REVISED	APPROVED					WEIGHT	SHEET	REVISION
REVISIONS							UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED				1/1	A0
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn														