SIEMENS

Data sheet

3RV2031-4UA15



Circuit breaker size S2 for motor protection, CLASS 10 A-release 32...40 A N-release 585 A screw terminal Standard switching capacity with transverse auxiliary switches 1 NO+1 NC

product brand name	SIRIUS
product designation	Circuit breaker
design of the product	For motor protection
product type designation	3RV2
General technical data	
size of the circuit-breaker	\$2
size of contactor can be combined company-specific	\$2 \$2
product extension auxiliary switch	Yes
power loss [W] for rated value of the current	
at AC in hot operating state	20 W
 at AC in hot operating state per pole 	6.7 W
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	25g / 11 ms Sinus
mechanical service life (switching cycles)	
 of the main contacts typical 	50 000
 of auxiliary contacts typical 	50 000
electrical endurance (switching cycles) typical	50 000
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	10/15/2014
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
 during operation 	-20 +60 °C
 during storage 	-50 +80 °C
during transport	-50 +80 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
adjustable current response value current of the current-dependent overload release	32 40 A
operating voltage	
 rated value 	20 690 V
 at AC-3 rated value maximum 	690 V
 at AC-3e rated value maximum 	690 V

operating frequency rated value	50 60 Hz
operational current rated value	40 A
operational current	
at AC-3 at 400 V rated value	40 A
• at AC-3e at 400 V rated value	40 A
operating power	
• at AC-3	
— at 230 V rated value	11 kW
— at 400 V rated value	18.5 kW
— at 500 V rated value	22 kW
— at 690 V rated value	37 kW
• at AC-3e	
— at 230 V rated value	11 kW
— at 400 V rated value	18.5 kW
— at 500 V rated value	22 kW
— at 690 V rated value	37 kW
operating frequency	
• at AC-3 maximum	15 1/h
• at AC-3e maximum	15 1/h
Auxiliary circuit	
design of the auxiliary switch	transverse
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
operational current of auxiliary contacts at AC-15	
• at 24 V	2 A
• at 230 V	0.5 A
operational current of auxiliary contacts at DC-13	
• at 24 V	1 A
• at 60 V	0.15 A
• at 110 V	0 A
• at 125 V	0 A
• at 220 V	0 A
Protective and monitoring functions	
product function	
 ground fault detection 	No
 phase failure detection 	Yes
trip class	CLASS 10
design of the overload release	thermal
breaking capacity maximum short-circuit current (Icu)	
• at AC at 240 V rated value	100 kA
• at AC at 400 V rated value	65 kA
• at AC at 500 V rated value	10 kA
• at AC at 690 V rated value	4 kA
breaking capacity operating short-circuit current (Ics)	
at AC	100 //
• at 240 V rated value	100 kA
• at 400 V rated value	30 kA
at 500 V rated value	5 kA
at 690 V rated value	2 kA
response value current of instantaneous short-circuit trip	585 A
unit	
unit	
unit UL/CSA ratings	
unit UL/CSA ratings full-load current (FLA) for 3-phase AC motor	40 A
unit UL/CSA ratings full-load current (FLA) for 3-phase AC motor • at 480 V rated value	40 A 40 A
unit UL/CSA ratings full-load current (FLA) for 3-phase AC motor • at 480 V rated value • at 600 V rated value	40 A 40 A
unit UL/CSA ratings full-load current (FLA) for 3-phase AC motor • at 480 V rated value • at 600 V rated value yielded mechanical performance [hp]	
unit UL/CSA ratings full-load current (FLA) for 3-phase AC motor • at 480 V rated value • at 600 V rated value yielded mechanical performance [hp] • for single-phase AC motor	40 A
unit UL/CSA ratings full-load current (FLA) for 3-phase AC motor • at 480 V rated value • at 600 V rated value yielded mechanical performance [hp] • for single-phase AC motor — at 110/120 V rated value	40 A 3 hp
unit UL/CSA ratings full-load current (FLA) for 3-phase AC motor • at 480 V rated value • at 600 V rated value yielded mechanical performance [hp] • for single-phase AC motor	40 A

at 200/208 V rated value	15 hr		
— at 200/208 V rated value	15 hp		
— at 220/230 V rated value	15 hp		
— at 460/480 V rated value	30 hp		
— at 575/600 V rated value	40 hp		
contact rating of auxiliary contacts according to UL	C300 / R300		
Short-circuit protection			
product function short circuit protection	Yes		
design of the short-circuit trip	magnetic		
design of the fuse link			
 for short-circuit protection of the auxiliary switch 	fuse gG: 10 A, miniature circuit breaker C 6 A (short-circuit current lk <		
required	400 A)		
design of the fuse link for IT network for short-circuit protection of the main circuit			
• at 240 V	none required		
• at 240 V	none required 125		
• at 500 V	100		
• at 690 V	80		
Installation/ mounting/ dimensions			
mounting position	any		
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 60715		
hoight	140 mm		
height			
width	55 mm		
depth	149 mm		
required spacing			
 for grounded parts at 400 V 			
— downwards	50 mm		
— upwards	50 mm		
— at the side	10 mm		
 for live parts at 400 V 			
— downwards	50 mm		
— upwards	50 mm		
— at the side	10 mm		
 for grounded parts at 500 V 			
— downwards	50 mm		
— upwards	50 mm		
— at the side	10 mm		
 for live parts at 500 V 			
— downwards	50 mm		
— upwards	50 mm		
— at the side	10 mm		
 for grounded parts at 690 V 			
— downwards	50 mm		
— upwards	50 mm		
— at the side	10 mm		
• for live parts at 690 V			
— downwards	50 mm		
— upwards	50 mm		
— at the side	10 mm		
Connections/ Terminals			
type of electrical connection			
for main current circuit	screw-type terminals		
for auxiliary and control circuit	screw-type terminals		
arrangement of electrical connectors for main current circuit	Top and bottom		
type of connectable conductor cross-sections			
for main contacts			
- solid or stranded	2x (1 25 mm²), 1x (1 35 mm²)		
 — finely stranded with core end processing 	2x (1 25 mm ²), 1x (1 25 mm ²)		
 at AWG cables for main contacts 			
	2x (18 3), 1x (18 2)		
type of connectable conductor cross-sections			

at AWG cables tightening torque for main contac	anded aded with core end proce for auxiliary contacts ts with screw-type termi	nals	2x (0.5 1.5 mm²), 2x (0.75 2x (0.5 1.5 mm²), 2x (0.75 2x (20 16), 2x (18 14) 3 4.5 N⋅m				
 for auxiliary con 	tacts with screw-type te	rminals	0.8 1.2 N·m				
design of screwdrive	er shaft		Diameter 5 to 6 mm				
size of the screwdriv	ver tip		Pozidriv size 2				
design of the thread	of the connection scr	ew					
 for main contact 	ts		M6				
 of the auxiliary a 	and control contacts		M3				
Safety related data							
B10 value							
	nd rate according to SN	31920	5 000				
		51520	3 000				
proportion of dange		4000	50.0/				
	d rate according to SN 3		50 %				
	nd rate according to SN	31920	50 %				
failure rate [FIT]							
	d rate according to SN 3		50 FIT				
T1 value for proof test IEC 61508	t interval or service life a	according to	10 y				
	on the front according	to IEC	IP20				
	touch protection on the front according to IEC 60529			finner onto the forwartical contact from the front			
display version for sw		ing to IEC 60529 finger-safe, for vertical contact from the front Handle Handle					
Certificates/ approval	-		Tandie				
SE CAN	<u>Confirmation</u>			<u>KC</u>	EHC		
For use in hazardou	is locations	Declaration o	f Conformity	Test Certificates			
IECE×	KEX ATEX	CE EG-Konf.		Type Test Certific- ates/Test Report	Special Test Certific- ate		
Marine / Shipping							
ABS	BUREAU VERITAS		Lloyd's Register LRS	PRS	RINA		
Marine / Shipping	other		Railway				
RMRS	<u>Confirmation</u>	VDE	Vibration and Shock	<u>Confirmation</u>			
Further information Information- and Downloadcenter (Catalogs, Brochures,)							

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2031-4UA15

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2031-4UA15

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RV2031-4UA15

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2031-4UA15&lang=en


Characteristic: Tripping characteristics, I²t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RV2031-4UA15/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2031-4UA15&objecttype=14&gridview=view1

144.4





last modified:

6/25/2022 🖸

7/4/2022