## SIEMENS

## Data sheet

## 3RV2311-0DC20




Circuit breaker size S00 for starter combination Rated current 0.32 A N-release 4.2 A Spring-type terminal Standard switching capacity

product brand name	SIRIUS
product designation	Circuit breaker
design of the product	For starter combinations
product type designation	3RV2
General technical data	
size of the circuit-breaker	S00
size of contactor can be combined company-specific	S00, S0
product extension auxiliary switch	Yes
power loss [W] for rated value of the current	
<ul> <li>at AC in hot operating state</li> </ul>	5.5 W
<ul> <li>at AC in hot operating state per pole</li> </ul>	1.8 W
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	25g / 11 ms
mechanical service life (switching cycles)	
<ul> <li>of the main contacts typical</li> </ul>	100 000
<ul> <li>of auxiliary contacts typical</li> </ul>	100 000
electrical endurance (switching cycles) typical	100 000
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	
installation altitude at height above sea level maximum	2 000 m
ambient temperature	
<ul> <li>during operation</li> </ul>	-20 +60 °C
<ul> <li>during storage</li> </ul>	-50 +80 °C
during transport	-50 +80 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
operating voltage	
rated value	20 690 V
<ul> <li>at AC-3 rated value maximum</li> </ul>	690 V
<ul> <li>at AC-3e rated value maximum</li> </ul>	690 V
operating frequency rated value	50 60 Hz
operational current rated value	0.32 A
operational current	
<ul> <li>at AC-3 at 400 V rated value</li> </ul>	0.32 A
<ul> <li>at AC-3e at 400 V rated value</li> </ul>	0.32 A

operating power	
• at AC-3	
— at 230 V rated value	0 kW
— at 400 V rated value	0.1 kW
— at 500 V rated value	0.1 kW
— at 690 V rated value	0.1 kW
• at AC-3e	0.1341
— at 230 V rated value	0 kW
— at 400 V rated value	0.1 kW
— at 500 V rated value	0.1 kW 0.1 kW
— at 690 V rated value	0.1 KVV
<ul> <li>operating frequency</li> <li>at AC-3 maximum</li> </ul>	15 1/h
• at AC-3e maximum	15 1/h
Auxiliary circuit	15 1/11
	0
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
	0
Protective and monitoring functions	
product function	No
ground fault detection	No
phase failure detection	No
breaking capacity maximum short-circuit current (Icu)	100 kA
at AC at 240 V rated value	100 kA
at AC at 400 V rated value	100 kA
at AC at 500 V rated value	100 kA
at AC at 690 V rated value	100 kA
breaking capacity operating short-circuit current (Ics) at AC	
<ul> <li>at 240 V rated value</li> </ul>	100 kA
<ul> <li>at 400 V rated value</li> </ul>	100 kA
• at 500 V rated value	100 kA
• at 690 V rated value	100 kA
response value current of instantaneous short-circuit trip unit	4.2 A
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
<ul> <li>at 480 V rated value</li> </ul>	0.32 A
<ul> <li>at 600 V rated value</li> </ul>	0.32 A
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 60715
height	106 mm
width	45 mm
depth	97 mm
required spacing	
<ul> <li>for grounded parts at 400 V</li> </ul>	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
<ul> <li>for live parts at 400 V</li> </ul>	
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
<ul> <li>for grounded parts at 500 V</li> </ul>	
— downwards	30 mm

— upwards		30 mm		
— at the side		9 mm		
• for live parts at 500 V		9 11111		
- downwards		30 mm		
— upwards		30 mm		
— upwards — at the side		9 mm		
		9 11111		
<ul> <li>for grounded parts at 690 V</li> </ul>		50		
— downwards		50 mm		
— upwards		50 mm		
— backwards		0 mm		
— at the side		30 mm		
— forwards		0 mm		
<ul> <li>for live parts at 690 V</li> </ul>				
— downwards		50 mm		
— upwards		50 mm		
— backwards		0 mm		
— at the side		30 mm		
— forwards		0 mm		
Connections/ Terminals				
type of electrical connection				
for main current circuit		spring-loaded terminals		
arrangement of electrical connectors for ma	in current	Top and bottom		
circuit				
type of connectable conductor cross-sectio	ns			
for main contacts				
— solid or stranded		2x (0,5 4 mm <sup>2</sup> )		
<ul> <li>finely stranded with core end proces</li> </ul>		2x (0.5 2.5 mm <sup>2</sup> )		
<ul> <li>finely stranded without core end pro</li> </ul>	cessing	2x (0.5 2.5 mm²)		
<ul> <li>at AWG cables for main contacts</li> </ul>		2x (20 12)		
design of screwdriver shaft		Diameter 3 mm		
size of the screwdriver tip		3,0 x 0,5 mm		
Safety related data				
B10 value				
<ul> <li>with high demand rate according to SN 3</li> </ul>	1920	5 000		
proportion of dangerous failures				
<ul> <li>with low demand rate according to SN 31920</li> </ul>		50 %		
<ul> <li>with high demand rate according to SN 31920</li> </ul>		50 %		
failure rate [FIT]				
<ul> <li>with low demand rate according to SN 31920</li> </ul>		50 FIT		
T1 value for proof test interval or service life according to		10 y		
IEC 61508				
protection class IP on the front according to	IEC	IP20		
60529	EC 60520	finder cafe, for vertical contr	at from the front	
		finger-safe, for vertical conta Handle		
display version for switching status Certificates/ approvals		папше		
General Product Approval				
	Confirmatio	n 🗢	KC	
(SA) (m)	<u>commute</u>	- (u)	<u></u>	CO <b>r</b>
				ΓΠΙ
CSA CCC		UL		
Declaration of Conformity	Test Certifica	ates	Marine / Shipping	
	Type Test Ce		Star and	
	ates/Test Re	port <u>ate</u>		(1) 法保留
			ARS	
			nua	VERITAS


Subject to change without notice © Copyright Siemens



Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RV2311-0DC20/char Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2311-0DC20&objecttype=14&gridview=view1



last modified:

6/25/2022 🖸