


• General Description

ASPL1117 is a series of low dropout three-terminal regulators with a dropout of 1.3V at 0.9A load current. ASPL1117 features a very low standby current 2mA compared to 5mA of competitor.

Other than a fixed version, Vout = 1.2V, 1.5V, 1.8V, 2.5V, 3.3V and 5.0V, ASPL1117 has an adjustable version, which can provide an output voltage from 1.25 to 5.0V with only two external resistors.

ASPL1117 offers thermal shut down and current limit functions, to assure the stability of chip and power system. And it uses trimming technique to guarantee output voltage accuracy within 2%. Other output voltage accuracy can be customized on demand, such as 1%. ASPL1117 is available in SOT-223, TO-252, SOT-89 power package.



• Features


- Maximum output current is 900mA
- Range of operation input voltage: Max 20V
- ► Line regulation: 0.03%/V (typ.)
- Standby current: 2mA (typ.)
- Load regulation: 0.2%/A (typ.)
- Environment Temperature: $-20^{\circ}C \sim 85^{\circ}C$

• Applications

- > Power Management for STB, Mother Board, Graphic Card
- LCD Monitor and LCD TV
- Appliances and White Goods
- ADSL Modem, WLAN
- Post Regulators For Switching Supplies



• Block Diagram



• Absolute Maximum Rating

8	
Parameter	Value
Max Input Voltage	20V
Max Power Dissipation(Pd)	1.0W
Max Output Current	0.9A
Recommended operating junction temperature(Tj)	-20~125℃
Max Operating Junction Temperature(Tj)	150°C
Ambient Temperature(Ta)	-20°C~85°C
Storage Temperature(Ts)	-40°C ~ 150°C
Lead Temperature & Time	260°C, 10S

Caution: Exceed these limits to damage to the device. Exposure to absolute maximum rating conditions may affect device reliability.

NOV 2021 Version 3.1

2/11



• Electrical Characteristics

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
Vref	Reference	ASPL1117-ADJ	1 225 1		1 275	V
voltage		10mA≤Iout≤0.9A,Vin=3.25V	1.225 1.25		1.275	v
		AUPL1117-1.2	1.176	1.2	1.224	V
		0≤Iout≤0.9A, Vin=3.2V	1.170	1.2	1.224	v
		ASPL1117-1.5	1.470	1.5	1.530	V
		0≤Iout≤0.9A , Vin=3.5V	1.470		1.550	v
		ASPL1117-1.8	1.764	1.8	1.836	V
	Original	0≤Iout≤0.9A, Vin=3.8V	1.701		1.050	•
Vout	Output voltage	ASPL1117-2.5	2.45	2.5	2.55	V
	voltage	0≤Iout≤0.9A, Vin=4.5V				
		ASPL1117-3.3	3.234	3.3	3.366	V
		0≤Iout≤0.9A, Vin=5.3V	5.251	5.5	5.500	•
		ASPL1117-5.0	4.9	5.0	5.1	V
		0≤Iout≤0.9A, Vin=7.0V	,			
		ASPL1117-1.2		0.03	0.2	%/V
		Iout=10mA, 2.7V≤Vin≤10V				
		ASPL1117-ADJ			0.2	%/V
		Iout=10mA,		0.03		
		2.75V≤Vin≤12V				
		ASPL1117-1.5		0.03	0.2	%/V
		Iout=10mA, 3.0V≤Vin≤12V ASPL1117-1.8			├	
ΔVout	Line Regulation	ASPL1117-1.8 Iout=10mA, 3.3V≤Vin≤12V	0.03		0.2	%/V
		ASPL1117-2.5				
		ASFL1117-2.5 Iout=10mA, 4.0V≤Vin≤12V	0.03		0.2	%/V
		ASPL1117-3.3				
		Iout=10mA, 4.8V≤Vin≤12V		0.03	0.2	%/V
		ASPL1117-5.0		0.03	0.2	%/V
		Iout=10mA, 6.5V≤Vin≤12V		0.05	0.2	,0, (
		ASPL1117-1.2 Vin =2.7V, 10mA≤Iout≤0.9A		2	8	mV
	Load regulation	ASPL1117-ADJ			2 8	mV
∆Vout		ASFL1117-ADJ Vin =2.75V, 10mA≤Iout≤0.9A		2		
		ASPL1117-1.5				
		Vin =3.0V, 10mA≤Iout≤0.9A	2.5		10	mV
		ASPL1117-1.8		2	10	mV
		Vin =3.3V, 10mA≤Iout≤0.9A		3	12	mV
		ASPL1117-2.5		4	16	mV
		Vin =4.0V, 10mA≤Iout≤0.9A				
		ASPL1117-3.3		6	24	mV
		Vin =4.8V, 10mA≤Iout≤0.9A		-		
		ASPL1117-5.0 Vin =6.5V, 10mA≤Iout≤0.9A		9	36	mV
		• III 0.5 •, 10IIIA_10ut_0.9A		l		

Vdrop	Dropout voltage	Iout =100mA		1.23	1.3	V
1 -		Iout=0.9A		1.3	1.5	V
Ilimit	Current limit	Vin-Vout=2V;Tj =25°C	0.8	0.9		А
Imin	Minimum	ASPL1117-ADJ	2	2	10	mA
111111	load current	ASFLIII/-ADJ		10	IIIA	
		ASPL1117-1.2,Vin=10V		2	5	mA
		ASPL1117-1.5,Vin=12V		2	5	mA
	Quiescent	ASPL1117-1.8,Vin=12V		2	5	mA
Iq	Current	ASPL1117-2.5,Vin=12V		2	5	mA
	Current	ASPL1117-3.3,Vin=12V		2	5	mA
		ASPL1117-5.0,Vin=12V		2	5	mA
IAdi	Adjust pin	ASPL1117-ADJ	55	120	uA	
IAdj	current	Vin =5.0V, 10mA≤Iout≤0.9A				55
		f=100Hz, Cout=104		65		dB
PSRR	Ripple	f=1KHz, Cout=104		65		dB
PSKK	Regulation	f=10KHz, Cout=104		60		dB
		f=22KHz, Cout=104		57		dB
Lahanaa	Iadj change	ASPL1117-ADJ		0.2	10	
Ichange		Vin =5.0V, 10mA≤Iout≤0.9A	0.2		.2 10	uA
$\Delta V / \Delta T$	Temperature		±100			
	coefficien					ppm
θ_{JC}	Thermal	SOT-223		20		°C/W
	resistance	TO-252 SOT89-3		$10 \\ 8$		C/ w

Note1: All test are conducted under ambient temperature 25 ° Cand within a short period of time 20ms

Note2: Load current smaller than minimum load current of ASPL1117-ADJ will lead to unstable or oscillation output.

• Detailed Description

ASPL1117 is a series of low dropout voltage, three terminal regulators. Its application circuit is very simple: the fixed version only needs two capacitors and the adjustable version only needs two resistors and two capacitors to work. It is composed of some modules including start-up circuit, bias circuit, bandgap, thermal shutdown, current limit, power transistors and its driver circuit and so on.

The thermal shut down modules can assure chip and its application system working safety when the junction temperature is larger than 140 $^{\circ}$ C.


The bandgap module provides stable reference voltage, whose temperature coefficient is compensated by careful design considerations. The temperature coefficient is under 100 ppm/ $^{\circ}$ C. And the accuracy of output voltage is guaranteed by trimming technique.



• Typical Application

ASPL1117 has an adjustable version and six fixed versions (1.2V, 1.5V, 1.8V, 2.5V, 3.3V and 5.0V)


Fixed Output Voltage Version



Application circuit of ASPL1117 fixed version

- 1) Recommend using 10uF tancapacitor as bypass capacitor (C1) for all application circuit.
- 2) Recommend using 10uF tancapacitor to assure circuit stability.

Adjustable Output Voltage Version



Application Circuit of ASPL1117-ADJ

The output voltage of adjustable version follows the equation: Vout= $1.25 \times (1+R2/R1)+IAdj \times R2$. We can ignore IAdj because IAdj (about 50uA) is much less than the current of R1 (about 2~10mA).

1) To meet the minimum load current (>10mA) requirement, R1 is recommended to be 1250hm or lower. As ASPL1117-ADJ can keep itself stable at load current about 2mA, R1 is not allowed to be higher than 6250hm.

2) Using a bypass capacitor (C_{ADJ}) between the ADJ pin and ground can improve ripple rejection. This bypass capacitor prevents ripple from being amplified as the output voltage is increased. The impedance of C_{ADJ} should be less than R1 to prevent ripple from being amplified. As R1 is normally in the range of 100Ω ~500 Ω , the value of C_{ADJ} should satisfy this equation: $1/(2\pi \times \text{fripple} \times C_{ADJ}) < R1$.

• Thermal Considerations

We have to take heat dissipation into great consideration when output current or differential voltage of input and output voltage is large. Because in such cases, the power dissipation consumed by ASPL1117 is very large. ASPL1117 series uses SOT-223 package type and its thermal resistance is about 20 ° C/W. And the copper area




ASPL1117

900mA Bipolar Linear Regulator


of application board can affect the total thermal resistance. If copper area is 5cm*5cm (two sides), the resistance is about $30 \degree \text{C/W}$. So the total thermal resistance is about $20 \degree \text{C/W} + 30 \degree \text{C/W}$. We can decrease total thermal resistance by increasing copper area in application board. When there is no good heat dissipation copper are in PCB, the total thermal resistance will be as high as $120 \degree \text{C/W}$, then the power dissipation of ASPL1117 could allow on itself is less than 1W. And furthermore, ASPL1117 will work at junction temperature higher than $125 \degree \text{C}$ under such condition and no lifetime is guaranteed.

• Typical Performance Characteristics T=25 °C unless specified.




Line Regulation

Dropout Voltage




Load Regulation

ASPL1117-ADJ Vout Vs. Iout



Thermal performance with OTP



ASPL1117-ADJ Dropout Vs. Iout

6/11



• Ordering Information

Ordering Device No.	Package	Packing	Quantity
ASPL1117-XX-DT-R	SOT-223	Tape&Reel	2500/Reel
ASPL1117-XX-KQ-R	TO-252	Tape&Reel	2500/Reel
ASPL1117-XX-DI-R	SOT-89	Tape&Reel	1000/Reel

Note: "xx" stands for output voltages. Example: "1.8"=1.8V, "3.3"=3.3V, "5.0"=5.0V, "ADJ"=Adjustable version, etc.

Note: "DT"=SOT-223, "KQ"=TO-252, "DI"=SOT-89. Note: "R" stands for Packing, Tape&Reel.


P/N example: ASPL1117-1.8-DT-R, ASPL1117-3.3-DT-R, ASPL1117-ADJ-DT-R, etc.







Package Information

SOT-223









Recommended Land Pattern


Symbol	Dimensions in Millimeters		Dimensions in Inches	
Symbol	Min	Max	Min	Max
Α	1.50	1.70	0.059	0.067
A1		0.10		0.004
b	0.60	0.82	0.024	0.032
b1	2.90	3.10	0.114	0.122
С	0.24	0.35	0.009	0.014
D	6.15	6.65	0.242	0.262
E	3.30	3.70	0.130	0.146
е	2.30 TYP		0.091	I TYP
e1	4.50	4.70	0.177	0.185
Н	6.70	7.30	0.264	0.287
L	0.80	1.15	0.031	0.045
θ	0 °	10°	0 n	10°



TO-252







Recommended Land Pattern




Sumbol	Dimensions in Millimeters		Dimensions in Inches	
Symbol	Min	Max	Min	Max
А	2.25	2.65	0.089	0.104
A1	0.00	0.15	0.000	0.006
A2	2.20	2.40	0.087	0.094
b	0.50	0.70	0.020	0.028
b1	0.70	0.90	0.028	0.035
С	0.46	0.66	0.018	0.026
c1	0.46	0.66	0.018	0.026
D	6.30	6.70	0.248	0.264
D1	5.20	5.40	0.205	0.213
E	5.30	5.70	0.209	0.224
E1	1.40	1.60	0.055	0.063
Н	9.40	9.90	0.370	0.390
е	2.30 TYP		0.09 TYP	
L	1.40	1.77	0.055	0.070
L1	0.50	0.70	0.020	0.028
θ	0°	8°	0°	8°





ASPL1117


900mA Bipolar Linear Regulator


SOT-89











Recommended Land Pattern

Symbol	Dimensions in Millimeters		Dimensions in Inches	
Symbol	Min	Max	Min	Max
A	1.30	1.70	0.051	0.067
b	0.40	0.60	0.016	0.024
b1	0.25	0.55	0.010	0.022
С	0.30	0.50	0.012	0.020
D	4.30	4.70	0.169	0.185
D1	1.40	1.80	0.055	0.071
E	2.30	2.70	0.091	0.106
е	1.5TYP		0.059TYP	
e1	2.90	3.10	0.114	0.122
Н	3.90	4.40	0.154	0.173
L	0.80	1.20	0.031	0.047



IMPORTANT NOTICE

ShenZhen Ascend Semiconductor incorporated MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A

PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

ShenZhen Ascend Semiconductor Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. ShenZhen Ascend Semiconductor Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does ShenZhen Ascend Semiconductor Incorporated convey any license under its patent or trademark rights,

nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume .

all risks of such use and will agree to hold Ascendsemi Incorporated and all the companies whose products are represented on ShenZhen Ascend Semiconductor Incorporated website, harmless against all damages.

ShenZhen Ascend Semiconductor Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use ShenZhen Ascend Semiconductor Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold ShenZhen Ascend Semiconductor Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

www.ascendsemi.com