SIEMENS

Data sheet

3SU1802-0AC10-4HB1



AS-Interface enclosure for command devices, 22 mm, round, Enclosure material plastic, enclosure top part gray, 2 control points plastic, Recess for labels, B=Pushbutton white, label: I, 1 NO, spring-type terminal, A=Pushbutton black label: O 1 NC, spring-type terminal, floor mounting, Insulation displacement system on top, Labels enclosed

product brand name	SIRIUS ACT		
product designation	Enclosures		
product type designation	3SU1		
equipment of commanding and signaling device	A = Pushbutton / B = Pushbutton		
manufacturer's article number			
 of supplied contact module 	A1 = 3SU1400-2AA10-3CA0 / B2 = 3SU1400-2AA10-3BA0		
 of supplied contact module at the command point A 1 	<u>3SU1400-2AA10-3CA0</u>		
 of supplied contact module at the command point B 2 	<u>3SU1400-2AA10-3BA0</u>		
 of supplied communication module 	AB = 3SU1400-2EK10-6AA0		
 of the supplied holder 	A = 3SU1500-0AA10-0AA0, B = 3SU1500-0AA10-0AA0		
 of the supplied holder at the command point A 	<u>3SU1500-0AA10-0AA0</u>		
 of the supplied holder at the command point B 	<u>3SU1500-0AA10-0AA0</u>		
 of the supplied actuator 	A = 3SU1000-0AB10-0AA0 / B = 3SU1000-0AB60-0AA0		
 of the supplied actuator at the command point A 	<u>3SU1000-0AB10-0AA0</u>		
 of the supplied actuator at the command point B 	<u>3SU1000-0AB60-0AA0</u>		
 of supplied empty enclosure 	<u>3SU1802-0AA00-0AB1</u>		
 of supplied accessory 	A = 3SU1900-0AF16-0QA0, B = 3SU1900-0AF16-0QB0		
 of the supplied accessories at the command point A 	<u>3SU1900-0AF16-0QA0</u>		
 of the supplied accessories at the command point B 	<u>3SU1900-0AF16-0QB0</u>		
Enclosure			
design of the housing	with recess for label		
shape of the enclosure front	rectangular		
material of the enclosure	plastic		
number of command points	2		
product component			
 EMERGENCY STOP device 	No		
 protective collar 	No		
color of the enclosure top part	grey		
delivery state			
● as a kit	No		
 pre-wired on strip terminal 	Yes		
fastening method of the enclosure	Vertical		
Actuator			
design of the actuating element	Pushbutton / pushbutton		
suitability for use EMERGENCY OFF switch	No		
product feature lockout	No		
product extension optional light source	No		
color of the actuating element	A = black / B = white		

material of the actuating element	plastic
shape of the actuating element	round
number of contact modules	2
type of unlocking device	A = none / B = none
Front ring	
product component front ring	Yes
design of the front ring	Standard
material of the front ring	plastic
color of the front ring	black
Holder	
material of the holder	Plastic
Display	
number of LED modules	0
General technical data	
product function	
 positive opening 	Yes
 EMERGENCY OFF function 	No
EMERGENCY STOP function	No
protection class IP	IP66, IP67, IP69(IP69K)
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12K, 13
shock resistance	
 according to IEC 60068-2-27 	sinusoidal half-wave 15g / 11 ms
 for railway applications according to EN 61373 	Category 1, Class B
vibration resistance	
 according to IEC 60068-2-6 	10 500 Hz: 5g
 for railway applications according to EN 61373 	Category 1, Class B
reference code according to IEC 81346-2	S
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A
continuous current of the DIAZED fuse link gG	10 A
Substance Prohibitance (Date)	10/01/2014
operating voltage	
• at AC	
— at 50 Hz rated value	18 31.6 V
— at 60 Hz rated value	18 31.6 V
at DC rated value	18 31.6 V
cable entry type	Adapter ASI shaped cable (insulation displacement method) M20 cable
0	entry
Communication/ Protocol	40.1
design of the interface for communication	AS-i
type of electrical connection of the communication interface	Insulation piercing technology top/right
Auxiliary circuit	
	Silver allow
design of the contact of auxiliary contacts	Silver alloy 1
number of NC contacts for auxiliary contacts number of NO contacts for auxiliary contacts	1
-	
Connections/ Terminals	
type of electrical connection of modules and accessories	Spring-type terminal
type of electrical connection on enclosure	Adapter ASI shaped cable (insulation displacement method)
tightening torque of the screws in the bracket	1 1.2 N·m
tightening torque of fixing screws in the enclosure cover	1.5 1.7 N·m
Ambient conditions	
ambient temperature	
	-25 +70 °C
during operation	-25 +70 C
• during storage environmental category during operation according to IEC	
60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95%, no condensation in operation permitted for all devices behind front panel)
Installation/ mounting/ dimensions	
fastening method of modules and accessories	Floor mounting

height		134.4 mm			
width		85 mm			
depth		75 mm			
shape of the installation opening		round			
Accessories					
number of labels		2			
marking of the name plate for command devices		A = O / B = I			
color of the label					
number of inscription plates	number of inscription plates 0				
Certificates/ approvals					
General Product Approval					
	<u>Confirmatio</u>		VDE	EHC	
Declaration of Conformity	Confirmation		OTHER OTHER	EHC	

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1802-0AC10-4HB1


Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1802-0AC10-4HB1

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SU1802-0AC10-4HB1

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1802-0AC10-4HB1&lang=en



last modified:

1/26/2022 🖸