## SIEMENS

## Data sheet

## 3RV2321-1GC10



Circuit breaker size S0 for starter combination Rated current 6.3 A N-release 82 A screw terminal Standard switching capacity

product brand name	SIRIUS			
product designation	Circuit breaker			
design of the product	For starter combinations			
product type designation	3RV2			
General technical data				
size of the circuit-breaker	SO			
size of contactor can be combined company-specific				
product extension auxiliary switch	Yes			
power loss [W] for rated value of the current				
<ul> <li>at AC in hot operating state</li> </ul>	7.25 W			
<ul> <li>at AC in hot operating state per pole</li> </ul>	2.4 W			
insulation voltage with degree of pollution 3 at AC rated value	690 V			
surge voltage resistance rated value	6 kV			
shock resistance according to IEC 60068-2-27	25g / 11 ms			
mechanical service life (switching cycles)				
<ul> <li>of the main contacts typical</li> </ul>	100 000			
<ul> <li>of auxiliary contacts typical</li> </ul>	100 000			
electrical endurance (switching cycles) typical	100 000			
reference code according to IEC 81346-2	Q			
Substance Prohibitance (Date)	10/01/2009			
Ambient conditions				
installation altitude at height above sea level maximum	2 000 m			
ambient temperature				
<ul> <li>during operation</li> </ul>	-20 +60 °C			
<ul> <li>during storage</li> </ul>	-50 +80 °C			
<ul> <li>during transport</li> </ul>	-50 +80 °C			
relative humidity during operation	10 95 %			
Main circuit				
number of poles for main current circuit	3			
operating voltage				
<ul> <li>rated value</li> </ul>	20 690 V			
<ul> <li>at AC-3 rated value maximum</li> </ul>	690 V			
at AC-3e rated value maximum	690 V			
operating frequency rated value	50 60 Hz			
operational current rated value	6.3 A			
operational current				
<ul> <li>at AC-3 at 400 V rated value</li> </ul>	6.3 A			
<ul> <li>at AC-3e at 400 V rated value</li> </ul>	6.3 A			

operating power	
• at AC-3	
— at 230 V rated value	1.5 kW
— at 400 V rated value	2.2 kW
— at 500 V rated value	3 kW
— at 690 V rated value	4 kW
• at AC-3e	
— at 230 V rated value	1.5 kW
— at 400 V rated value	2.2 kW
— at 500 V rated value	3 kW
— at 690 V rated value	4 kW
operating frequency	
<ul> <li>at AC-3 maximum</li> </ul>	15 1/h
<ul> <li>at AC-3e maximum</li> </ul>	15 1/h
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
Protective and monitoring functions	
product function	
ground fault detection	No
phase failure detection	No
breaking capacity maximum short-circuit current (lcu)	
at AC at 240 V rated value	100 kA
at AC at 400 V rated value	100 kA
• at AC at 500 V rated value	100 kA
at AC at 690 V rated value	6 kA
breaking capacity operating short-circuit current (lcs)	
at AC	
<ul> <li>at 240 V rated value</li> </ul>	100 kA
<ul> <li>at 400 V rated value</li> </ul>	100 kA
<ul> <li>at 500 V rated value</li> </ul>	100 kA
• at 690 V rated value	4 kA
response value current of instantaneous short-circuit trip	82 A
unit UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor <ul> <li>at 480 V rated value</li> </ul>	6.3 A
at 600 V rated value	6.3 A
yielded mechanical performance [hp]	
for single-phase AC motor	0.05 hz
— at 110/120 V rated value	0.25 hp
— at 230 V rated value	0.5 hp
for 3-phase AC motor	
— at 200/208 V rated value	1 hp
— at 220/230 V rated value	1.5 hp
— at 460/480 V rated value	3 hp
— at 575/600 V rated value	5 hp
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 60715
height	97 mm
width	45 mm
depth	97 mm
required spacing	
<ul> <li>for grounded parts at 400 V</li> </ul>	

T1 value for proof test interval or service life according to IEC 61508         protection class IP on the front according to IEC 60529         touch protection on the front according to IEC 60529         display version for switching status         Certificates/ approvals	IP20 finger-safe, for vertical contact from the front Handle
IEC 61508         protection class IP on the front according to IEC         60529         touch protection on the front according to IEC 60529         display version for switching status	finger-safe, for vertical contact from the front
IEC 61508 protection class IP on the front according to IEC 60529 touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front
IEC 61508 protection class IP on the front according to IEC 60529	
IEC 61508 protection class IP on the front according to IEC	IP20
	10 у
with low demand rate according to SN 31920	50 FIT
failure rate [FIT]	
with high demand rate according to SN 31920	50 %
<ul> <li>with low demand rate according to SN 31920</li> </ul>	50 %
proportion of dangerous failures	
with high demand rate according to SN 31920	5 000
B10 value	
Safety related data	
• for main contacts	M4
design of the thread of the connection screw	
size of the screwdriver tip	Pozidriv size 2
design of screwdriver shaft	Diameter 5 to 6 mm
<ul> <li>for main contacts with screw-type terminals</li> </ul>	2 2.5 N·m
tightening torque	
at AWG cables for main contacts	2x (16 12), 2x (14 8)
— finely stranded with core end processing	2x (1 2.5 mm <sup>2</sup> ), 2x (2.5 6 mm <sup>2</sup> ), 1x 10 mm <sup>2</sup>
— solid or stranded	2x (1 2.5 mm²), 2x (2.5 10 mm²)
for main contacts	
type of connectable conductor cross-sections	
arrangement of electrical connectors for main current circuit	Top and bottom
for main current circuit	screw-type terminals
type of electrical connection	
Connections/ Terminals	
— forwards	0 mm
— at the side	30 mm
— backwards	0 mm
— upwards	50 mm
— downwards	50 mm
• for live parts at 690 V	
— forwards	0 mm
— at the side	30 mm
— backwards	0 mm
— upwards	50 mm
— downwards	50 mm
• for grounded parts at 690 V	
— at the side	9 mm
— upwards	30 mm
— downwards	30 mm
• for live parts at 500 V	
— at the side	9 mm
— upwards	30 mm
— downwards	30 mm
<ul> <li>for grounded parts at 500 V</li> </ul>	
— at the side	9 mm
— upwards	30 mm
- downwards	30 mm
<ul> <li>for live parts at 400 V</li> </ul>	
— at the side	9 mm
— upwards	30 mm
— downwards	30 mm

(SP)	<u>Confirmation</u>	CCC	(UL) II	<u>KC</u>	EHC		
Declaration of Con	formity	Test Certificates		Marine / Shipping			
	CE EG-Konf.	<u>Type Test Certific-</u> ates/Test Report	<u>Special Test Certific-</u> <u>ate</u>	ABS	BUREAU VERITAS		
Marine / Shipping					other		
	Lloyds Register urs	PRS	RINA	RMRS	<u>Confirmation</u>		
other	Railway						
UDE VDE	<u>Confirmation</u>	Vibration and Shock					
Further information	oursia a de anten (Catala						
Information- and Downloadcenter (Catalogs, Brochures,) https://www.siemens.com/ic10 Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2321-1GC10 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2321-1GC10 Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/ww/en/ps/3RV2321-1GC10 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2321-1GC10⟨=en Characteristic: Tripping characteristics, I <sup>2</sup> t, Let-through current https://support.industry.siemens.com/cs/ww/en/ps/3RV2321-1GC10/char Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2321-1GC10&objecttype=14&gridview=view1							
last modified: 6/25/2022 C							

0/20/2022