SIEMENS

Data sheet 3RV2311-1JC10



Circuit breaker size S00 for starter combination Rated current 10 A N release 130 A screw terminal Standard switching capacity

product brand name SIR	IUS
product designation Circ	uit breaker
design of the product For	starter combinations
product type designation 3RV	/2
General technical data	
size of the circuit-breaker S00	
size of contactor can be combined company-specific S00	, S0
product extension auxiliary switch Yes	
power loss [W] for rated value of the current	
• at AC in hot operating state 9.25	5 W
• at AC in hot operating state per pole 3.1	W
insulation voltage with degree of pollution 3 at AC rated value 690	V
surge voltage resistance rated value 6 kV	
shock resistance according to IEC 60068-2-27 25g	/ 11 ms
mechanical service life (switching cycles)	
• of the main contacts typical 100	000
• of auxiliary contacts typical 100	000
electrical endurance (switching cycles) typical 100	000
reference code according to IEC 81346-2 Q	
Substance Prohibitance (Date) 10/0	01/2009
Ambient conditions	
installation altitude at height above sea level maximum 2 00	00 m
ambient temperature	
• during operation -20	+60 °C
• during storage -50	+80 °C
• during transport -50	+80 °C
relative humidity during operation 10 .	95 %
Main circuit	
number of poles for main current circuit 3	
operating voltage	
• rated value 20 .	690 V
• at AC-3 rated value maximum 690	V
• at AC-3e rated value maximum 690	V
operating frequency rated value 50 .	60 Hz
operational current rated value 10 A	4
operational current	
• at AC-3 at 400 V rated value	A

operating power	
• at AC-3	
— at 230 V rated value	2.2 kW
— at 400 V rated value	4 kW
— at 500 V rated value	5.5 kW
— at 690 V rated value	7.5 kW
• at AC-3e	
— at 230 V rated value	2.2 kW
— at 400 V rated value	4 kW
— at 500 V rated value	5.5 kW
— at 690 V rated value	7.5 kW
operating frequency	
• at AC-3 maximum	15 1/h
at AC-3e maximum	15 1/h
Auxiliary circuit	
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	0
number of CO contacts for auxiliary contacts	0
Protective and monitoring functions	
product function	
 ground fault detection 	No
phase failure detection	No
breaking capacity maximum short-circuit current (Icu)	
 at AC at 240 V rated value 	100 kA
 at AC at 400 V rated value 	100 kA
 at AC at 500 V rated value 	42 kA
at AC at 690 V rated value	6 kA
breaking capacity operating short-circuit current (Ics)	
at AC	400 l-A
at 240 V rated value	100 kA
• at 400 V rated value	100 kA
at 500 V rated value	42 kA
at 690 V rated value	4 kA
response value current of instantaneous short-circuit trip unit	130 A
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
 at 480 V rated value 	10 A
at 600 V rated value	10 A
yielded mechanical performance [hp]	
 for single-phase AC motor 	
 — at 110/120 V rated value 	0.5 hp
— at 230 V rated value	1.5 hp
 for 3-phase AC motor 	
— at 200/208 V rated value	2 hp
— at 220/230 V rated value	3 hp
— at 460/480 V rated value	5 hp
— at 575/600 V rated value	10 hp
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
design of the fuse link for IT network for short-circuit protection of the main circuit	
● at 400 V	gL/gG 50 A
● at 500 V	gL/gG 40 A
● at 690 V	gL/gG 40 A
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 60715

height	97 mm
width	45 mm
depth	97 mm
required spacing	97 111111
for grounded parts at 400 V— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
• for live parts at 400 V	9 111111
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
for grounded parts at 500 V	9 111111
— downwards	30 mm
— upwards	30 mm
— at the side	9 mm
for live parts at 500 V	9 111111
— downwards	30 mm
— upwards — upwards	30 mm
— upwards — at the side	9 mm
	7 111111
for grounded parts at 690 V— downwards	50 mm
	50 mm
— upwards — backwards	0 mm
	30 mm
— at the side — forwards	0 mm
for live parts at 690 V	O IIIIII
·	50 mm
— downwards	50 mm
— upwards — backwards	0 mm
— at the side	30 mm
— at the side — forwards	0 mm
Connections/ Terminals	Ollilli
type of electrical connection	
for main current circuit	screw-type terminals
arrangement of electrical connectors for main current circuit	Top and bottom
type of connectable conductor cross-sections	
• for main contacts	
— solid or stranded	2x (0,75 2,5 mm²), 2x 4 mm²
finely stranded with core end processing	2x (0.5 1.5 mm²), 2x (0.75 2.5 mm²)
at AWG cables for main contacts	2x (18 14), 2x 12
tightening torque	
for main contacts with screw-type terminals	0.8 1.2 N·m
design of screwdriver shaft	Diameter 5 to 6 mm
size of the screwdriver tip	Pozidriv size 2
design of the thread of the connection screw	
for main contacts	M3
Safety related data	
B10 value	
with high demand rate according to SN 31920	5 000
proportion of dangerous failures	
with low demand rate according to SN 31920	50 %
with high demand rate according to SN 31920	50 %
failure rate [FIT]	
with low demand rate according to SN 31920	50 FIT
T1 value for proof test interval or service life according to	10 y
IEC 61508	
protection class IP on the front according to IEC	IP20
	IP20 finger-safe, for vertical contact from the front

Handle

Certificates/ approvals

General Product Approval



Confirmation





<u>KC</u>



Declaration of Conformity

Test Certificates

Marine / Shipping



Special Test Certificate

Type Test Certificates/Test Report





Marine / Shipping











Confirmation

other

other

Railway



Confirmation

Vibration and Shock

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RV2311-1JC10

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RV2311-1JC10

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RV2311-1JC10

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RV2311-1JC10&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RV2311-1JC10/char

Further characteristics (e.g. electrical endurance, switching frequency)
http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RV2311-1JC10&objecttype=14&gridview=view1

last modified:

6/25/2022

