

#### > Features

- Size 0.18\*0.12 inch /4.5\*3.2 mm
- RoHS compliant, lead-free and halogen-free
- Fast response to fault current
- Low resistance
- Low profile
- Compatible with high temperature solders

#### Applications

- Computer, Mobile phones, Multimedia
- Automotive, Industrial controls, Telephony and broadband
- Game machines, Portable electronics, Battery

#### ➤ Electrical Characteristics (25°C)

Part Number	$\mathbf{I}_{hold}$	$\mathbf{I}_{trip}$	V <sub>max</sub>	$\mathbf{I}_{max}$	P <sub>d typ</sub>	Time to trip		R <sub>min</sub>	R <sub>1max</sub>
Part Number	(A)	(A)	(V <sub>dc</sub> )	(A)	(W)	(A)	(Sec)	(Ω)	(Ω)
BSMD1812L-600-12V	6.00	12.0	12	50	2.0	20.00	5.00	0.0008	0.010

### Vocabulary

**I**hold = Hold current: maximum current device will pass without tripping in 25°C still air.

**I**<sub>trip</sub> = Trip current: minimum current at which the device will trip in 25°C still air.

 $V_{max}$  = Maximum voltage device can withstand without damage at rated current ( $I_{max}$ ).

 $I_{max}$  = Maximum fault current device can withstand without damage at rated voltage  $(V_{max})$ .

 $P_{d typ.}$  = Typical power dissipated from device when in the tripped state at 25°C still air.

 $R_{min}$  = Minimum resistance of device in initial (un-soldered) state.

**R**<sub>1max</sub> = Maximum resistance of device at 25°C measured one hour after tripping or reflow soldering of 260°C for 20 sec.


Caution: Operation beyond the specified ratings may result in damage and possible arcing and flame.



### Warning

- Users shall independently assess the suitability of these devices for each of their applications.
- Operation of these devices beyond the stated maximum ratings could result in damage to the devices and lead to electrical arcing and/or fire.
- These devices are intended to protect against the effects of temporary over-current or over-temperature conditions and are not intended to perform as protective devices where such conditions are expected to be repetitive or prolonged in duration.
- Exposure to silicon-based oils, solvents, electrolytes, acids, and similar materials can adversely affect the prolonged of these PPTC devices.
- These devices undergo thermal expansion under fault conditions, and thus shall be provided with adequate space and be protected against mechanical stresses.
- Circuits with inductance may generate a voltage (L di/dt) above the rated voltage of the PPTC device.

### > Thermal Derating Curve






## > Thermal Derating Chart

Part Number	Ambient operating temperature hold current(I <sub>hold</sub> )								
r art Number	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
BSMD1812L-600-12V	9.0	8.0	7.0	6.0	5.2	4.6	4.2	3.7	3.1

## > Environmental Specifications

Test	Conditions	Resistance change			
Passive aging	+85°C, 1000 hrs.	±5% typical			
Humidity aging	+85°C, 85% R.H., 168 hours	±5% typical			
Thermal shock	+85°C to -40°C, 20 times	±33% typical			
Resistance to solvent	MIL-STD-202, Method 215	No change			
Vibration	MIL-STD-202, Method 201	No change			
Ambient operating conditions: - 40 °C to +85 °C					
Maximum surface temperature of the device in the tripped state is 125 °C					

# ➤ Soldering Parameters






Profile Feature	Pb-Free Assembly			
Average Ramp-Up Rate(Ts <sub>max</sub> to T <sub>p</sub> )	3°C/second max			
Preheat				
-Temperature Min(Ts <sub>min</sub> )	150°C			
-Temperature Max(Ts <sub>max</sub> )	200°C			
-Time(Ts <sub>min</sub> to Ts <sub>max</sub> )	60~180 seconds			
Time maintained above:				
-Temperature(T <sub>L</sub> )	217°C			
-Time(t <sub>L</sub> )	60~150 seconds			
Peak Temperature(T <sub>p</sub> )	260°C			
Ramp-Down Rate	6°C/second max			
Time 25°C to Peak Temperature	8 minutes max			
Storage Condition	0°C~30°C,30%-60%RH			


- Recommended reflow methods: IR, vapor phase oven, hot air oven, N<sub>2</sub> environment for lead-free.
- Recommended maximum paste thickness is 0.25mm.
- Devices can be cleaned using standard industry methods and solvents.

**Note 1:** All temperature refer to topside of the package, measured on the package body surface.

**Note 2:** If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

### Physical Dimensions & Recommended Pad Layout (mm)






Dart Number	Marking	Quantity	А		В		С		D	Е
Part Number			Min	Max	Min	Max	Min	Max	Min	Min
BSMD1812L-600-12V		1500	4.37	4.73	3.07	3.41	0.50	1.10	0.30	0.25




# ➤ Tape And Reel Specifications (mm)



Governing Specifications	BSMD1812-600-12V
W	$12.0 \pm 0.3$
F	$5.5 \pm 0.05$
E <sub>1</sub>	1.75 ± 0.1
$D_0$	1.55 ± 0.05
$D_1$	1.55 <sub>min</sub>
P <sub>0</sub>	$4.0 \pm 0.1$
$P_1$	$8.0 \pm 0.1$
P <sub>2</sub>	$2.0 \pm 0.05$
$A_0$	$3.58 \pm 0.1$
B <sub>0</sub>	$4.93 \pm 0.1$
Т	$0.2 \pm 0.1$
K <sub>0</sub>	1.25 ± 0.1
Leader <sub>min</sub>	390
Trailer <sub>min</sub>	160

Reel Dimensions					
С	φ178 ± 1.0				
D	$\phi 60.2 \pm 0.5$				
Н	$16.0 \pm 0.5$				
W	13.2 ± 1.5				



### > Contact information

SHENZHEN BHFUSE INDUSTRIAL CO., LTD

TEL: 0755-85259917

E-MAIL: sales@bhfuse.com