

- ★ Green Device Available
- ★ Super Low Gate Charge
- ★ Excellent CdV/dt effect decline
- ★ Advanced high cell density Trench technology

Product Summary

RoHS


BVDSS	RDS(on)	ID
20V	43mΩ	3.0A

Description

The 2302V is the high cell density trenched N-ch MOSFETs, which provide excellent RDS(on) and efficiency for most of the small power switching and load switch applications.

The 2302V meet the RoHS and Green Product requirement with full function reliability approved.

SOT23 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	20	V
V_{GS}	Gate-Source Voltage	± 12	V
$I_D @ T_A = 25^\circ C$	Continuous Drain Current, $V_{GS} @ 10V^1$	3	A
$I_D @ T_A = 70^\circ C$	Continuous Drain Current, $V_{GS} @ 10V^1$	1.2	A
I_{DM}	Pulsed Drain Current ²	12	A
$P_D @ T_A = 25^\circ C$	Total Power Dissipation ³	0.85	W
T_{STG}	Storage Temperature Range	-55 to 150	°C
T_J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	---	162	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	---	°C/W

Electrical Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Test condition	Min.	Typ.	Max.	Units
Off Characteristic						
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0\text{V}, I_D=250\mu\text{A}$	20	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=20\text{V}, V_{GS}=0\text{V},$	-	-	1	μA
I_{GSS}	Gate to Body Leakage Current	$V_{DS}=0\text{V}, V_{GS}=\pm 12\text{V}$	-	-	± 100	nA
On Characteristics						
$V_{GS(\text{th})}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu\text{A}$	0.4	0.7	1	V
$R_{DS(\text{on})}$ note ₂	Static Drain-Source on-Resistance	$V_{GS}=4.5\text{V}, I_D=3\text{A}$	-	45	55	$\text{m}\Omega$
		$V_{GS}=2.5\text{V}, I_D=2\text{A}$	-	62	85	
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{DS}=10\text{V}, V_{GS}=0\text{V}, f=1.0\text{MHz}$	-	184	-	pF
C_{oss}	Output Capacitance		-	38	-	pF
C_{rss}	Reverse Transfer Capacitance		-	28	-	pF
Q_g	Total Gate Charge	$V_{DS}=10\text{V}, I_D=3\text{A}, V_{GS}=4.5\text{V}$	-	2.7	-	nC
Q_{gs}	Gate-Source Charge		-	0.4	-	nC
Q_{gd}	Gate-Drain("Miller") Charge		-	0.5	-	nC
Switching Characteristics						
$t_{d(on)}$	Turn-on Delay Time	$V_{DS}=10\text{V}, I_D=3\text{A}, R_{GEN}=3\Omega, V_{GS}=4.5\text{V}$	-	8	-	ns
t_r	Turn-on Rise Time		-	27	-	ns
$t_{d(off)}$	Turn-off Delay Time		-	26	-	ns
t_f	Turn-off Fall Time		-	33	-	ns
Drain-Source Diode Characteristics and Maximum Ratings						
I_s	Maximum Continuous Drain to Source Diode Forward Current	-	-	3	-	A
I_{SM}	Maximum Pulsed Drain to Source Diode Forward Current	-	-	12	-	A
V_{SD}	Drain to Source Diode Forward Voltage	$V_{GS}=0\text{V}, I_s=3\text{A}$	-	-	1.2	V

Note :

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. Pulse Test: Pulse Width $\leqslant 300\mu\text{s}$, Duty Cycle $\leqslant 0.5\%$

Typical Performance Characteristics

Figure 1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 5: Gate Charge Characteristics




Figure 4: Body Diode Characteristics





Figure 6: Capacitance Characteristics



Typical Performance Characteristics

Figure 7: Normalized Breakdown Voltage




Figure 8: Normalized on Resistance vs. Junction Temperature (Tj)




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Ambient Temperature (TA)






Figure 11: Maximum Effective Transient Thermal Resistance (Z_{thJA})



SOT23 Mechanical tData



DIMENSIONS (unit : mm)

Symbol	Min	Typ	Max	Symbol	Min	Typ	Max
A	0.9	1.01	1.15	A ₁	0.01	0.05	0.1
b _p	0.3	0.42	0.5	c	0.08	0.13	0.15
D	2.8	2.92	3	E	1.2	1.33	1.4
e	--	1.9	--	e ₁	--	0.95	--
H _E	2.25	2.4	2.55	L _p	0.3	0.42	0.5
Q	0.45	0.49	0.55	v	--	0.2	--
w	--	0.1	--				