




REV	LOCAS	DESCRIPTION	DRAW	DATE
A0	NEW	PERLIMINARY	Long	2018.04.06

**SPECIFICATIONS**

- 1、 Current Rating:2A
- 2、 Voltage Rating:100V
- 3、 Temperature Range:-25°C~+85°C
- 4、 Contact Resistance:20mΩ Max
- 5、 Insulation Resistance:1000MΩ Min
- 6、 Withstanding Voltang:800V AC/minute
- 7、 Material & Finish:  
Housing:LCP, UL94 V-0  
PIN:Brass, Plated Tin  
Nail:Brass, Plated Tin



**Ordering Information**

P:Pin Header Series  
A:Finished Product  
No.of PINS  
Plating Number  
200:Pitch 2.00mm  
520:Height 5.20mm

P A XX 12 200 520- 92 S M S

S:SMT TYPE  
D:DIP TYPE  
M:Male(排针)  
F:Female(排母)  
S:Single(单排)  
D:Double(双排)  
Running number

**RECOMMEND P.C.B LAYOUT**  
PCB TOLERANCE:±0.05 (TOP VIEW)

Circuits	Dimensions mm	
	A	B
02	2.00	8.00
03	4.00	10.00
04	6.00	12.00
05	8.00	14.00
06	10.00	16.00
07	12.00	18.00
08	14.00	20.00
09	16.00	22.00
10	18.00	24.00
11	20.00	26.00
12	22.00	28.00
13	24.00	30.00
14	26.00	32.00
15	28.00	34.00
16	30.00	36.00
17	32.00	38.00
18	34.00	40.00
19	36.00	42.00
20	38.00	44.00

MEASURE POINT:  
QUADRANT POINT (Ⓢ)  
TANGENCY POINT (Ⓣ)  
INTERSECTION POINT (Ⓟ)  
UNLESS OTHERWISE SPECIFIED, TOLERANCE:  
X: ±0.25  
XX: ±0.20  
XXX: ±0.15  
ANGULAR: ±5°



**DONG GUAN D-CHAIN TECHNOLOGY CO.,LTD**

DRAWN	Long	DATE	2018.04.06	TITLE:	Pitch2.0 Water SMT TYPE
CHECKED		DATE			
APPROVED		DATE			
PART No.	PAXX12200520-92SMS	REV:	A0	SCALE:	1:1
DRAWING No.		SIZE:	A4	SHEET:	1/1
		UNIT:			mm