






REV	LOKAS	DESCRIPTION	DRAW	DATE
AO	NEW	PERLIMINARY	Andy	2022.09.22

- NOTES:
- Material:
    - 1.1 Housing/Cap: LCP.
    - 1.2 Terminal/Noil: Brass.
  - Finish:
    - Terminal/Noil: Plated Tin.
  - Specification:
    - 3.1 Current Rating: 1A
    - 3.2 Voltage Rating: 100V
    - 3.3 Insulation Resistance: 100MΩ MIN.
    - 3.4 Dielectric withstanding voltage: 500V AC for one minute.
    - 3.5 Contact resistance: 40m Max.
    - 3.6 Operating Temperature: -25°C~+85°C;



CKT	DimA	DimB	DimC	DimD
2	1.25	3.25	7.50	7.50
3	2.50	4.50	8.75	8.75
4	3.75	5.75	10.00	10.00
5	5.00	7.00	11.25	11.25
6	6.25	8.25	12.50	12.50
7	7.50	9.50	13.75	13.75
8	8.75	10.75	15.00	15.00
9	10.00	12.00	16.25	16.25
10	11.25	13.25	17.50	17.50
11	12.50	14.50	18.75	18.75
12	13.75	15.75	20.00	20.00
13	15.00	17.00	21.25	21.25
14	16.25	18.25	22.50	22.50
15	17.50	19.50	23.75	23.75
16	18.75	20.75	25.00	25.00
17	20.00	22.00	26.25	26.25
18	21.25	23.25	27.50	27.50
19	22.50	24.50	28.75	28.75
20	23.75	25.75	30.00	30.00

Ordering Information  
 P A XX 12 125 470 -334-XX-S M S  
 P: Pin Header Series  
 A: Finished Product  
 No. of PINS:  
 Plating Number:  
 125: Pitch 1.25mm  
 470: Height 4.70mm  
 Running number


XX: Colour  
 01: nature (本色)  
 02: Black (黑色)  
 03: Blue (蓝色)

S: Single  
 D: Double

F: Female  
 M: Male

L: S: SMT TYPE  
 D: DIP TYPE

RECOMMENDED PCB LAYOUT  
 GENERAL TOLERANCE ±0.05



MEASURE POINT:  
 QUADRANT POINT  
 TANGENCY POINT  
 INTERSECTION POINT

UNLESS OTHERWISE SPECIFIED, TOLERANCE:  
 X ±0.25  
 XX ±0.20  
 XXX ±0.15  
 ANGULAR ±5°

**D-CHAIN**

**DONG GUAN D-CHAIN TECHNOLOGY CO., LTD**

DRAWN	Andy	DATE	2022.06.22
CHECKED		DATE	
APPROVED		DATE	

PART No. PAXX12125470-334-XXSMS  
 REV: AO  
 DRAWING No. SIZE: A4 SHEET: 1/1

TITLE: Pitch 1.25 Wafer Row SMT

UNIT: mm