


# HER201~HER208

## 2.0Amp High Efficiency Silicon Rectifiers

### Features

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- Low reverse leakage
- High forward surge current capability
- High temperature soldering guaranteed  
260°C/10 seconds at terminals

### DO-15



Dimensions in inches and (millimeters)

### Mechanical Data

- Case :** Molded plastic body  
**Terminals :** Solder plated, solderable per MIL-STD-750, Method 2026  
**Polarity :** Polarity symbol marking on body  
**Mounting Position :** Any  
**Weight :** 0.0116 ounce, 0.33 grams

### Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	HER 201	HER 202	HER 203	HER 204	HER 205	HER 206	HER 207	HER 208	UNITS	
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	300	400	600	800	1000	V	
Maximum RMS voltage	$V_{RMS}$	35	70	140	210	280	420	560	700	V	
Maximum DC blocking voltage	$V_{DC}$	50	100	200	300	400	600	800	1000	V	
Maximum average forward rectified current at $T_L=100^\circ C$	$I_{(AV)}$	2.0								A	
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	$I_{FSM}$	60.0								A	
Maximum instantaneous forward voltage at 2.0A	$V_F$	1.0			1.4		1.7			V	
Maximum DC reverse current $T_A=25^\circ C$ at rated DC blocking voltage $T_A=125^\circ C$	$I_R$	10.0 500								$\mu A$	
Maximum reverse recovery time (Note 1)	$T_{rr}$	50					75				ns
Typical junction capacitance (Note 2)	$C_J$	50.0								pF	
Typical thermal resistance	$R_{qJA}$	75.0								$^\circ C/W$	
Operating junction and storage temperature range	$T_J, T_{STG}$	-55 to +150								$^\circ C$	

**Note:** 1. Reverse recovery time test condition:  $I_F=0.5A$   $I_R=1.0A$   $I_{rr}=0.25A$   
 2. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

## Ratings And Characteristic Curves

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PERLEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS




FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS

