

**General Description**

These P-Channel enhancement mode power field effect transistors use advanced packaging technology and design to provide excellent RDS(ON). This device is suitable for use as a load switch or in PWM applications.

**Features**

- P-channel Enhancement mode
- 100% Avalanche tested
- 175°C operating temperature
- RoHS compliant

**Absolute Maximum Ratings****Product Summary**

BVDSS	RDS(on)	ID
-30V	8.8mΩ	-90A

**Applications**

- DC-DC Converters
- LCD Display inverter
- Power Management in Note book

**TO252 / TO251 Pin Configuration**

Type	Package	Marking
CMD90P03	TO-252	CMD90P03
CMU90P03	TO-251	CMU90P03

Symbol	Parameter	Rating	Units
$V_{DS}$	Drain-Source Voltage	-30	V
$V_{GS}$	Gate-Source Voltage	$\pm 20$	V
$I_D @ T_c = 25^\circ C$	Continuous Drain Current	-90	A
$I_{DM}$	Pulsed Drain Current	-270	A
EAS	Single Pulse Avalanche Energy ( $I_D = -40A$ )	320	mJ
$P_D @ T_c = 25^\circ C$	Total Power Dissipation	135	W
$T_{STG}$	Storage Temperature Range	-55 to 175	°C
$T_J$	Operating Junction Temperature Range	-55 to 175	°C

**Thermal Data**

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient	---	62	°C/W
$R_{\theta JC}$	Thermal Resistance Junction-Case	---	1.1	°C/W

Electrical Characteristics ( $T_J=25^\circ\text{C}$  , unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$\text{BV}_{\text{DSS}}$	Drain-Source Breakdown Voltage	$V_{\text{GS}}=0\text{V}$ , $I_D=-1\text{mA}$	-30	---	---	V
$R_{\text{DS(ON)}}$	Static Drain-Source On-Resistance	$V_{\text{GS}}=-10\text{V}$ , $I_D=-20\text{A}$	---	7	8.8	$\text{m}\Omega$
		$V_{\text{GS}}=-4.5\text{V}$ , $I_D=-10\text{A}$	---	10	12	
$V_{\text{GS(th)}}$	Gate Threshold Voltage	$V_{\text{GS}}=V_{\text{DS}}$ , $I_D =-250\mu\text{A}$	-1	---	-2.5	V
$I_{\text{DSS}}$	Drain-Source Leakage Current	$V_{\text{DS}}=-24\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $T_J=25^\circ\text{C}$	---	---	-1	$\text{uA}$
		$V_{\text{DS}}=-24\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $T_J=125^\circ\text{C}$	---	---	-100	
$I_{\text{GSS}}$	Gate-Source Leakage Current	$V_{\text{GS}} = \pm 20\text{V}$ , $V_{\text{DS}}=0\text{V}$	---	---	$\pm 100$	nA
$g_{\text{fs}}$	Forward Transconductance	$V_{\text{DS}}=-5\text{ V}$ , $I_D=-15\text{A}$	---	30	---	S
$R_g$	Gate Resistance	$V_{\text{DS}}=0\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $f=1\text{MHz}$	---	15	---	$\Omega$
$Q_g$	Total Gate Charge	$V_{\text{DD}}=-24\text{V}$ , $I_D=-90\text{A}$	---	125	---	$\text{nC}$
$Q_{\text{gs}}$	Gate-Source Charge		---	30	---	
$Q_{\text{gd}}$	Gate-Drain Charge		---	15	---	
$T_{\text{d(on)}}$	Turn-On Delay Time	$V_{\text{DD}}=-15\text{V}$ , $V_{\text{GS}}=-10\text{V}$ , $R_C=3.5\Omega$	---	20	---	$\text{ns}$
$T_r$	Rise Time		---	12	---	
$T_{\text{d(off)}}$	Turn-Off Delay Time		---	140	---	
$T_f$	Fall Time		---	40	---	
$C_{\text{iss}}$	Input Capacitance	$V_{\text{DS}}=-25\text{V}$ , $V_{\text{GS}}=0\text{V}$ , $f=1\text{MHz}$	---	2900	---	$\text{pF}$
$C_{\text{oss}}$	Output Capacitance		---	2300	---	
$C_{\text{rss}}$	Reverse Transfer Capacitance		---	65	---	

## Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
$I_s$	Continuous Source Current	$V_G=V_D=0\text{V}$ , Force Current	---	---	-90	A
$I_{\text{SM}}$	Pulsed Source Current		---	---	-270	A
$V_{\text{SD}}$	Diode Forward Voltage	$V_{\text{GS}}=0\text{V}$ , $I_F=-20\text{A}$ $T_j=25^\circ\text{C}$	---	---	-1.2	V





