


Multilayer Chip Common Mode Filter-SDMM Series

Operating Temp. : -40°C ~+85°C



FEATURES

- Effective for suppressing common mode noise at high frequency
- Excellent solderability characteristics
- Small size & low profile
- Multilayer type SMD component based on LTCC technology

APPLICATIONS

- Common mode noise suppression of high speed differential signal lines, such as MIPI, MHL, HDMI in mobile phone, tablet PC, TV etc.

PRODUCT IDENTIFICATION

SDMM

①

Type	
SDMM	Multilayer Chip Common Mode Filter

0806

②

U

③

External Dimensions (L×W) (mm)	
0605	0.65×0.50
0806	0.85×0.65
0906	0.90×0.68

-2

④

Common Mode Impedance (Ω)	
Example	Nominal Value
350	35
900	90

900

⑤

T

⑥

Feature Type	
H	for High-Speed Differential Signal Lines
U	for Ultra High Speed Differential Signal Lines


④

Number of Lines	
2	2 Lines
3	3 Lines


⑥

Packing	
T	Tape & Reel

SHAPE DIMENSIONS AND LAND-PATTERN



SHAPE DIMENSIONS AND LAND-PATTERN



Unit: mm

Type	L	W	T	SL	SW	P	b
SDMM0605	0.65±0.05	0.50±0.05	0.30±0.05	0.12±0.10	0.15±0.10	0.40±0.10	/
SDMM0806	0.85±0.05	0.65±0.05	0.40±0.05	0.20±0.05/-0.10	0.27±0.05	0.50±0.05	/
SDMM0906	0.90±0.05	0.68±0.05	0.40±0.05	0.12±0.10	0.15±0.10	0.35±0.10	SL

EQUIVALENT CIRCUIT



SPECIFICATION

SDMM0605H Series

Part Number	Common mode Impedance @ 100MHz	Max. DC Resistance	Max. Rated Current	Rated Voltage	Withstand Voltage	Min. Insulation Resistance
Units	Ω	Ω	mA	Volts	Volts	MΩ
Symbol	Z	DCR	I _r	VDC	V _p	IR
SDMM0605H-2-900T	90±20%	5.0	100	5	12.5	100

SDMM0906H Series

Part Number	Common mode Impedance @ 100MHz	Max. DC Resistance	Max. Rated Current	Withstand Voltage	Min. Insulation Resistance
Units	Ω	Ω	mA	Volts	MΩ
Symbol	Z	DCR	I _r	V _p	IR
SDMM0906H-3-300T	30±20%	4.0	50	12.5	100

SPECIFICATION

SDMM0605U Series

Part Number	Common mode Impedance @ 100MHz	Max. DC Resistance	Max. Rated Current	Rated Voltage	Withstand Voltage	Min. Insulation Resistance
Units	Ω	Ω	mA	Volts	Volts	M Ω
Symbol	Z	DCR	I _r	VDC	V _p	IR
SDMM0605U-2-120T	12±5	2.5	50	5	12.5	100
SDMM0605U-2-250T	25±20%	3.5	50	5	12.5	100





SDMM0806U Series

Part Number	Common Mode Impedance @ 100MHz	Max. DC Resistance	Max. Rated Current	Min. Insulation Resistance	Cutoff Frequency (typ.)
Units	Ω	Ω	mA	M Ω	GHz
Symbol	Z	DCR	I _r	IR	f ₀
SDMM0806U-2-120T	12±5	2.5	130	100	>8
SDMM0806U-2-350T	35±20%	3.5	100	100	>6
SDMM0806U-2-470T	47±20%	4.0	100	100	6
SDMM0806U-2-900T	90±20%	4.5	100	100	3.5

Note: Absolute maximum long term direct-current voltage between D+ and D-of differential lines: DC 1.5V



TYPICAL ELECTRICAL CHARACTERISTICS

SDMM0605H Series




TYPICAL ELECTRICAL CHARACTERISTICS





SDMM0906H Series



SDMM0906H Series



SDMM0605U Series



TYPICAL ELECTRICAL CHARACTERISTICS

SDMM0806U Series

