



Features:

- Fast Switching
- Low Gate Charge and $R_{DS(on)}$
- Low Reverse transfer capacitances
- 100% Single Pulse avalanche energy Test

V_{DSS}	60	V
I_D	0.3	A
P_D	0.35	W
$R_{DS(ON)max}$	2.5	Ω

Applications:

- PWM applications
- Load switch
- Power management



Absolute ($T_c=25^\circ\text{C}$ unless otherwise specified):

Symbol	Parameter	Rating	Units
V_{DSS}	Drain-to-Source Voltage	60	V
I_D	Continuous Drain Current	0.3	A
	Continuous Drain Current $T_c = 100^\circ\text{C}$	0.19	A
$I_{DM^{a1}}$	Pulsed Drain Current	0.9	A
V_{GS}	Gate-to-Source Voltage	± 20	V
dv/dt^{a3}	Peak Diode Recovery dv/dt	5.0	V/ns
P_D	Power Dissipation	0.35	W
$V_{ESD(G-S)}$	Gate source ESD (HBM-C= 100pF, R=1.5k Ω)	2000	V
T_J, T_{stg}	Operating Junction and Storage Temperature Range	150, -55 to 150	$^\circ\text{C}$
T_L	Maximum Temperature for Soldering	300	$^\circ\text{C}$

Electrical Characteristics ($T_c = 25^\circ C$ unless otherwise specified):

OFF Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
V_{DSS}	Drain to Source Breakdown Voltage	$V_{GS}=0V, I_D=-250\mu A$	60	--	--	V
$\Delta V_{DSS}/\Delta T_J$	Bvdss Temperature Coefficient	$I_D=-250\mu A$, Reference $25^\circ C$	--	0.1	--	$V/^\circ C$
I_{DSS}	Drain to Source Leakage Current	$V_{DS}=60, V_{GS}=0V, T_a=25^\circ C$	--	--	1	μA
		$V_{DS}=48V, V_{GS}=0V, T_a=125^\circ C$	--	--	250	
$I_{GSS(F)}$	Gate to Source Forward Leakage	$V_{GS} = +20V$	--	--	10	μA
$I_{GSS(R)}$	Gate to Source Reverse Leakage	$V_{GS} = -20V$	--	--	-10	μA

ON Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
$R_{DS(ON)}$	Drain-to-Source On-Resistance	$V_{GS}=10V, I_D=0.5A$	--	--	2.5	Ω
$R_{DS(ON)}$	Drain-to-Source On-Resistance	$V_{GS}=4.5V, I_D=0.3A$	--	--	3.5	Ω
$V_{GS(TH)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	1.0	1.7	2.5	V
Pulse width $t_p \leq 380\mu s, \delta \leq 2\%$						

Dynamic Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
g_{fs}	Forward Transconductance	$V_{DS}=10V, I_D=0.2A$	0.1	5.0	--	S
C_{iss}	Input Capacitance		--	20	--	pF
C_{oss}	Output Capacitance	$V_{GS} = 0V, V_{DS} = 15V$ $f = 1.0MHz$	--	12	--	
C_{rss}	Reverse Transfer Capacitance		--	4.4	--	

Resistive Switching Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
$t_{d(ON)}$	Turn-on Delay Time	$I_D = 0.2A, V_{DD} = 15V$ $V_{GS} = 10V, R_G = 3.0\Omega$	--	10	--	ns
t_r	Rise Time		--	45	--	
$t_{d(OFF)}$	Turn-Off Delay Time		--	15	--	
t_f	Fall Time		--	10	--	
Q_g	Total Gate Charge	$I_D = 0.3A, V_{DD} = 15V$ $V_{GS} = 10V$	--	1.7	--	nC
Q_{gs}	Gate to Source Charge		--	0.9	--	
Q_{gd}	Gate to Drain ("Miller")Charge		--	1.3	--	

Source-Drain Diode Characteristics						
Symbol	Parameter	Test Conditions	Rating			Units
			Min.	Typ.	Max.	
I _S	Continuous Source Current (Body Diode)		--	--	0.3	A
I _{SM}	Maximum Pulsed Current (Body Diode)		--	--	0.9	A
V _{SD}	Diode Forward Voltage	I _S =0.3A, V _{GS} =0V	--	--	1.5	V
t _{rr}	Reverse Recovery Time	I _S =0.3A, T _j = 25°C	--	40	--	ns
Q _{rr}	Reverse Recovery Charge	dI _F /dt=100A/us, V _{GS} =0V	--	120	--	nC

Pulse width tp≤380μs, δ≤2%

Symbol	Parameter	Typ.	Units
R _{θJA}	Junction-to-Ambient	350	°C/W

^{a1}: Repetitive rating; pulse width limited by maximum junction temperature

^{a3}: I_{SD} = 0.3A, di/dt ≤ 100A/us, V_{DD} ≤ BV_{DS}, Start T_j=25 °C

Typical Electrical And Thermal Characteristics




Figure 1:Switching Test Circuit




Figure 3 Output Characteristics




Figure 2:Switching Waveforms




Figure 4 Transfer Characteristics




Figure 5 Drain-Source On-Resistance










Figure 6 Rdson vs Vgs


Figure 7 Gate Charge

Figure 8 Source-Drain Diode Forward

Figure 9 Drain-Source On-Resistance

Figure 10 Safe Operation Area

Figure 11 Capacitance vs Vds


Figure 12 Normalized Maximum Transient Thermal Impedance