


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A0.	/.	新版发行	20.05.04	Yang
A1.	/.	重新核对图面	21.01.06	LiHui

PIN数	A±0.1	B±0.1	C±0.1
2P	4.30	1.00	3.25
3P	5.30	2.00	4.25
4P	6.30	3.00	5.25
5P	7.30	4.00	6.25
6P	8.30	5.00	7.25
7P	9.30	6.00	8.25
8P	10.30	7.00	9.25
9P	11.30	8.00	10.25
10P	12.30	9.00	11.25

- Specifications:
1. Rated Voltage : 50V AC/DC
 2. Rated Current : 1A AC,DC
 3. Withstand Voltage : 200V AC/minute
 4. Contact Resistance : 50mΩ(MAX.)
 5. Insulation Resistance : 100MΩ(MIN.)
 6. Storage Temperature Range: -40°C~+85°C;
 7. Operation Temperature Range: -25°C~+70°C;

3	插片	黄铜H65	镀镍锡	
2	插针	黄铜H65	镀镍锡	
1	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注



深圳市虹成电子有限公司

UNLESS OTHERWISE, GENERAL TOLERANCE:		NAME: 针座1.0立贴8P编带		P/N: HCZZ0039-8			
X. xxx ±0.05				DWG NO:			
X. xx ±0.15							
X. x ±0.25							
ANGULAR:		THIRD ANGLE PROJECTION		UNIT: SCALE SIZE: SHEET: REV.			
X. xx° ±1°				MM 1:1 A4 1/1 A1			
X. x° ±3°				DRAWN: CHECKED:		APPROVED:	
X. ° ±5°							