ABS07AIG

Request Samples 🕥

Check Inventory 🕥

3.2 x 1.5 x 0.9 mm RoHS/RoHS II Compliant MSL Level = N/A

Features

- AEC-Q200 Qualified
- Automotive Grade 1: -40°C to +125°C
- TS16949 Production Line Certified
- PPAP Available Upon Request
- Hermetically Seam-sealed Ceramic Package
- RoHS/RoHS II Compliant and Pb free

Applications

- Infotainment Systems
- Keyless Entry & Startup
- GPS & Navigation
- Comfort control
- ADAS (Advanced Driver Assistance Systems)
- Vehicle to Vehicle Communication
- LiDAR (Light Detection and Ranging)
- In-vehicle Networking
- Powertrain & Drive Control
- Power Control & Conversion


Parameters	Min.	Тур.	Max.	Units	Notes
Frequency		32.768		kHz	
Operation Mode	Flexural Mode (Tuning Fork)				
Operating Temperature	-40		+125	°C	Option "blank"; See options
Storage Temperature	-55		+125	°C	
Frequency Tolerance @	-10		+10		Option "1"; See options
+25°C	-20		+20	ppm	Option "blank"; See options
Temperature Coefficient	-0.040	-0.036		ppm/T ²	
Turn-over Temperature	+20	+25	+30	°C	
E			60		Over -40°C to +85°C
Equivalent series resistance (ESR)			70	kΩ	Over -40°C to +105°C
			80		Over -40°C to +125°C
Shunt capacitance (C0)		<1.4		pF	
Motional capacitance (C1)		4.7		fF	
Load capacitance(CL)		12.5		pF	Option "blank"; See options
Drive Level		0.1	0.5	μW	
Q value	10000	30000			
Aging	-3		+3	ppm	@25°C±3°C First year
Insulation Resistance	500			MΩ	@ 100 Vdc





5101Hidden Creek Ln Spicewood TX78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 06-07-22





5101Hidden Creek Ln Spicewood TX78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 06-07-22

ABS07AIG Request Samples 🕥 Check Inventory 3.2 x 1.5 x 0.9 mm $\left|\right\rangle$ **RoHS/RoHS II Compliant** Pb MSL Level = N/A **Mechanical Dimensions** 3.2±0.15 5 5±0.1 0.9max. 0.75 4-0.1 C0.25 Recommended Land Pattern 1.55 1.0 1.0 œ **Dimensions: mm Sealing Method = Seam Sealing**


ABRACON

5101Hidden Creek Ln Spicewood TX78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 06-07-22

ABS07AIG

Request Samples 🕥



3.2 x 1.5 x 0.9 mm RoHS/RoHS II Compliant MSL Level = N/A

220 °C

220 °C

Reflow Profile [JEDEC J-STD-020]




Table 1

	1Pb Eutectic Process assification Temperatures (Tc)				
Package	Volume mm ³	Volume mm ³			
Thickness	<350	>350			

235 °C

220 °C

<u>></u>2.5 mm Table 2

<2.5 mm

Classification	Temperatures	(T _c)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T _{smin})	100°C	150°C
Temperature maximum (T _{smax})	150°C	200°C
Time (T _{smin} to T _{smax}) (t _s)	60 - 120 sec.	60 - 120 sec.
Average ramp-up rate (T _{smax} to T _P)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T _L)	183°C	217°C
Time at liquidous (t_L)	60 - 150 sec.	60 - 150 sec.
Peak package body temperature (T _P)*	see Table 1	see Table 2
Time $(t_p)^{**}$ within 5°C of the specified classification temperature (T_C)	20 sec.	30 sec.
Ramp-down rate (T _p to T _{smax})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max


*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature $(t_{\mbox{\tiny p}})$ is defined as supplier minimum and a user maximum.



5101Hidden Creek Ln Spicewood TX78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 06-07-22




Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit:

www.abracon.com

ABRACON

REVISED: 06-07-22



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information



5101Hidden Creek Ln Spicewood TX78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISED: 06-07-22