# **CMOS Circuit for Analog Quartz Clocks with Bipolar Stepping Motor Drive**


#### **Description**

The H1344 is a low power 32kHz analog clock integrated circuit designed in CMOS technology to drive a bipolar stepping motor. A set of capacitors is provided on chip to be connected, in any combination, to the two oscillator terminals, with a maximum total capacitance of 48pF. Both the motor pulse period and the motor pulse width are maskprogrammable (see page 6 for already available options). For versions v143 and v221, the TEST1 and TEST2 pins are only for test and must not be used in the application.

### **Applications**

- Stepper Motor Driver for time-switches
- Analog clocks

# **Functional Diagram**



### Fig. 1

#### **Features**

- 32kHz quartz oscillator
- Integrated capacitors, mask selectable
- Single battery operation
- 0.7 μA typical current consumption
- Low resistance outputs for bipolar stepping motor
- Mask options for pad designation, motor period and pulse width, alarm frequency, modulation and duty
- Alarm output function compatible with either NPN or PNP-driver transistors
- Alarm input function
- 1024Hz output on AL<sub>IN</sub> pad for oscillator frequency verification
- Fast test function
- ESD protected terminals

### Pin Assignment




Fig. 2



### **Absolute Maximum Ratings**

Parameter	Symbol	Min.	Max.	Units
Supply voltage range Input voltage Storage temperature	V <sub>DD</sub> -V <sub>SS</sub> V <sub>IN</sub> T <sub>STOR</sub>	-0.3 V <sub>ss</sub> -55	+5 V <sub>DD</sub> +125	, °<<

Table 1

Stresses beyond these listed maximum ratings may cause permanent damage to the device. Exposure to conditions beyond specified operating conditions may affect device reliability or cause malfunction.

### **Handing Procedures**

This device contains circuitry to protect the terminals against damage due to high static voltages or electrical fields. However, it is advised that normal precautions be taken to avoid application of any voltage higher than maximum rated voltages to this circuit.

#### **Recommended Operating Conditions**

Parameter	Symbol	Value	Units
Ambient temperature Quartz frequency Quartz series resistance Motor coil resistance Positive supply Negative supply	$\begin{array}{l} T \\ F_{Q} \\ R_{Q} \\ R_{M} \\ V_{DD} \\ V_{SS} \end{array}$	25 32768 30 200 1.55	°C Hz kΩ Ω V

Table 2

### **Operating Conditions**

Parameter	Symbol	Min.	Тур.	Max.	Units
Operating temperature Quartz series resistance Trimmer capacitance	T <sub>OPR</sub>	-20 1.5	30	+70 50 30	°C kΩ pF

Table 3

### **Electrical and Switching Characteristics**

at recommended operating conditions (valid unless otherwise specified)

Parameter	Symbol	Test	Min.	Тур.	Max.	Units
Supply voltage Supply current	V <sub>DD</sub> I <sub>DD</sub>	operating without motor, AL <sub>IN</sub> open	+1.1	0.7	+1.8 2.0	V μA
Motor Output Current into load Pulse period Pulse width	I <sub>M</sub> T <sub>1</sub> t <sub>w</sub>	$V_{DD} = 1.2V, R_M = 200\Omega$	±4.0	Mask option* Mask option*		mA s ms
Alarm Output Frequency Modulation Cycle time Pulse duration Output current for driving NPN-transistor Output current for driving PNP-transistor	f <sub>A</sub> f <sub>A1</sub> T <sub>2</sub> t <sub>P</sub> IALOUTN IALOUTN IALOUTN IALOUTN IALOUTN	$V_{DD} = 1.2V, V_{OL} = 0.2V \\ V_{DD} = 1.2V, V_{OH} = 0.7V \\ V_{DD} = 1.2V, V_{OL} = 0.5V \\ V_{DD} = 1.2V, V_{OH} = 1.0V$	0.5 0.3 0.3 0.5	Mask option* Mask option* Mask option* Mask option*		Hz Hz s s μA mA mA
Alarm Input Test In/Output Alarm input delay Test frequency Input current (alarm) Input current	t <sub>ALD</sub> f <sub>T</sub> I <sub>IN</sub>	Input at $V_{SS}$ , $V_{DD} = 1.4V$ Input at $V_{DD}$	125 -1 1	1024 -5 15	570 -10 30	ms Hz μA μA
Oscillator Build-up time Stability against supply voltage variation Output capacitance Input capacitance	$\begin{array}{c} t_{\text{START}} \\ \underline{\Delta f} \\ \underline{\Delta V_{\text{DD}} \times f} \\ C_{\text{OUT}} \\ C_{\text{IN}} \end{array}$	$V_{DD} = 1.2V$ $1.1V \le V_{DD} \le 1.8V$		5 Mask option* Mask option*	2 12	s ppm/V pF pF

Table 4

<sup>\*</sup> See "Available options" on page 6.



# **Timing Waveforms**

# **Motor Output Waveform**




Fig. 3

### **Alarm Output Waveform**




Fig. 4



#### **Functional Description**

#### **Oscillator and Frequency Divider**

The quartz oscillator consists of an inverter, internal feedback resistance to bias the input and integrated capacitors. The values of the integrated capacitors are selectable by metal mask. The oscillator is designed for 32768Hz.

#### **Motor Drive Output**

The circuit contains two push-pull output buffers for driving bipolar stepping motors. Between two pulses, both P-channel transistor of the other buffer are conducting. The outputs are protected against inductive voltage spikes with diodes to both supply pins.

Both the motor pulse period and motor pulse width are programmable by metal mask over a wide range of values (see page 6 for available options).

#### **Alarm Output**

The alarm is activated by connecting ALARM<sub>IN</sub> to  $V_{SS}$  and is deactivated by opening the connection. A metal mask option is available to program a continuous activation of the alarm output.

The alarm output driver contains a push-pull output buffer to drive an external sound source by means of an external bipolar transistor. A metal mask option is available to allow the use of NPN or PNP-transistors.

The tone frequency, modulation frequency, modulation frequency and cycle time (ON/OFF time) are metal mask selectable.

#### **Test Mode**

The ALARM<sub>IN</sub> pin fulfills three functions:

- a) For normal operation, the ALARM<sub>IN</sub> pin is left open. The circuit provides a square wave signal of 1024Hz, which can be used to tune the oscillator.
- b) If the pin is connected to  $V_{\text{SS}}$ , the alarm signal is provided at pin 6.

If the ALARM<sub>IN</sub> pin is connected to  $V_{DD}$ , all output frequencies are increased by a factor of 64, the alarm modulation of  $f_{A1} = 8Hz$  and  $f_A = 2kHz$  are suppressed.

#### **Test configuration**




Fig. 5



# **Pad Location Diagram**

All dimensions in  $\mu\text{m}$ 





Fig. 6


5







# Package Information





END MEW





#### NOTES:

1 MAXIMUM DIE THICKNESS ALLOWABLE IS .015.

DIMENSIONING & TOLERANCES PER ANSI.Y14.5M - 1982.

"D" & "E" ARE REFERENCE DATUMS AND DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS, BUT DOES INCLUDE MOLD MISMATCH AND ARE MEASURED AT THE MOLD PARTING LINE. MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED 0.006 INCHES AT END AND .010 INCHES AT WINDOW

A "L" IS THE LENGTH OF TERMINAL FOR

SOLDERING TO A SUBSTRATE.

6. "N" IS THE NUMBER OF TERMINAL POSITIONS.

TERMINAL POSITIONS ARE SHOWN FOR

REFERENCE ONLY.

/8) FORMED LEADS SHALL BE PLANAR WITH RESPECT TO ONE ANOTHER WITHIN .003 INCHES AT SEATING PLANE.

THE APPEARANCE OF PIN #1 I.D ON THE 8 LD IS OPTIONAL, ROUND TYPE ON SINGLE LEADFRAME AND RECTANGULAR

TYPE ON MATRIX LEADFRAME.

COUNTRY OF ORIGIN LOCATION ON PACKAGE BOTTOM IS OPTIONAL AND DEPENDS ON ASSEMBLY LOCATION.

11. CONTROLLING DIMENSION: INCHES.

12. THIS PART IS COMPLIANT WITH JEDEC STANDARD MS-012, VARIATION AA, AB & AC.

#### THIS TABLE IN MILLIMETERS

S		COMMON	1		NOTE		3		5	
M B	D	<b>IMENSION</b>	VS .	N <sub>O</sub> _	VARI-		D		N	
°l MI	٧.	NOM.	MAX.	T <sub>E</sub>	ATIONS	MIN.	NOM.	MAX.		
A 1.5	5	1.63	1.73		AA	4.80	4.93	4.98	8	
A <sub>1</sub> 0.1	27	0.15	0.25		AB	8.58	8.69	8.74	14	
A <sub>2</sub> 1.4	0	1.47	1.55		AC	9.80	9.93	9.98	16	
B 0.3	35	0.41	0.49							
C 0.1	9	0.20	0.25							
D	SEE	VARIATIO	NS	3						
E 3.8	1	3.94	3.99							
е		1.27 BSC								
H 5.8	4	5.99	6.20							
h 0.2	25	0.33	0.41							
L 0.4	1	0.64	0.89							
N	SEE	VARIATIO	NS	5						
∞ 0		5°	8°							
X 2.1	6	2.36	2.54							



#### **Ordering Information**

#### **Versions**

The versions below are considered standards. For the other delivery form, please contact EM Microelectronic-Marin S.A. Please make sure to give the complete part number when ordering.

		I	Motor	A	Alarm Output			Integrated Capacitance				
Part Number	Version	Period (T <sub>1</sub> )	Pulse width (tw)	Frequency (f <sub>A</sub> )	Modulation $(f_{A1})$	Cycle time (T <sub>2</sub> )	Pulse duration (t <sub>P</sub> )	(C <sub>IN</sub> )	(Соит)	Alarm Output Transistor	Package	Delivery Form
EM1344V143DL8A+	1/4.40										DIL8	Stick
EM1344V143SO8A+	V143 *\	2s	46.8ms					17pF	25pF		8 pin SOIC	Stick
EM1344V143SO8B+	,										8 pin SOIC	Tape & Reel
EM1344V221DL8A+	V221										DIL8	Stick
EM1344V221SO8A+		2s	1s					9pF	20pF		8 pin SOIC	Stick
EM1344V221SO8B+											8 pin SOIC	Tape & Reel

<sup>\*)</sup> Supply voltage range of 1.4V - 2.8V

EM Microelectronic-Marin SA ("EM") makes no warranties for the use of EM products, other than those expressly contained in EM's applicable General Terms of Sale, located at http://www.emmicroelectronic.com. EM assumes no responsibility for any errors which may have crept into this document, reserves the right to change devices or specifications detailed herein at any time without notice, and does not make any commitment to update the information contained herein.

No licenses to patents or other intellectual property rights of EM are granted in connection with the sale of EM products, neither expressly nor implicitly.

In respect of the intended use of EM products by customer, customer is solely responsible for observing existing patents and other intellectual property rights of third parties and for obtaining, as the case may be, the necessary licenses.

Important note: The use of EM products as components in medical devices and/or medical applications, including but not limited to, safety and life supporting systems, where malfunction of such EM products might result in damage to and/or injury or death of persons is expressly prohibited, as EM products are neither destined nor qualified for use as components in such medical devices and/or medical applications. The prohibited use of EM products in such medical devices and/or medical applications is exclusively at the risk of the customer