











1 2 3 4 5 6 7 8 9

F  
E  
D  
C  
B  
A



Specifications  
 Current Rating:3.0A AC DC  
 Voltage Rating:125V AC DC  
 Insulation Resistance:1000MΩ Min.  
 Dielectric Withstanding Voltage:500V AC/minute  
 Contact Resistance:10mΩ Max.  
 Operating Temperature:-40°C to +105°C  
 Materials  
 Contact Material: Phosphor Bronze  
 Insulator Material:Nylon-9T,UL 94V-0  
 Solder Tabs: Brass  
 All materials must meet Greenconn hazardous substances control standards.



PIN.	M	L	L1
2pin	2.00	8.00	4.80
3pin	4.00	10.00	6.80
4pin	6.00	12.00	8.80
5pin	8.00	14.00	10.80
6pin	10.00	16.00	12.80
7pin	12.00	18.00	14.80
8pin	14.00	20.00	16.80
9pin	16.00	22.00	18.80
10pin	18.00	24.00	20.80
11pin	20.00	26.00	22.80
12pin	22.00	28.00	24.80
13pin	24.00	30.00	26.80
14pin	26.00	32.00	28.80
15pin	28.00	34.00	30.80

### Ordering Information

GWFD116 - XX XX A 001 D X A X  
 No. Of Pins Per Row 02~15      Standard Plating 22=Matte Tin      Color 2=White      Standard Packing D=Tape&Reel

### PCB LAYOUT

 Website:www.greenconn.com E-mail:sales@greenconn.com	3RD.ANG PROJ.	GENERAL TOLERANCE		DESIGNED: CHECKED: APPROVED:	DATE: DATE: DATE:	DWG. NO. GWFD116-CA001DA	TITLE. 2.00mm PITCH 90° SMT WAFER
		X:±5'	X:±0.50			PART NO. GWFD116-XXXXA001DXAX	
		.X'±2"	.X±0.30				
		.XX'±1"	.XX±0.20				
REV. A	UNIT. mm	SCALE. 1:1	PAGE. 1/1	.XXX'±/	.XXX±/		

AQ 1 2 3 4 5 6 7 8 9