

Features

- Complementary to MMBT3906
- Power dissipation of 300mW
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260°C

Mechanical Data

- Case: SOT-23
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026

Classification Of h_{FE}

RANK	RANGE
L	100-200
H	200-300



Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Collector-Base Voltage	V_{CBO}	V	-40
Collector-Emitter Voltage	V_{CEO}		-40
Emitter-Base Voltage	V_{EBO}		-5.0
Collector Current	I_C	A	-0.2
Collector Power Dissipation	P_C	mW	300
Storage temperature	T_{stg}	°C	-55 ~+150
Junction temperature	T_J	°C	-55 ~+150
Typical Thermal Resistance	$R_{\theta J-A}$	°C /W	625

Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	SYMBOL	UNIT	Condition	Min	Max
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	V	$I_C = -10\mu A, I_E = 0$	-40	—
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$		$I_C = -1.0mA, I_B = 0$	-40	—
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$		$I_C = -10\mu A, I_C = 0$	-5.0	—
Collector cut-off current	I_{CEO}	nA	$V_{CE} = -30V, V_{EB} = -3.0V$	—	-100
Collector-Base cut-off current	I_{CBO}		$V_{CB} = -40V, I_E = 0$	—	-100
Emitter-Base cut-off current	I_{EBO}		$V_{EB} = -5V, I_C = 0$	—	-100
DC Current Gain	$h_{FE(1)}$	—	$V_{CE} = -1.0V, I_C = -10mA$	100	300
	$h_{FE(2)}$		$V_{CE} = -1.0V, I_C = -50mA$	60	—
	$h_{FE(2)}$		$V_{CE} = -1.0V, I_C = -100mA$	30	—
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	V	$I_C = -50mA, I_B = -5mA$	—	-0.30
Base-Emitter Saturation Voltage	$V_{BE(sat)}$	V	$I_C = -50mA, I_B = -5mA$	—	-0.95
Delay time	t_d	ns	$V_{CC} = -3V, V_{BE(off)} = -0.5V, I_C = -10mA, I_{B1} = I_{B2} = -1mA$	—	35
Rise time	t_r			—	35
Storage time	t_s			—	225
Fall time	t_f			—	75

SOT-23







▶ Small-signal Characteristics

ITEM	SYMBOL	Condition	UNIT	Min	Max
Transition frequency	f_T	$I_C = -10\text{mA}, V_{CE} = -20\text{V}, f = 100\text{MHz}$	MHz	300	—



▶ Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-23	R1	0.008	3000	30000	120000	7"


▶ Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



► **Ratings And Characteristics Curves** (Ta=25°C Unless otherwise specified)




► **Package Outline Dimensions** (SOT-23)



Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.15	0.035	0.045
A1	-	0.10	-	0.004
A2	0.90	1.05	0.035	0.041
b	0.30	0.50	0.012	0.020
c	0.10	0.20	0.004	0.008
D	2.80	3.00	0.110	0.118
E	1.20	1.40	0.047	0.055
E1	2.25	2.55	0.089	0.100
e	0.950TYP		0.037TYP	
e1	1.80	2.00	0.071	0.079
L	0.550REF		0.022REF	
L1	0.30	0.50	0.012	0.020
θ	-	8°	-	8°

► **Suggested Pad Layout**



Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.80	-	0.031	-
K	-	0.90	-	0.035
M	2.00	-	0.078	-
N	-	1.90	-	0.074