



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE  $\pm 0.05$ )

SPECIFICATIONS  
 Rated Current:3.0AMP  
 Contact Resistance:20m $\Omega$  Max  
 Withstand Voltage:1000V AC/DC  
 Insulation Resistance:1000M $\Omega$  Min  
 Operation Temperature:-40 $^{\circ}$ c to +105 $^{\circ}$ c

Contact Material:Copper Alloy  
 Contact Plating:Au or Sn Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 260 $^{\circ}$ C $\pm$ 5 $^{\circ}$ C 5S

**Ordering Information**

PM 254 - \* - N - Z - \* - \*\*

No.of Rows 1=Single Row 2=Dual Row	No.of Pins 2-40Pin	Type Z=直针 S=弯针 R=弯脚	Length (Plastic) (mm)	Contact Plating G0:Gold Flash G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Flash/Tin S1:Tin
--	-----------------------	------------------------------	--------------------------	--

			GENERAL TOLERANCE		制 图 DRAWING		<b>深圳市华灿天禄电子有限公司</b> ShenzhenhuacantianluELECTRONICS CO., LTD					
			DIM	TOL	审 核 CHECK							
			X. X	$\pm 0.30$	批 准 APPROVAL			产 品 名 称 TITLE	2.54双排 排母 直针(塑高8.5)	版 本 REV.	A	
			X. XX	$\pm 0.20$	比 例 SCALE			产 品 料 号 PART NO.	PM254-2-N-Z-8.5-XX(L11.7)	单 位 UNITS	mm	
			X. XXX	$\pm 0.10$	投 影 Projection			材 料 MATERIAL			页 次 SHEET	1/1
序 号 No.	变 更 内 容 MODIFY CONTENT	日 期 MODIFY DATE	Angle	$\pm 3.0^{\circ}$								