SIEMENS

Data sheet

3VA5170-4EC36-1AA0



circuit breaker 3VA5 UL frame 125 breaking capacity class S 25kA @ 480 V 3-pole, line protection TM230, FTAM, In=70A overload protection Ir=70A fixed short-circuit protection Ii=5...10 x In UL489 SB (naval), 50 deg. cel. cable connection on both sides

| Model | | |
|--|-----------------------------|--|
| product brand name | SENTRON | |
| product designation | Molded-case circuit breaker | |
| product designation / according to UL file | SEAM | |
| Product version | System protection | |
| design of the load switch / according to UL 489 / Heating, Air Conditioning, and Refrigeration circuit breaker (HACR Type) | Yes | |
| design of the load switch / according to UL 489 / High- Intensity-Discharge circuit breaker (HID Type) | No | |
| design of the load switch / according to UL 489 / Switching Duty circuit breaker (SWD Type) | No | |
| design of the overcurrent release | TM230 | |
| protection function of the overcurrent release | LI | |
| number of poles | 3 | |
| General technical data | | |
| operating voltage / at AC / rated value | 690 V | |
| power loss [W] / maximum | 18.3 W | |
| Active power loss / for rated value of the current / at AC / in hot operating state / per pole | 6.1 W | |
| mechanical service life (switching cycles) / typical | 20 000 | |
| Electrical endurance (switching cycles) / at AC-1 / at 380/415 V 50/60 Hz | 8 000 | |
| Electrical endurance (switching cycles) / at AC-1 / at 690 V 50/60 Hz | 4 000 | |
| electrical endurance (switching cycles) / at 480 V | 8 000 | |
| electrical endurance (switching cycles) / at 600 V | 4 000 | |
| Neutral conductors / upgradeable/retrofittable | No | |
| ground-fault monitoring version | without | |
| product function | | |
| communication function | No | |
| other measurement function | No | |
| Net Weight | 0.951 kg | |
| Current | | |
| marking / according to UL 489 / 100%-rated breaker | No | |
| operational current | | |
| • at 40 °C | 70 A | |
| ● at 45 °C | 69 A | |
| • at 50 °C | 68 A | |
| ● at 55 °C | 67 A | |
| • at 60 °C | 66 A | |
| ● at 65 °C | 65 A | |
| ● at 70 °C | 64 A | |

| Switching capacity according to IEC 60947 | | |
|---|--|--|
| switching capacity class of the circuit breaker | S | |
| design of short-circuit protection | For switching power values in DC networks, see the 3VA molded case circuit breaker device manual; link to be found under Service & Support in the last chapter | |
| switching capacity according to UL 489 | | |
| breaking capacity current | | |
| • at 240 V | 65 kA | |
| ● at 480 V | 25 kA | |
| • at 600 Y/347 V | 14 kA | |
| djustable parameters | | |
| product feature / for L-tripping / selectable characteristic function | No | |
| type of value list setting current (Ir) / for L-tripping / with I2t characteristic | Fest | |
| reference value setting current (Ir) / for L-tripping / with I2t characteristic | x ln | |
| set values setting current (Ir) / for L-tripping / with I2t characteristic | 1 | |
| adjustable response factor setting current (Ir) / for L-tripping / with I2t characteristic / minimum | 1 | |
| adjustable response factor setting current (Ir) / for L-tripping / with I2t characteristic / maximum | 1 | |
| adjustable response value setting current (Ir) / of the L-trip / with I2t characteristic / minimum | 70 A | |
| adjustable response value setting current (Ir) / of the L-trip / with I2t characteristic / maximum type of value list delay time (tr) / for L-tripping / with I2t | 70 A Fest | |
| type of value list delay time (tr) / for L-tripping / with 12t characteristic reference value delay time (tr) / for L-tripping / with 12t | rest S | |
| characteristic set values delay time (tr) / for L-tripping / with I2t | 1 | |
| characteristic adjustable response value delay time (tr) / for L-tripping / | 1s | |
| with I2t characteristic / minimum adjustable response value delay time (tr) / for L-tripping / | 1s | |
| with I2t characteristic / maximum product feature / for S-tripping / independent of direction / | No | |
| selectable characteristic function product feature / for I-tripping / can be switched on/off | No | |
| design of I-trip / adjustable | Yes | |
| reference value setting current (li) / for l-tripping | x In | |
| set values setting current (li) / for I-tripping | 5;6;7;8;9;10 | |
| adjustable response factor setting current (li) / for l-tripping / minimum | 5 | |
| adjustable response factor setting current (li) / for l-tripping / maximum | 10 | |
| adjustable response value setting current (li) / for l-tripping / minimum | 350 A | |
| adjustable response value setting current (li) / for I-tripping / maximum | 700 A | |
| product feature / for G-tripping / selectable characteristic function | No | |
| product feature / with neutral conductor protection / can be switched on/off | No | |
| product feature / with neutral conductor protection / adjustable type of value list setting current (InN) / for N tripping | Yes | |
| type of value list setting current (InN) / for N-tripping | | |
| reference value setting current (InN) / for N-tripping adjustable absolute value setting current (InN) / for N- tripping / minimum | x In 0 A | |
| adjustable absolute value setting current (InN) / for N-tripping / maximum | 0 A | |
| tripping characteristic / of the lower tolerance band | AK_3VA5_1_70A_TM2_SuMuH_uT | |
| tripping characteristic / of the upper tolerance band | AK_3VA5_1_70A_TM2_GuMuH_gT | |
| let-through energy characteristic / at 240 V | DE_3VA5_1_70A_TMI2_outline u starter_3u4p_240V | |
| let-through energy characteristic / at 415 V | DE 3VA5 1 70A TM line u starter 3u4p 415V | |
| let-through energy characteristic / at 470 V | DE_3VA5_1_70A_TM_line u starter_3u4p_690V | |

tripping characteristic / of the let-through current characteristic / at 240 V
tripping characteristic / of the let-through current characteristic / at 415 V
tripping characteristic / of the let-through current characteristic / at 415 V
tripping characteristic / of the let-through current characteristic / at 690 V
Adjustable response value current / lg min.
adjustable current response value current / of the current-dependent overload release / full-scale value
Ground fault protection / tripping switchable / I2t=ON/OFF

DS_3VA5_1_70A_TM_line u starter_3u4p_415V

DS_3VA5_1_70A_TM_line u starter_3u4p_690V

70 A

70 A

70 A

| Ground fault protection / tripping switchable / I2t=ON/OFF | No |
|---|---|
| Mechanical Design | |
| product component | |
| undervoltage release | No |
| voltage trigger | No |
| trip indicator | No |
| height [in] | 5.51 in |
| Height | 140 mm |
| width [in] | 3 in |
| Type of connectable conductor cross-section, round conductor terminal, stranded | 1 x (8 AWG - 3/0) |
| Width | 76.2 mm |
| depth [in] | 3.01 in |
| depth | 76.5 mm |
| Connections | |
| arrangement of electrical connectors / for main current circuit | Front connection |
| type of electrical connection / for main current circuit | circular conductor terminal on both sides |
| Auxiliary circuit | |
| number of CO contacts / for auxiliary contacts | 0 |
| Accessories | |
| product extension / optional / motor drive | Yes |
| Environmental conditions | |
| protection class IP / on the front | IP40 |
| ambient temperature | |
| during operation / minimum | -25 °C |
| during operation / maximum | 70 °C |
| during storage / minimum | -40 °C |
| during storage / maximum | 80 °C |

General Product Approval

combat vessels) / supplement SB



Confirmation

certificate of suitability / as approval for NAVAL (no







Miscellaneous

EMC Declaration of Conformity Marine / Shipping other

Yes











Miscellaneous

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA5170-4EC36-1AA0

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3VA5170-4EC36-1AA0


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax en.aspx?mlfb=3VA5170-4EC36-1AA0


CAx-Online-Generator


http://www.siemens.com/cax


Tender specifications


http://www.siemens.com/specifications














last modified: 7/15/2022 🖸