



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C ~ +85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-PHD-2x2ALT	2.00	6.00
3	HC-PHD-2x3ALT	4.00	8.00
4	HC-PHD-2x4ALT	6.00	10.00
5	HC-PHD-2x5ALT	8.00	12.00
6	HC-PHD-2x6ALT	10.00	14.00
7	HC-PHD-2x7ALT	12.00	16.00
8	HC-PHD-2x8ALT	14.00	18.00
9	HC-PHD-2x9ALT	16.00	20.00
10	HC-PHD-2x10ALT	18.00	22.00
11	HC-PHD-2x11ALT	20.00	24.00
12	HC-PHD-2x12ALT	22.00	26.00

GENERAL TOLERANCE			制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
	DIM	TOL	审核 CHECK		产品名称 TITLE	PHD (2.0) 双排立贴	版本 REV.	A
	X.X	±0.30	批准 APPROVAL		产品料号 PART NO.	HC-PHD-2xNALT	单位 UNITS	mm
1	初版发行		比例 SCALE		材料 MATERIAL		页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle	±3.0°	投影 Projection			