

TMG60N04NF

N-Channel Enhancement Mosfet

General Description

- Low $R_{DS(ON)}$
- RoHS and Halogen-Free Compliant

Applications

- Load switch
- PWM


General Features

$V_{DS} = 40V$ $I_D = 60A$

$R_{DS(ON)} = 6.9m\Omega(\text{typ.})@V_{GS}=10V$



100% UIS Tested

100% R_g Tested



Marking: 60N04

NF:DFN5x6-8L



Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ Unless Otherwise Noted)

| Symbol | Parameter | Rating | Units |
|-----------------------------|--|------------|------------------|
| V_{DS} | Drain-Source Voltage | 40 | V |
| V_{GS} | Gate-Source Voltage | ± 20 | V |
| $I_D@T_C=25^\circ\text{C}$ | Continuous Drain Current ¹ | 60 | A |
| $I_D@T_C=100^\circ\text{C}$ | Continuous Drain Current ¹ | 35 | A |
| I_{DM} | Pulsed Drain Current ² | 130 | A |
| EAS | Single Pulse Avalanche Energy ³ | 48 | mJ |
| I_{AS} | Avalanche Current | 35 | A |
| $P_D@T_C=25^\circ\text{C}$ | Total Power Dissipation ⁴ | 39 | W |
| T_{STG} | Storage Temperature Range | -55 to 150 | $^\circ\text{C}$ |
| T_J | Operating Junction Temperature Range | -55 to 150 | $^\circ\text{C}$ |

Thermal Data

| Symbol | Parameter | Typ. | Max. | Unit |
|-----------------|---|------|------|--------------------|
| $R_{\theta JA}$ | Thermal Resistance Junction-ambient (Steady State) ¹ | --- | 60 | $^\circ\text{C/W}$ |
| $R_{\theta JC}$ | Thermal Resistance Junction-Case ¹ | --- | 3.2 | $^\circ\text{C/W}$ |

**TMG60N04NF****N-Channel Enhancement Mosfet****Electrical Characteristics (T_J=25 °C, unless otherwise noted)**

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|---------------------|--|--|------|------|------|------|
| BV _{DSS} | Drain-Source Breakdown Voltage | V _{GS} =0V, I _D =250uA | 40 | --- | --- | V |
| R _{DS(ON)} | Static Drain-Source On-Resistance ² | V _{GS} =10V, I _D =12A | --- | 6.9 | 8.5 | mΩ |
| | | V _{GS} =4.5V, I _D =10A | --- | 10.0 | 15 | |
| V _{GS(th)} | Gate Threshold Voltage | V _{GS} =V _{DS} , I _D =250uA | 1.35 | --- | 3 | V |
| I _{DSS} | Drain-Source Leakage Current | V _{DS} =32V, V _{GS} =0V, T _J =25°C | --- | --- | 1 | uA |
| | | V _{DS} =32V, V _{GS} =0V, T _J =55°C | --- | --- | 5 | |
| I _{GSS} | Gate-Source Leakage Current | V _{GS} =±20V, V _{DS} =0V | --- | --- | ±100 | nA |
| R _g | Gate Resistance | V _{DS} =0V, V _{GS} =0V, f=1MHz | --- | 1.7 | --- | Ω |
| Q _g | Total Gate Charge (4.5V) | V _{DS} =20V, V _{GS} =4.5V, I _D =12A | --- | 5.8 | --- | nC |
| Q _{gs} | Gate-Source Charge | | --- | 3 | --- | |
| Q _{gd} | Gate-Drain Charge | | --- | 1.2 | --- | |
| T _{d(on)} | Turn-On Delay Time | V _{DD} =15V, V _{GS} =10V, R _G =3.3Ω I _D =1A | --- | 14.3 | --- | ns |
| T _r | Rise Time | | --- | 5.6 | --- | |
| T _{d(off)} | Turn-Off Delay Time | | --- | 20 | --- | |
| T _f | Fall Time | | --- | 11 | --- | |
| C _{iss} | Input Capacitance | V _{DS} =15V, V _{GS} =0V, f=1MHz | --- | 690 | --- | pF |
| C _{oss} | Output Capacitance | | --- | 193 | --- | |
| C _{rss} | Reverse Transfer Capacitance | | --- | 38 | --- | |

Diode Characteristics

| Symbol | Parameter | Conditions | Min. | Typ. | Max. | Unit |
|-----------------|--|---|------|------|------|------|
| I _s | Continuous Source Current ^{1,5} | V _G =V _D =0V, Force Current | --- | --- | 60 | A |
| V _{SD} | Diode Forward Voltage ² | V _{GS} =0V, I _s =1A, T _J =25°C | --- | --- | 1 | V |

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width ≤ 300us , duty cycle ≤ 2%
- 3.The EAS data shows Max. rating . The test condition is V_{DD}=25V,V_{GS}=10V,L=0.1mH,I_{AS}=31A
- 4.The power dissipation is limited by 150°C junction temperature
- 5.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

TMG60N04NF

N-Channel Enhancement Mosfet

Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.2 On-Resistance vs G-S Voltage




Fig.3 Source Drain Forward Characteristics




Fig.4 Gate-Charge Characteristics




Fig.5 Normalized $V_{GS(th)}$ vs T_J




Fig.6 Normalized $R_{DS(on)}$ vs T_J

TMG60N04NF

N-Channel Enhancement Mosfet




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 U clamped Inductive Waveform

Package Mechanical Data:DFN5x6-8L



| Symbol | Common | | | |
|--------|----------|--------|----------|--------|
| | mm | | Inch | |
| | Min | Max | Min | Max |
| A | 1.03 | 1.17 | 0.0406 | 0.0461 |
| b | 0.34 | 0.48 | 0.0134 | 0.0189 |
| c | 0.824 | 0.0970 | 0.0324 | 0.082 |
| D | 4.80 | 5.40 | 0.1890 | 0.2126 |
| D1 | 4.11 | 4.31 | 0.1618 | 0.1697 |
| D2 | 4.80 | 5.00 | 0.1890 | 0.1969 |
| E | 5.95 | 6.15 | 0.2343 | 0.2421 |
| E1 | 5.65 | 5.85 | 0.2224 | 0.2303 |
| E2 | 1.60 | / | 0.0630 | / |
| e | 1.27 BSC | | 0.05 BSC | |
| L | 0.05 | 0.25 | 0.0020 | 0.0098 |
| L1 | 0.38 | 0.50 | 0.0150 | 0.0197 |
| L2 | 0.38 | 0.50 | 0.0150 | 0.0197 |
| H | 3.30 | 3.50 | 0.1299 | 0.1378 |
| I | / | 0.18 | / | 0.0070 |