


规格承认书

SPECIFICATION


1/2

CUSTOMER		CUSTOMER'S P/S	
TSSUE DATE	2023.01.24	OUR P/N	XRCD32-2R2M

1. 外观尺寸图 DIMENSIOS



2. 接线图 CONNECTION (BOTTOM VIEW)

 $A=3.5\pm 0.2$ $B=3.0\pm 0.2$ $C=2.1\pm 0.2$


3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	$\Phi 0.17$	11.5TS	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 100KHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XRCD32-2R2M	$2.2\mu\text{H}\pm 20\%$	$0.095\ \Omega$	1.6A	2R2	—

备注:

 OPERATING TEMP. : $-40^{\circ}\text{C}\sim +85^{\circ}\text{C}$

INDUCTANCE DROP=10% TYP. AT IDC.

制作DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
C. Z. W 2023.01.24	L. J. W 2023.01.24	O. T. Q 2023.01.24	



试产（样）报告

(TEST REPORT)

2/2

MODEL NO: 产品型号:	XRCD32-2R2M	EVALUATED Q' TY: 试样数:	10PCS
--------------------	-------------	--------------------------	-------

WATERIAL CODE: 磁材型号规格:	TESTED DATE: 试制日期:	2023. 01. 24
---------------------------	-----------------------	--------------

SPC 规格	LOA (S-F)	DCR								
	uH	Ω								
LOTS 序号	2. 2uH± 20%	MAX 0. 095								
1	2. 2	0. 078								
2	2. 3	0. 084								
3	2. 5	0. 083								
4	2. 2	0. 080								
5	2. 4	0. 084								
6	2. 4	0. 080								
7	2. 5	0. 085								
8	2. 2	0. 087								
9	2. 3	0. 078								
10	2. 5	0. 084								
11	2. 2	0. 079								

(DATA) 试样情况记录

REMARK: HK1062A, HK5028C. VR-114, VR-115
 备注: 100KHZ 0. 1V
 外观: OK

RESULTS: 判定: <input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 非ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	制样员DRW	东莞市祥如电子有限公司
	L. F. T 2023. 01. 24	