

**TM05N02HI**
**N-Channel Enhancement Mosfet**
**General Description**

- Low R<sub>DS(ON)</sub>
- RoHS and Halogen-Free Compliant




**Applications**

- Load switch
- PWM

**Product Summary**

V<sub>DS</sub> = 20V I<sub>D</sub> = 5.0A  
 R<sub>DS(ON)</sub> = 22 mΩ (typ.) @ V<sub>GS</sub> = 4.5V

100% UIS Tested  
 100% R<sub>g</sub> Tested



Marking: 2300 OR 05N02

**Absolute Maximum Ratings (T<sub>C</sub>=25°C unless otherwise noted)**

Symbol	Parameter	Rating	Units
V <sub>DS</sub>	Drain-Source Voltage	20	V
V <sub>GS</sub>	Gate-Source Voltage	±12	V
I <sub>D</sub> @T <sub>A</sub> =25°C	Continuous Drain Current, V <sub>GS</sub> @ 10V <sup>1</sup>	5.0	A
I <sub>D</sub> @T <sub>A</sub> =70°C	Continuous Drain Current, V <sub>GS</sub> @ 10V <sup>1</sup>	4.0	A
I <sub>DM</sub>	Pulsed Drain Current <sup>2</sup>	15.0	A
P <sub>D</sub> @T <sub>A</sub> =25°C	Total Power Dissipation <sup>3</sup>	1	W
T <sub>STG</sub>	Storage Temperature Range	-55 to 150	°C
T <sub>J</sub>	Operating Junction Temperature Range	-55 to 150	°C

**Thermal Data**

Symbol	Parameter	Typ.	Max.	Unit
R <sub>θJA</sub>	Thermal Resistance Junction-ambient <sup>1</sup>	---	125	°C/W
R <sub>θJC</sub>	Thermal Resistance Junction-Case <sup>1</sup>	---	80	°C/W

**TM05N02HI**
**N-Channel Enhancement Mosfet**
**Electrical Characteristics (T<sub>J</sub>=25 °C, unless otherwise noted)**

Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
--------	-----------	-----------------	-----	-----	-----	-------

**Off Characteristics**

BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> = 0 V, I <sub>D</sub> = 250 uA	20	--	--	V
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> = 20 V, V <sub>GS</sub> = 0 V	--	--	1	uA
		V <sub>DS</sub> = 16 V, T <sub>C</sub> = 125°C	--	--	10	uA
I <sub>GSSF</sub>	Gate-Body Leakage Current, Forward	V <sub>GS</sub> = 10 V, V <sub>DS</sub> = 0 V	--	--	100	nA
I <sub>IGSSR</sub>	Gate-Body Leakage Current, Reverse	V <sub>GS</sub> = -10 V, V <sub>DS</sub> = 0 V	--	--	-100	nA

**On Characteristics**

V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = 250 uA	0.45	0.7	1.1	V
R <sub>D(on)</sub>	Static Drain-Source On-Resistance	V <sub>GS</sub> = 4.5 V, I <sub>D</sub> = 3.5 A	--	22	30	mΩ
		V <sub>GS</sub> = 2.5 V, I <sub>D</sub> = 2.0 A	-	22	37	

**Dynamic Characteristics**

C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> = 10 V, V <sub>GS</sub> = 0 V, f = 1.0 MHz	--	180	-	pF
C <sub>oss</sub>	Output Capacitance		--	37	-	pF
C <sub>rss</sub>	Reverse Transfer Capacitance		--	34	-	pF

**Switching Characteristics**

t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>GS</sub> = 5 V, V <sub>DS</sub> = 10 V, I <sub>D</sub> = 3 A, R <sub>G</sub> = 6 Ω, R <sub>L</sub> = 2.7 Ω	--	4.5	--	ns
t <sub>r</sub>	Turn-On Rise Time		--	31	--	ns
t <sub>d(off)</sub>	Turn-Off Delay Time		--	12	--	ns
t <sub>f</sub>	Turn-Off Fall Time		--	4.0	--	ns
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> = 10 V, I <sub>D</sub> = 3 A, V <sub>GS</sub> = 5 V	--	6.23	--	nC
Q <sub>gs</sub>	Gate-Source Charge		--	6	--	nC
Q <sub>gd</sub>	Gate-Drain Charge		--	0.5	--	nC

**Drain-Source Diode Characteristics and Maximum Ratings**

I <sub>S</sub>	Maximum Continuous Drain-Source Diode Forward Current	--	--	5.0	A
I <sub>SM</sub>	Maximum Pulsed Drain-Source Diode Forward Current	--	--	10.5	A
V <sub>SD</sub>	Drain to Source Diode Forward Voltage, V <sub>GS</sub> = 0 V, I <sub>SD</sub> = 3.5 A, T <sub>J</sub> = 25°C	--	--	1.2	V

**Notes:**

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. Device mounted on FR-4 PCB, 1inch x 0.85inch x 0.062 inch
3. Pulse Test: Pulse Width≤300μs, Duty Cycles≤0.5%

## Typical Performance Characteristics




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance Variation vs  
Drain Current and Gate Voltage




Figure 4. Body Diode Forward Voltage  
Variation with Source Current  
and Temperature




Figure 5. Capacitance Characteristics






Figure 6. Gate Charge Characteristics

## TM05N02HI


## N-Channel Enhancement Mosfet




**Figure 7. Breakdown Voltage Variation vs Gate-Voltage**




**Figure 8. On-Resistance Variation vs Gate Voltage**



**Figure 9. Maximum Safe Operating Area**




**Figure 10. Maximum Continuous Drain Current vs Case Temperature**



**Figure 11. Transient Thermal Response Curve**

## Package Mechanical Data: SOT-23



Symbol	Dimensions in Millimeters	
	MIN.	MAX.
A	0.900	1.150
A1	0.000	0.100
A2	0.900	1.050
b	0.300	0.500
c	0.080	0.150
D	2.800	3.000
E	1.200	1.400
E1	2.250	2.550
e	0.950TYP	
e1	1.800	2.000
L	0.550REF	
L1	0.300	0.500
θ	0°	8°