



## 产品规格书

CUSTOMER		CUSTOMER'S P/S	
ISSUE DATE	2022.05.06	OUR P/N	XRCD43-331K

### 1. 外观尺寸图 DIMENSIONS



### 2. 接线图 CONNECTION (BOTTOM VIEW)




### 3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.08	118TS (REF)	CLOSED

### 4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1kHz 0.25V	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XRCD43-331K	330uH±10%	3.6 Ω	0.28A	331	—

### 5. 推荐回流焊温度曲线



备注:

OPERATING TEMP. :-40°C ~ +85°C

INDUCTANCE DROP=35% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD
--------	--------	---------

L. C. Q 2022. 05. 06	O. T. Q 2022. 05. 06	X. S. H	东莞市祥如电子有限公司
-------------------------	-------------------------	---------	-------------

# 试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:	XRCD43-331K	EVALUATED Q' TY: 试样数:	10PCS
--------------------	-------------	--------------------------	-------

WATERIAL CODE: 磁材型号规格:	SMD 4532	TESTED DATE: 试制日期:	2022. 05. 06
---------------------------	----------	-----------------------	--------------


SPC 规格	1KHz/0.25V L (uH)	DCR (Ω)								
			LOTS 序号	330uH ± 20%	MAX 3.6 Ω					
1	338.2	3.52								
2	327.5	3.48								
3	340.8	3.49								
4	331.3	3.48								
5	332.7	3.50								
6	329.5	3.49								
7	336.8	3.46								
8	337.6	3.48								
9	338.2	3.47								
10	333.6	3.49								
11										
12										
13										
14										
15										

(DATA) 试样情况记录

REMARK: HM2801A HM2770A HP4342A VR-114 VR115  
 备注: 用100KHz 0.25V全检  
 外观: OK

RESULTS: 判定:	制样员DRW	
<input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____		东莞市祥如电子有限公司

# 包装



## 包装方式

LEADER部	SEAL TAPE 尺寸	1圈以上
	START CARRIER TAPE尺寸	20cm以上
	TRATLER部尺寸	10cm以上
	数量	2000pcs

