



产品规格书

CUSTOMER		CUSTOMER'S P/S	
TSSUE DATE	2023.05.01	OUR P/N	XRCD75-1R5M

1. 外观尺寸图 DIMENSIOS



2. 接线图 CONNECTION (BOTTOM VIEW)




3. 绕线规格 WINDING SPEC

端子 TERMINZL	线 WIRE	圈数 TURNS	绕线方式 WINDING METHOD
S---F	Φ0.43	6.0TS (REF)	CLOSED

4. 电气特性 ELECTRONICS CHARACTERISTIC

客户代码 Part No.	厂方代码 OUR Part No.	电感量 Inductance at 1kHz	直流电阻 D. C. R max.	定格电流 I. D. C max.	标识 Marking	规格代码 Sample No.
	XRCD75-1R5M	1.5uH±30%	0.018 Ω	4.0A	1R5(黑色)	—

5. 推荐回流焊温度曲线



备注:

OPERATING TEMP. : -40℃ ~ +85℃

INDUCTANCE DROP=35% TYP. AT IDC.

制作 DRW	审核 CHK	确认 APPD	东莞市祥如电子有限公司
陈泽伟	刘汉清		

2023.05.01	2023.05.01		
------------	------------	--	--

试产（样）报告

(TEST REPORT)

MODEL NO: 产品型号:	XRCD75-1R5M	EVALUATED Q' TY: 试样数:	5PCS
--------------------	-------------	--------------------------	------

WATERIAL CODE: 磁材型号规格:	SMD 7850	TESTED DATE: 试制日期:	2023. 05. 01
---------------------------	----------	-----------------------	--------------


SPC 规格	1KHz/0.25V	1KHz/0.25V							
	LOA(S-F) uH	DCR Ω							
LOTS 序号	1.5uH±30%	MAX 0.018							
1	1.5	0.010							
2	1.6	0.011							
3	1.6	0.011							
4	1.5	0.010							
5	1.6	0.010							
6									
7									
8									
9									
10									
11									
12									
13									
14									
15									

(DATA) 试样情况记录

REMARK: HM2801A HM2770A HP4342A VR-114 VR115
 备注: 用100KHz 0.25V全检
 外观: OK

RESULTS: 判定: <input checked="" type="checkbox"/> 合格 (PASSED) <input checked="" type="checkbox"/> ROHS <input type="checkbox"/> 不合格, 改良后 (FAILED) 参照 (REF) _____	制样员DRW	东莞市祥如电子有限公司
	陈泽伟 2023. 05. 01	

包装



包装方式

LEADER部	SEAL TAPE 尺寸	10cm以上
	START CARRIER TAPE尺寸	20cm以上
	TRATLER部尺寸	10cm以上
	数量	1000pcs

