

## Product Summary


- 60V/-2.8A  
 $R_{DS(ON)} = 100m\Omega$  (Typ) @  $V_{GS} = -10V$   
 $R_{DS(ON)} = 150m\Omega$  (Typ) @  $V_{GS} = -4.5V$
- Typfical ESD protectfion: 1500V

## Application

- DC-DC Converters.
- Load Switch.
- Power Management.

## Package and Pin Configuration

SOT-23



P-Channel MOSFET

Marking: 9CTPM

## Absolute Maximum Ratings ( $T_A = 25^\circ C$ unless otherwise noted)

Characteristic		Symbol	Value	Unit	
Drain-Source Voltage		$V_{DSS}$	-60	V	
Gate-Source Voltage		$V_{GS}$	$\pm 20$	V	
Continuous Drain Current	$V_{GS} = -10V$	$I_D$	-2.8	A	
			-2.4		
			-2.3		
Pulsed Drain Current		$I_{DM}$	-13.6	A	
Continuous Source Current (Body Diode)		(Note 6)	$I_S$	-2.5	A
Pulsed Source Current (Body Diode)		(Note 7)	$I_{SM}$	-13.6	A

## Thermal Characteristics (@ $T_A = +25^\circ C$ , unless otherwise specified.)



Characteristic		Symbol	Value	Unit
Power Dissipation Linear Derating Factor	(Note 5)	$P_D$	1.1	W
	(Note 6)		8.8	
			1.92	
Thermal Resistance, Junction to Ambient	(Note 5)	$R_{\theta JA}$	113	$^\circ C/W$
	(Note 6)		65	
Operating and Storage Temperature Range		$T_J, T_{STG}$	-55 to +150	$^\circ C$

**Electrical Characteristics (  $T_A = 25^\circ\text{C}$  unless otherwise noted )**


[www.sot23.com.tw](http://www.sot23.com.tw)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
<b>OFF CHARACTERISTICS</b>						
Drain-Source Breakdown Voltage	$BV_{DSS}$	-60	—	—	V	$I_D = -250\mu\text{A}, V_{GS} = 0\text{V}$
Zero Gate Voltage Drain Current	$I_{DSS}$	—	—	-1	$\mu\text{A}$	$V_{DS} = -48\text{V}, V_{GS} = 0\text{V}$
Gate-Source Leakage	$I_{GSS}$	—	—	$\pm 100$	nA	$V_{GS} = \pm 20\text{V}, V_{DS} = 0\text{V}$
<b>ON CHARACTERISTICS</b>						
Gate Threshold Voltage	$V_{GS(th)}$	-1	-1.5	-3	V	$I_D = -250\mu\text{A}, V_{DS} = V_{GS}$
Static Drain-Source On-Resistance (Note 8)	$R_{DS(on)}$	—	100	150	m $\Omega$	$V_{GS} = -10\text{V}, I_D = -3\text{A}$
			150	200		$V_{GS} = -4.5\text{V}, I_D = -1.9\text{A}$
Forward Transconductance (Notes 8 & 9)	$g_{fs}$	—	4.7	—	S	$V_{DS} = -15\text{V}, I_D = -2.3\text{A}$
Diode Forward Voltage (Note 8)	$V_{SD}$	—	-0.85	-0.95	V	$I_S = -2\text{A}, V_{GS} = 0\text{V}$
Reverse Recovery Time (Note 9)	$t_{rr}$	—	25.1	—	ns	$I_F = -1.7\text{A}, di/dt = 100\text{A}/\mu\text{s}$
Reverse Recovery Charge (Note 9)	$Q_{rr}$	—	27.2	—	nC	
<b>DYNAMIC CHARACTERISTICS (Note 9)</b>						
Input Capacitance	$C_{iss}$	—	637	—	pF	$V_{DS} = -30\text{V}, V_{GS} = 0\text{V}$ $f = 1\text{MHz}$
Output Capacitance	$C_{oss}$	—	70	—	pF	
Reverse Transfer Capacitance	$C_{rss}$	—	53	—	pF	
Total Gate Charge (Note 10)	$Q_g$	—	9.8	—	nC	$V_{GS} = -5\text{V}$ $V_{DS} = -30\text{V}$ $I_D = -2.3\text{A}$
Total Gate Charge (Note 10)	$Q_g$	—	17.7	—	nC	
Gate-Source Charge (Note 10)	$Q_{gs}$	—	1.6	—	nC	
Gate-Drain Charge (Note 10)	$Q_{gd}$	—	4.4	—	nC	
Turn-On Delay Time (Note 10)	$t_{D(on)}$	—	2.6	—	ns	$V_{DD} = -30\text{V}, V_{GS} = -10\text{V}$ $I_D = -1\text{A}, R_G \cong 6\Omega$
Turn-On Rise Time (Note 10)	$t_r$	—	3.4	—	ns	
Turn-Off Delay Time (Note 10)	$t_{D(off)}$	—	26.2	—	ns	
Turn-Off Fall Time (Note 10)	$t_f$	—	11.3	—	ns	


**Typical Performance Characteristics ( $T_A=25^\circ\text{C}$  unless otherwise Specified)**









Transient Thermal Impedance




Pulse Power Dissipation




Output Characteristics



Output Characteristics



Typical Transfer Characteristics



Normalised Curves v Temperature







TECH PUBLIC

台舟电子

SQ2361AEES

60V P-CHANNEL ENHANCEMENT MODE MOSFET With ESD

www.sot23.com.tw







**TECH PUBLIC**


—台舟电子—

**SQ2361AEES**

60V P-CHANNEL ENHANCEMENT MODE MOSFET With ESD

[www.sot23.com.tw](http://www.sot23.com.tw)

**SOT-23 Package Information**



Symbol	Dimensions in Millimeters	
	MIN.	MAX.
A	0.900	1.150
A1	0.000	0.100
A2	0.900	1.050
b	0.300	0.500
c	0.080	0.150
D	2.800	3.000
E	1.200	1.400
E1	2.250	2.550
e	0.950TYP	
e1	1.800	2.000
L	0.550REF	
L1	0.300	0.500
$\theta$	0°	8°