

Precision Load Switch with Adjustable Current Limit

DESCRIPTION

The ETA6023 is a load switch which provides full protection to systems and loads which may encounter large current conditions. ETA6023 offers a 95mΩ current-limited switch which can operate over an input voltage range of 2.5-5.5V. The current limit can be externally programmed by a precision resistor, ranges from 75mA to 1.7A. Switch control is by a logic input (EN) capable of interfacing directly with low voltage control signals. Current is prevented from flowing when the switch is off and the output voltage is higher than the input voltage. ETA6023 also features thermal shutdown protection which shuts off the switch to prevent damage to the part when a continuous over-current condition causes excessive heating. When the switch current reaches the current limit, the parts operate in a constant-current mode to prohibit excessive currents from causing damage. The ETA6023 will not turn off after a current limit fault, but will rather remain in the constant current mode indefinitely. ETA6023 is housed in a tiny SOT23-5L package

APPLICATION

- USB ports/Hubs
- Hot Swaps
- Cellphones
- Tablet PC
- Set Top Box
- PC motherboard
- Handheld Devices

FEATURES

- Up to 1.5A Max Load current
- Accurate Current-limit threshold: +/-5%
- Programmable Current-limit : 75mA to 1.7A
- Fast Over-Current Response
- Reversed Current blocking
- Thermal Shutdown, UVLO protection
- Tiny SOT23-5L Package

ORDERING INFORMATION

PART	PACKAGE PIN	TOP MARK
ETA6023S2F-T	SOT23-5	B8YW └── Date Code └── Product Number

TYPICAL APPLICATION

