

Programmable Current-Limited Load Switch

DESCRIPTION

The ETA6280 is a load switch which provides full protection to systems and loads which may encounter large current conditions. ETA6280 offers a $70m\Omega$ currentlimited switch which can operate over an input voltage range of 2.1-6V. The current limit can be externally programmed by a precision resistor, ranging from 75mA to 2.2A. Switch control is by a logic input (EN) capable of interfacing directly with low voltage control signals. Current is prevented from flowing when the switch is off and the output voltage is higher than the input voltage. ETA6280 also features thermal shutdown protection which shuts off the switch to prevent damage to the part when a continuous over-current condition causes excessive heating. When the switch current reaches the current limit, the parts operate in a constant-current mode to prohibit excessive currents from causing damage. The ETA6280 will not turn off after a current limit fault, but will rather remain in the constant current mode indefinitely. The nFAULT output asserts low during over-current and reverse-voltage conditions.

ETA6280 is available in three types of package: SOT23-5, SOT23-6, DFN2x2-6


FEATURES

- Wide Input Voltage Range: 2.1V to 6V
- ▼ 7.5V Input Standoff Voltage
- ◆ 6.1V OVP
- Up to 2A Max Continuous Load Current
- Programmable Current Limit: 75mA to 2200mA
- Fast Over Current Response
- ◆ Fault Flag Output: nFAULT Pin
- Reversed Input-Output Current Blocking
- Thermal Shutdown, UVLO Protection
- Tiny SOT23-5, SOT23-6, DFN2x2-6 Package
- RoHS Compliant

APPLICATIONS

- USB Ports and Hubs
- Digital TVs
- Set-Top Boxes
- VOIP Phones


TYPICAL APPLICATION



ORDERING INFORMATION	PART No.	PACKAGE	TOP MARK	Pcs/Reel
	ETA6280S2F	SOT23-5	Hx <u>YW</u>	3000
	ETA6280S2G	SOT23-6	Hx <u>YW</u>	3000
	ETA6280D2G	DFN2x2-6	Hx <u>YW</u>	3000



PIN CONFIGURATION



ABSOLUTE MAXIMUM RATINGS

(Note: Exceeding these limits may damage the device. Exposure to absolute maximum rating conditions for long periods may affect device reliability.)

IN, OUT Voltage to GN	1D	0.3	V to 7.5V
All other Pin Voltage to	GND	0.3	V to 7.5V
EN Voltage to IN		7.5	V to 0.3V
OUT to ground current	t	Interna	lly limited
Junction Temperature		160°C	
Storage Temperature F	Range	–55°C	to 150°C
Thermal Resistance	θ_{JC}	θ_{JA}	
DFN2x2-6	30	80	ºC/W
SOT23-6	90	180	°C/W
SOT23-5	110	220	°C/W
Lead Temperature (So	ldering, 1	0sec)	260°C

Recommended Operating Conditions

(Note: The device is not guaranteed to function outside its operating conditions.)

Ambient Temperature	Range	40	°C to 85°C
Junction Temperature	Range	40°	C to 125°C

ELECTRICAL CHARACTERISTICS

(V_{IN} = 5V, unless otherwise specified. Typical values are at TA = 25°C.)

PARAMETER	SYMBOL	TESTCONDITIONS	MIN	TYP	MAX	UNIT
Input Standoff Voltage	VIN_MAX		7.5			V
Input Voltage Range	VIN_RANGE		2.1	N 10	6	V
Input OVP	OVP			6.1	/	V
Input UVLO	UVLO	Rising, Hysteresis=100mV	Γ	2.0	1	V
Input Supply Current	IQQ	R _{ILIM} =20K		100		μΑ
Input Shutdown Current	ISD			0.9		μΑ
Power Switch On Resistance ⁽¹⁾	DON	I _{SW} =500mA		70		mΩ
Fower Switch On Resistance	KON	I _{SW} =500mA, -40°C≤T _J ≤120°C			130	mΩ
		R _{ILIM} =6.8K		1.0		Α
Current limit Threshold	ILIM	R _{ILIM} =17K		0.4		Α
	$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$		Α			
Turn-On Time	TDELAY	3 3 1		1		ms
Turn-On Time	TSS			50		μs
Forward regulation voltage	VFW	Light Load		25		mV
Response time to Short-circuit	TSHORT			1		μs
Reverse Indication Threshold	VREV	V _{OUT} -V _{IN}		150		mV
Reverse Leakage Current	VIN_LKG	V _{OUT} =5.5V,V _{IN} =0V		0.5	2	μΑ
CNI Voltage Threehold	VIN_HI	EN Pin Voltage Rising, Enable IC	1.1			V
EN Voltage Threshold	VIN_LO	EN Pin Voltage Falling, Disable IC			0.4	V

ETA6280



PARAMETER	SYMBOL	TESTCONDITIONS	MIN	TYP	MAX	UNIT
nFAULT Output Low Voltage	VO_L0	I _{nFAULT} =1mA		70	170	mV
Output Discharge resistance	RDIS	V _{EN} =0V		300		Ω
nFAULT Output Leakage	FLT_LKG				1	μΑ
	TF_ILIM	De-assertion due to Over-current		9		ms
nFAULT Deglitch Time	TF_REV	De-assertion due to Reverse- Voltage		4.5		ms
Thermal Shutdown	TSD			160		,C
Thermal Shutdown In Current Limit	TSD_ILIM			135		°C
Thermal Shutdown Hysteresis	TSD_HYS			15		°C

Note:


(1): Guaranteed by Engineering Characterization

PIN DESCRIPTION

DIN NAME	PACKAGE			DESCRIPTION
PIN NAME	SOT23-5	SOT23-6	DFN2x2-6	
IN	5	1	6	Power input. Bypass with a 4.7µF capacitor to GND
OUT	1	6	1	Current limit Output. 10uF is recommended for output capacitor.
GND	2	2	5	Ground
ILIM	3	5	2	Current limit threshold setting pin. Connect a resistor (R _{ILIM}) from this pin to GND to set different current limit values. The current limit can be calculated by using the following formula: $I_{LIM}(A) = 6.8/R_{ILIM}(k\Omega)$
EN	4	3	4	Enable Input Pin. Drive this pin high to enable, low to disable.
nFAULT	N/A	4	3	Fault flagging pin. Connect a pull up resistor to IN, when in FAULT conditions, this pin is asserted low.
EP	N/A	N/A	EP	Thermal Pad. Used to sink the heat through the circuit board traces. Connect EP to GND on board.



FUNCTIONAL BLOCK DIAGRAM



FUNCTION DESCRIPTION


The ETA6280 is a load switch which provides full protection to systems and loads which may encounter large current conditions. ETA6280 offers a $70m\Omega$ current-limited switch which can operate over an input voltage range of 2.1-6V. The current limit can be externally programmed by a precision resistor, ranges from 75mA to 2.2A. ETA6280 also features reverse voltage blocking, UVLO, and thermal shutdown to protect IC from overheating. An nFAULT flag output provides a pull-down signal to indicate fault conditions.

CURRENT LIMITING

The current limit ensures that the current through the switch doesn't exceed a maximum value while not limiting at less than a minimum value. The current at which the parts will limit is adjustable through the selection of an external resistor connected to ILIM. The current limit can be calculated by using the following formula:

 $I_{LIM}(A)=6.8/R_{ILIM}(k\Omega)$

R _{ILIM} (kΩ)	Current limit(A)
3.3	2.06
6.8	1.00
13	0.52
15	0.45
20	0.34
30	0.23
39	0.17
51	0.13
68	0.10






ETA6280 thermal cycles if an overload condition is present long enough to activate thermal limiting in any of the above cases. The device turns off when the junction temperature exceeds 135°C (typically) while in current limit. The device remains off until the junction temperature cools 15°C (typically) and then restarts

IN-OUT FORWARD VOLTAGE REGULATION and REVERSE-VOLTAGE BLOCKING

ETA6280 is integrated an advanced technology to get a perfect reverse protection function. When Output current is high enough, the different voltage between IN and OUT terminals is determined by I_{OUT}*RON. But when output current is low, OUT is regulated to be always lower than IN a small difference, VFW. This will control VGS of Power MOSFET small enough to handle output current with its VDS not changed. And finally, there is not any reverse current at any condition since Power MOSFET will be in Cutoff when output current reaches zero.



This prevents damage to devices on the input side of the ETA6280 by preventing significant current from sinking into the input capacitance.

The nFAULT pin will not indicate the reverse condition until output voltage exceeds the input voltage by 150mV (typically) for TF_REV=4.5ms (typically).

nFAULT FLAG

The nFAULT open-drain output is asserted (active low) during an over-current, over temperature or reverse-voltage condition. The ETA6280 asserts the FAULT signal until the fault condition is removed and the device resumes normal operation. The nFAULT signal is de-asserted once device power is cycled or the enable is toggled and the device resumes normal operation. The ETA6280 is designed to eliminate false nFAULT reporting by using an internal delay "deglitch" circuit for over-current (9-ms typically) and reverse-voltage (4.5-ms typically) conditions without the need for external circuitry. This ensures that nFAULT is not accidentally asserted due to normal operation such as starting into a heavy capacitive load. The deglitching circuitry delays entering and leaving fault conditions. Over temperature conditions are not deglitched and assert the nFAULT signal immediately.



APPLICATION INFORMATION

INPUT OUTPUT CAPACITANCE

Input and output capacitance improve the performance of the device; the actual capacitance should be optimized for the particular application. For all applications, a 4.7µF or greater ceramic bypass capacitor between IN and GND is recommended a s close to the device as possible for local noise de-coupling. This precaution reduces ringing on the input due to power-supply transients. Additional input capacitance may be needed on the input to reduce voltage overshoot from exceeding the absolute maximum voltage of the device during heavy transient conditions. This is especially important during bench testing when long, inductive cables are used to connect the evaluation board to the bench power-supply. Placing a high-value electrolytic capacitor on the output pin is recommended when large transient currents are expected on the output.

POWER DISSIPATION

During normal operation as a switch, the power dissipated in the part will depend upon the level at which the current limit is set. The maximum allowed setting for the current limit is 2A and this will result in a power dissipation of,

$$P=(ILIM)^2 \times R_{ON} = 2^2 \times 0.09 = 360 \text{mW}$$


assuming the part is in high temperature, the Ron increases to 90mohm.

If the part goes into current limit the maximum power dissipation will occur when the output is shorted to 1V above ground. This is more power than the package can dissipate, but the thermal shutdown of the part will activate to protect the part from damage due to excessive heating. A short on the output will cause the part to operate in a constant current state dissipating a worst-case power of,

$$P_{(MAX)} = [VIN(max)-1] \times ILIM(max) = (6.1-1) \times 2 = 10.2W$$

This large amount of power will activate the thermal shutdown and the part will cycle in and out of thermal shutdown so long as the ON pin is active and the short is present.


PCB LAYOUT GUIDE







PACKAGE OUTLINE

Package: SOT23-6




Symbol	Dimensions In	n Millimeters	Millimeters Dimensions In Inch		
Symbol	Min	Max	Min	Max	
Α	1.050	1.250	0.041	0.049	
A1	0.000	0.100	0.000	0.004	
A2	1.050	1.150	0.041	0.045	
b	0.300	0.500	0.012	0.020	
С	0.100	0.200	0.004	0.008	
D	2.820	3.020	0.111	0.119	
E	1.500	1.700	0.059	0.067	
E1	2.650	2.950	0.104	0.116	
е	0.950	(BSC)	0.037(BSC)		
e1	1.800	2.000	0.071	0.079	
L	0.300	0.600	0.012	0.024	
θ	0°	8°	0°	8°	







Comb a l	Symbol Dimensions In M		Dimensions	In Inches
Symbol			Min	Max
Α	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
С	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
е	0.950(BSC)	0.037(BSC)
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°

Package: DFN2x2-6






TOP VIEW




Symbol	Dimensions In	n Millimeters	Dimensions In Inches			
Symbol	Min	Max	Min	Max		
Α	0.700	0.800	0.028	0.031		
A1	0.000	0.050	0.000	0.002		
A3	0.203	REF.	0.008	REF.		
D	1.900	2.100	0.075	0.083		
Е	1.900	2.100	0.075	0.083		
D1	0.900	1.100	0.035	0.043		
E1	1.500	1.700	0.059	0.067		
b	0.250	0.350	0.010	0.014		
b1	0.220	REF.	0.009 REF.			
е	0.650 BSC.		0.026 BSC.			
- 1	0.174	0.326	0.007	0.013		




TAPE AND REEL INFORMATION





- A0 Dimension designed to accommodate the component width
- B0 Dimension designed to accommodate the component length
 K0 Dimension designed to accommodate the component thickness
- W Overall width of the carrier tape
- P1 Pitch between successive cavity centers

QUADRANT ASSIGNMENTS FOR PIN 1 ORIENTATION IN TAPE



Device	Package Type	Pins	SPQ	Reel Diameter (mm)	Reel Width W1 (mm)	A0 (mm)	B0 (mm)	K0 (mm)	P1 (mm)	W (mm)	Pin1 Quadrant
ETA6280S2F	SOT23-5	5	3000	180	9.5	3.17	3.23	1.37	4	8	Q3
ETA6280S2G	SOT23-6	6	3000	180	9.5	3.17	3.23	1.37	4	8	Q3
ETA6280D2G	DFN2x2-6	6	3000	180	9.5	2.3	2.3	1.1	4	8	Q1