



TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

Approval Sheet For Product Specification

Issued Date:

Product Name: SAW Filter 40MHz SMD 7.0×5.0 mm

TST Parts No.:TB0318A

Customer Parts No.:_____

Company: _____
Division: _____
Approved by : _____
Date: _____

Checked by: _____ Andy Lee

Approval by: _____ Francis Chen

Date: _____ 2005/08/12



TAI-SAW TECHNOLOGY CO., LTD.

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,
Taoyuan, 324, Taiwan, R.O.C.

TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

SAW Filter 40 MHz

MODEL NO.: TB0318A

REV. NO.:1

A. MAXIMUM RATING:

1. Input Power Level: 10 dB_m
2. DC voltage: 5 V
3. Operating Temperature: -20°C to +85°C
4. Storage Temperature: -40°C to +85°C



RoHS Compliant
Lead free
Lead-free soldering

B. ELECTRICAL CHARACTERISTICS:


Item		Specification			
	Unit	Min.	Typ.	Max.	
Center Frequency F _c	MHz	-	40	-	
Insertion Loss IL _{min}	dB	-	9.0	12.0	
3dB Bandwidth	MHz	3.5	5.0	-	
Passband Ripple (F _c -1.75MHz~F _c +1.75MHz)	dB		1.2	2.0	
Group Delay Ripple (F _c -1.75MHz~F _c +1.75MHz)	nS		190	250	
Stopband Attenuation(reference to IL _{min} dB)					
F _c ±5MHz	dB	20	35	-	
27.5~32.5MHz	dB	31	42	-	
47.5~52.5MHz	dB	31	42	-	
0~30 MHz	dB	35	71	-	
50~70 MHz	dB	35	43	-	

Note: IL_{min} is the minimum of the pass band attenuation. The center frequency F_c is the mean value of the upper and lower frequencies at the 3dB filter attenuation level relative to the IL_{min}.


C. Frequency Characteristics :



D. MEASUREMENT CIRCUIT:




E. OUTLINE DRAWING:




Pin configuration:

- 4: RF Input or Balance Input
- 5: RF Input Ground or Balance Input Return
- 9: RF Output or Balance Output
- 10: RF Output Ground or Balance Output Return
- 1,2,3,6,7,8: Ground
- : Date Code



F. PCB FOOTPRINT:



G. PACKING:

1. REEL DIMENSION

