

**RoHS** 

COMPLIANT

HALOGEN

Available

### N-Channel 30-V (D-S) MOSFET


PRODUCT SUMMARY					
V <sub>DS</sub> (V)	<b>R<sub>DS(on)</sub> (</b> Ω <b>)</b>	I <sub>D</sub> (A)			
30	0.0030 at V <sub>GS</sub> = 10 V	25			
	0.0040 at $V_{GS}$ = 4.5 V	22			

#### **FEATURES**

- Halogen-free According to IEC 61249-2-21
  Available
- TrenchFET<sup>®</sup> Gen II
- Ultra Low On-Resistance Using High Density TrenchFET Power MOSFET Technology



- Synchronous Buck Low-Side
  - Notebook
  - Server
  - Workstation
- Synchronous Rectifier-POL



Parameter		Symbol	10 s	Steady State	Unit
Drain-Source Voltage		V <sub>DS</sub>	30		V
Gate-Source Voltage		V <sub>GS</sub>	± 20		v
	T <sub>A</sub> = 25 °C	– I <sub>D</sub>	25	17	
Continuous Drain Current (T <sub>J</sub> = 150 °C) <sup>a</sup>	T <sub>A</sub> = 70 °C		20	13	
Pulsed Drain Current (10 µs Pulse Width)		I <sub>DM</sub>	70		Α
Continuous Source Current (Diode Conduction) <sup>a</sup>		۱ <sub>S</sub>	2.9	1.3	
Avalanche Current		I <sub>AS</sub>	50		
	T <sub>A</sub> = 25 °C	PD	3.5	1.6	W
Maximum Power Dissipation <sup>a</sup>	T <sub>A</sub> = 70 °C	' D	2.2	1	
Operating Junction and Storage Temperature Range		T <sub>J</sub> , T <sub>stq</sub>	- 55 to 150		°C

THERMAL RESISTANCE RATINGS					
Parameter		Symbol	Typical	Maximum	Unit
Mauina huratian ta Anchianta	t ≤ 10 s	R <sub>thJA</sub>	29	35	
Maximum Junction-to-Ambient <sup>a</sup>	Steady State		67	80	°C/W
Maximum Junction-to-Foot (Drain)	Steady State	R <sub>thJF</sub>	13	16	

Notes:

a. Surface Mounted on 1" x 1" FR4 board.

<b>SPECIFICATIONS</b> T <sub>J</sub> = 25 °C, unless otherwise noted								
Parameter	Symbol	Test Conditions	Min.	Тур.	Max.	Unit		
Static								
Gate Threshold Voltage	V <sub>GS(th)</sub>	$V_{DS} = V_{GS}, I_D = 250 \ \mu A$			3.0	V		
Gate-Body Leakage	I <sub>GSS</sub>	$V_{DS} = 0$ V, $V_{GS} = \pm 20$ V			± 100	nA		
Zero Gate Voltage Drain Current		$V_{DS} = 30 \text{ V}, V_{GS} = 0 \text{ V}$			1	μΑ		
Zero Gale Vollage Dialit Guirent	DSS	$V_{DS}$ = 30 V, $V_{GS}$ = 0 V, $T_{J}$ = 55 °C			5			
On-State Drain Current <sup>a</sup>	On-State Drain Current <sup>a</sup> I <sub>D(on)</sub>		$V_{DS} \ge 5 \text{ V}, \text{ V}_{GS} = 10 \text{ V}$ 30			А		
	Beau	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 25 A		0.003		Ω		
Drain-Source On-State Resistance <sup>a</sup>	R <sub>DS(on)</sub>	$V_{GS} = 4.5 \text{ V}, \text{ I}_{D} = 22 \text{ A}$		0.004		52		
Forward Transconductance <sup>a</sup>	9 <sub>fs</sub>	$V_{DS} = 15 \text{ V}, \text{ I}_{D} = 25 \text{ A}$		110		S		
Diode Forward Voltage <sup>a</sup>	V <sub>SD</sub>	$I_{\rm S}$ = 2.9 A, $V_{\rm GS}$ = 0 V		0.72	1.1	V		
Dynamic <sup>b</sup>								
Input Capacitance	C <sub>iss</sub>			6500				
Output Capacitance	C <sub>oss</sub>	$V_{DS}$ = 15 V, $V_{GS}$ = 4.5 V, $I_{D}$ = 20 A		930		pF		
Reverse Transfer Capacitance	C <sub>rss</sub>			610				
Total Gate Charge	Qg			45	70			
Gate-Source Charge	Q <sub>gs</sub>	$V_{DS}$ = 15 V, $V_{GS}$ = 4.5 V, $I_{D}$ = 20 A		20		nC		
Gate-Drain Charge	Q <sub>gd</sub>			16		]		
Gate Resistance	Rg	f = 1.0 MHz		1.1		Ω		
Turn-On Delay Time	t <sub>d(on)</sub>			27	40			
Rise Time	t <sub>r</sub>	$V_{DD}$ = 15 V, $R_L$ = 15 $\Omega$		21	35	ns		
Turn-Off Delay Time	t <sub>d(off)</sub>	$\rm I_D\cong 1$ A, $\rm V_{GEN}$ = 10 V, $\rm R_g$ = 6 $\Omega$		107	160			
Fall Time	t <sub>f</sub>			43	65			
Source-Drain Reverse Recovery Time	t <sub>rr</sub>	I <sub>F</sub> = 2.9 A, dl/dt = 100 A/μs		45	70			


Notes:


a. Pulse test; pulse width  $\leq$  300 µs, duty cycle  $\leq$  2 %.

b. Guaranteed by design, not subject to production testing.

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

#### TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted






VBsemi Bsemi.com




















#### TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



# SOIC (NARROW): 8-LEAD JEDEC Part Number: MS-012






	MILLIM	IETERS	INCHES			
DIM	Min	Мах	Min	Max		
A	1.35	1.75	0.053	0.069		
A <sub>1</sub>	0.10	0.20	0.004	0.008		
В	0.35	0.51	0.014	0.020		
С	0.19	0.25	0.0075	0.010		
D	4.80	5.00	0.189	0.196		
E	3.80	4.00	0.150	0.157		
е	1.27	BSC	0.050 BSC			
н	5.80	6.20	0.228	0.244		
h	0.25	0.50	0.010	0.020		
L	0.50	0.93	0.020	0.037		
q	0°	8°	0°	8°		
S	0.44	0.64	0.018	0.026		
ECN: C-06527-Rev. I, 11-Sep-06 DWG: 5498						



**RECOMMENDED MINIMUM PADS FOR SO-8** 



Recommended Minimum Pads Dimensions in Inches/(mm)



## Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.com)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

### **Material Category Policy**

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be oHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.com)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.