3LD2565-1GP51-0US2

Data sheet



SENTRON, Switch disconnector 3LD, main switch, 3-pole, lu: 63 A, Operating power / at AC-23 A at 400 V: 22 kW, molded-plastic encapsulation for inch cable gland, 1 NC, 1 NO, rotary operating mechanism, black

Model	
product brand name	SENTRON
product designation	3LD Switch disconnector
design of the product	Main switch
display version / for switch position indicator manual operation	1 ON - 0 OFF
design of the actuating element	Short rotary knob
design of handle	rotary operating mechanism, black
type of the driving mechanism / motor drive	No
General technical data	
number of poles	3
number of poles / note	PE
type of device	fixed mounting
type of switch	Molded-plastic enclosure for inch threaded joint
size of switch disconnector	3
mechanical service life (switching cycles) / typical	100 000
electrical endurance (switching cycles)	
• at AC-23 A / at 690 V	6 000
I2t value / with closed switch / at 690 V / for combination switch + gG fuse / maximum	21 kA2.s
let-through I2t value / with closed switch / at 440 V / for combination switch + gG fuse / maximum	21 kA2.s
operating frequency / maximum	50 1/h
Voltage	
insulation voltage / rated value	690 V
surge voltage resistance / rated value	6 kV
Protection class	
protection class IP	IP65
degree of protection NEMA rating	1, 4X, 12
protection class IP / on the front	IP65
Dissipation	
power loss [W]	
 for rated value of the current / at AC / in hot operating state / per pole 	4.5 W
per conductor / typical	5 W
Current	
operational current	
at 40 °C / rated value	63 A
at 45 °C / rated value	63 A
• at 50 °C / rated value	63 A

155.00 / 1 1	00.4
at 55 °C / rated value	63 A
at AC / rated value	63 A
• at AC-23 A / at 400 V / rated value	43 A
• at AC-21 / at 690 V / rated value	63 A
 at AC-21 A / at 240 V / rated value 	63 A
at AC-21 A / at 440 V / rated value	63 A
operational current / of upstream fuse / rated value	63 A
let-through current / with closed switch	Cha
 at 440 V / for combination switch + gG fuse / maximum 	6 kA
at 690 V / for combination switch + gG fuse /	6 kA
maximum permissible	
Main circuit	
operating power	
at AC-23 A / at 240 V / rated value	11 kW
at AC-23 A / at 400 V / rated value	22 kW
at AC-23 A / at 440 V / rated value	22 kW
at AC-23 A / at 690 V / rated value	19 kW
at AC-3 / at 240 V / rated value	11 kW
at AC-3 / at 400 V / rated value	19 kW
• at AC-3 / at 690 V / rated value	15 kW
operational current / rated value	63 A
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
number of NC contacts / for auxiliary contacts	1
number of NO contacts / for auxiliary contacts	1
operating voltage / of auxiliary contacts / at AC / maximum	500 V
continuous current / of the auxiliary contact / rated value	10 A
insulation voltage / of the auxiliary switch / rated value	500 V
Suitability	
suitability for use	
main switch	Yes
 switch disconnector 	Yes
 EMERGENCY OFF switch 	No
 safety switch 	Yes
maintenance/repair switch	Yes
Appearance	
color / of the actuating element	
	black
Product details	black
	black
Product details	Yes
Product details product feature	
Product details product feature • can be locked into OFF position	Yes
Product details product feature	Yes 3
Product details product feature	Yes 3 4 mm 8 mm
Product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive	Yes 3 4 mm 8 mm
Product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger	Yes 3 4 mm 8 mm
Product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit	Yes 3 4 mm 8 mm
Product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit conditional short-circuit current / with line-side fuse	Yes 3 4 mm 8 mm
product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit conditional short-circuit current / with line-side fuse protection	Yes 3 4 mm 8 mm No No
Product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value	Yes 3 4 mm 8 mm
Product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL	Yes 3 4 mm 8 mm No No
Product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL	Yes 3 4 mm 8 mm No No
Product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 480 V / according to UL	Yes 3 4 mm 8 mm No No No
product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 600 V / according to UL	Yes 3 4 mm 8 mm No No No O The state of th
product details product feature • can be locked into OFF position number of bracket locks / maximum hasp thickness / of the bracket locks / minimum hasp thickness / of the bracket locks / maximum product extension / optional • motor drive • voltage trigger Short circuit conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value	Yes 3 4 mm 8 mm No No No 50 kA 63 A 600 V 40

to UL 508/UL 60947-4-1	475.4
continuous current / of upstream fuse / according to UL / rated value	175 A
type of fuse / according to UL	RK5
Number	
number of connectable NC contacts / for auxiliary contacts / attachable / maximum	2
number of connectable NO contacts / for auxiliary contacts / attachable / maximum	3
number of connectable CO contacts / for auxiliary contacts / attachable / maximum	0
Connections	
AWG number / as coded connectable conductor cross section / solid	
• maximum	6
• minimum	14
type of connectable conductor cross-sections / for copper conductor	
• solid	1x (2,535mm²)
 finely stranded / with core end processing 	1x (2.516 mm²)
stranded	1x (2,535mm²)
type of connectable conductor cross-sections / for auxiliary contacts	
• solid	lateral auxiliary switch 2x (0,75 2,5mm²), 1x 4mm²; front auxiliary switch 1x (0,75 2,5mm²)
• finely stranded / with core end processing	lateral auxiliary switch 2x (0,75 1,5mm²), 1x 2,5mm²; front auxiliary switch 1x 2,5mm²
• stranded	lateral auxiliary switch 2x (0,75 2,5mm²), 1x 4mm²; front auxiliary switch 1x (0,75 2,5mm²)
type of electrical connection	
 for main current circuit 	box terminal
 for auxiliary contacts 	connection terminals
Requirements	
design of the fuse link	
 for short-circuit protection of the main circuit / required 	fuse gL/gG: 63 A
 for short-circuit protection of the auxiliary switch / required 	fuse gL/gG: 10 A
Mechanical Design	
height	201 mm
width	146 mm
depth	149 mm
fastening method	Complete unit in enclosure
fastening method	
 4-hole front mounting 	No
 front mounting with central attachment 	
• Iront mounting with central attachment	Yes
rail mounting	Yes No
•	
• rail mounting	No
rail mounting net weight	No
• rail mounting net weight Environmental conditions	No
rail mounting net weight Environmental conditions ambient temperature / during operation	No 960 g
 rail mounting net weight Environmental conditions ambient temperature / during operation	No 960 g -25 °C



Confirmation







Miscellaneous

General Product Declaration of Conformity Test Certificates Marine / Shipping





Miscellaneous

Special Test Certific-<u>ate</u>



other

Environmental Confirmations

Miscellaneous

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD2565-1GP51-0US2

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3LD2565-1GP51-0US2

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD2565-1GP51-0US2

CAx-Online-Generator

http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications









