## SIEMENS

## Data sheet

## 3LD3448-1TK51



Load disconnector 3LD3, lu 63 A Main switch 3-pole Rated operating capacity at AC-23 A at 400V 22.0 kW floor mounting Basic switch with door coupling Central hole mounting 22.5mm Rotating drive black 66 x 66 mm with auxiliary switch 10E + 1S

Model	
product brand name	SENTRON
product designation	3LD Switch disconnector
design of the product	Main switch
display version / for switch position indicator manual operation	1 ON - 0 OFF
design of the actuating element	Short rotary knob
design of handle	rotary operating mechanism, black
type of the driving mechanism / motor drive	No
General technical data	
number of poles	3
number of poles / note	3
type of device	fixed mounting
type of switch	Floor mounting with door coupling
mechanical service life (switching cycles) / typical	100 000
electrical endurance (switching cycles)	
• at AC-23 A / at 690 V	6 000
I2t value / with closed switch / at 690 V / for combination switch + gG fuse / maximum	21 kA2.s
let-through I2t value / with closed switch / at 440 V / for combination switch + gG fuse / maximum	21 kA2.s
operating frequency / maximum	50 1/h
Voltage	
insulation voltage / rated value	690 V
surge voltage resistance / rated value	6 kV
Protection class	
protection class IP	IP65
degree of protection NEMA rating	1, 3R, 4X, 12
protection class IP / on the front	IP65
Dissipation	
power loss [W]	
<ul> <li>for rated value of the current / at AC / in hot operating state / per pole</li> </ul>	4.5 W
<ul> <li>per conductor / typical</li> </ul>	5 W
Current	
operational current	
• at 40 °C / rated value	63 A
• at 45 °C / rated value	63 A
• at 50 °C / rated value	63 A
• at 55 °C / rated value	63 A

	20. A
• at AC / rated value	63 A
• at AC-23 A / at 400 V / rated value	43 A
at AC-21 / at 690 V / rated value	63 A
• at AC-21 A / at 240 V / rated value	63 A
at AC-21 A / at 440 V / rated value	63 A
operational current / of upstream fuse / rated value	63 A
let-through current / with closed switch	
<ul> <li>at 440 V / for combination switch + gG fuse / maximum</li> </ul>	6 kA
<ul> <li>at 690 V / for combination switch + gG fuse /</li> </ul>	6 kA
maximum permissible	0 KA
Main circuit	
operating power	
• at AC-23 A / at 240 V / rated value	11 kW
• at AC-23 A / at 400 V / rated value	22 kW
• at AC-23 A / at 440 V / rated value	22 kW
• at AC-23 A / at 690 V / rated value	19 kW
<ul> <li>at AC-3 / at 240 V / rated value</li> </ul>	11 kW
• at AC-3 / at 400 V / rated value	19 kW
• at AC-3 / at 400 V / rated value	15 kW
operational current / rated value	63 A
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
· · · · · · · · · · · · · · · · · · ·	1
number of NC contacts / for auxiliary contacts	1
number of NO contacts / for auxiliary contacts	500 V
operating voltage / of auxiliary contacts / at AC / maximum	10 A
continuous current / of the auxiliary contact / rated value	
insulation voltage / of the auxiliary switch / rated value	500 V
Suitability	
suitability for use	N
• main switch	Yes
switch disconnector	Yes
EMERGENCY OFF switch	No
safety switch	Yes
maintenance/repair switch	Yes
Appearance	
color / of the actuating element	black
Product details	
product feature	
can be locked into OFF position	Yes
number of bracket locks / maximum	2
hasp thickness / of the bracket locks / minimum	4 mm
hasp thickness / of the bracket locks / maximum	6 mm
special product feature	Can be locked in zero position
product extension / optional	
motor drive	No
voltage trigger	No
Short circuit	
conditional short-circuit current / with line-side fuse protection	
• at 440 V / by gG fuse / rated value	10 kA
<ul> <li>at 690 V / by gG fuse / rated value</li> </ul>	6 kA
according UL	
operational current / at AC / according to UL 508/UL 60947-4-1 / rated value	63 A
operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value	600 V
active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value	25
active power [hp] / at AC / at 600 V / according to UL 508/UL 60947-4-1 / rated value	30

5 to 16 mm²) 516 mm²) 5 to 16 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
516 mm²) 5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
5 to 16 mm²) 75 2.5 mm²), 1x 4 mm²
75 2.5 mm²), 1x 4 mm²
75 1.5 mm²), 1x 2.5 mm²
75 2.5 mm²), 1x 4 mm²
erminal
erminals
JL/gG: 63 A
JL/gG: 10 A
n
n
ım
n unit fixed-mounted version
>
Declaration of Conformity

other

## Further information

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3448-1TK51 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3LD3448-1TK51 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax\_en.aspx?mlfb=3LD3448-1TK51 CAx-Online-Generator http://www.siemens.com/cax Tender specifications http://www.siemens.com/specifications

0