SIEMENS

Data sheet 3LD2430-0TK13



SENTRON, Switch disconnector 3LD, emergency switching-off switch, 3-pole, lu=250 A, operating power / at AC-23 A 400 V: 132 kW, installation in distribution boards, knob-operated mechanism, Red / yellow, handle direct at the switch

Model	
product brand name	SENTRON
product designation	3LD Switch disconnector
design of the product	EMERGENCY-STOP switch
display version / for switch position indicator manual operation	1 ON - 0 OFF
design of the actuating element	selector switch
design of handle	knob-operated mechanism, red/yellow
type of the driving mechanism / motor drive	No
General technical data	
number of poles	3
type of device	fixed mounting
type of switch	DIN-rail mounting
size of switch disconnector	5
mechanical service life (switching cycles) / typical	100 000
electrical endurance (switching cycles)	
• at AC-23 A / at 690 V	6 000
I2t value / with closed switch / at 690 V / for combination switch + gG fuse / maximum	557 kA2.s
let-through I2t value / with closed switch / at 440 V / for combination switch + gG fuse / maximum	557 kA2.s
operating frequency / maximum	50 1/h
Voltage	
insulation voltage / rated value	690 V
surge voltage resistance / rated value	8 kV
Protection class	
protection class IP	IP40
protection class IP / on the front	IP40
Dissipation	
power loss [W]	
 for rated value of the current / at AC / in hot operating state / per pole 	36 W
• per conductor / typical	36 W
Current	
operational current	
 at 40 °C / rated value 	250 A
• at 45 °C / rated value	250 A
 at 50 °C / rated value 	250 A
• at 55 °C / rated value	250 A
at AC / rated value	250 A

at AC-23 A / at 400 V / rated value	224 A
at AC-21 / at 690 V / rated value	250 A
at AC-21 A / at 240 V / rated value	250 A
at AC-21 A / at 440 V / rated value	250 A
operational current / of upstream fuse / rated value	250 A
let-through current / with closed switch	
 at 440 V / for combination switch + gG fuse / maximum 	15 kA
 at 690 V / for combination switch + gG fuse / maximum permissible 	15 kA
Main circuit	
operating power	
at AC-23 A / at 240 V / rated value	75 kW
at AC-23 A / at 400 V / rated value	132 kW
• at AC-23 A / at 440 V / rated value	132 kW
• at AC-23 A / at 690 V / rated value	55 kW
• at AC-3 / at 240 V / rated value	55 kW
at AC-3 / at 400 V / rated value at AC-3 / at 600 V / rated value at AC-3 / at 600 V / rated value	110 kW
at AC-3 / at 690 V / rated value	45 kW
operational current / rated value	250 A
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
number of NC contacts / for auxiliary contacts	0
number of NO contacts / for auxiliary contacts	0
operating voltage / of auxiliary contacts / at AC / maximum	500 V
continuous current / of the auxiliary contact / rated value	10 A
insulation voltage / of the auxiliary switch / rated value	500 V
Suitability	
suitability for use	
main switch	Yes
switch disconnector	Yes
EMERGENCY OFF switch	Yes
safety switch	Yes
maintenance/repair switch	Yes
Appearance	and a
color / of the actuating element	red
Product details	
product feature	
can be locked into OFF position	Yes
number of bracket locks / maximum	3
hasp thickness / of the bracket locks / minimum	4 mm
hasp thickness / of the bracket locks / maximum	6 mm
product extension / optional	
 motor drive 	No
 voltage trigger 	
	No
Short circuit	No
Short circuit conditional short-circuit current / with line-side fuse protection	No
conditional short-circuit current / with line-side fuse protection	50 kA
conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value	
conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL	
conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL	50 kA
conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 480 V / according to UL	50 kA 250 A
conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 600 V / according to UL	50 kA 250 A 600 V
conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value	50 kA 250 A 600 V 100
conditional short-circuit current / with line-side fuse protection • at 690 V / by gG fuse / rated value according UL operational current / at AC / according to UL 508/UL 60947-4-1 / rated value operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value active power [hp] / at AC / at 600 V / according to UL 508/UL 60947-4-1 / rated value short-time withstand current (SCCR) / at 600 V / according	50 kA 250 A 600 V 100 75

rated value		
type of fuse / according to UL	RK5	
Number		
number of connectable NC contacts / for auxiliary contacts / attachable / maximum	2	
number of connectable NO contacts / for auxiliary contacts / attachable / maximum	4	
number of connectable CO contacts / for auxiliary contacts / attachable / maximum	0	
Connections		
AWG number / as coded connectable conductor cross section / solid		
• minimum	1	
type of connectable conductor cross-sections / for copper conductor		
• solid	1x (16185mm²)	
 finely stranded / with core end processing 	1x (16150mm²)	
• stranded	1x (16185mm²)	
type of connectable conductor cross-sections / for auxiliary contacts		
• solid	2x (0.75 2.5 mm²), 1x 4 mm²	
 finely stranded / with core end processing 	2x (0.75 1.5 mm²), 1x 2.5 mm²	
stranded	2x (0.75 2.5 mm²), 1x 4 mm²	
type of electrical connection		
for main current circuit	box terminal	
 for auxiliary contacts 	connection terminals	
Requirements		
design of the fuse link		
 for short-circuit protection of the main circuit / required 	fuse gL/gG: 250 A	
 for short-circuit protection of the auxiliary switch / required 	fuse gL/gG: 10 A	
Mechanical Design		
height	169 mm	
width	112 mm	
depth	94 mm	
fastening method	Built-in unit fixed-mounted version	
fastening method		
 4-hole front mounting 	No	
 front mounting with central attachment 	No	
rail mounting	No	
net weight	2 047 g	
Environmental conditions		
ambient temperature / during operation		
• minimum	-25 °C	
maximum	55 °C	
ambient temperature / during storage / minimum	-25 °C	
General Product Approval		Declaration of Conformity





Confirmation







Declaration of	
Conformity	

Test Certificates

other

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD2430-0TK13

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3LD2430-0TK13

 $Image\ database\ (product\ images,\ 2D\ dimension\ drawings,\ 3D\ models,\ device\ circuit\ diagrams,\ ...)$

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD2430-0TK13

CAx-Online-Generator

http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications

-CI

