SIEMENS

Data sheet

3LD3430-0TL13



Load disconnector 3LD3, lu 63 A Main switch 3-pole + N Rated operating capacity at AC-23 A at 400V 22.0 kW Installation in distribution boards, Basic switch with selector knob red / yellow

Model		
product brand name	SENTRON	
product designation	3LD Switch disconnector	
design of the product	EMERGENCY-STOP switch	
display version / for switch position indicator manual operation	1 ON - 0 OFF	
design of the actuating element	selector switch	
design of handle	knob-operated mechanism, red/yellow	
type of the driving mechanism / motor drive	No	
General technical data		
number of poles	4	
number of poles / note	4	
type of device	fixed mounting	
type of switch	DIN-rail mounting	
mechanical service life (switching cycles) / typical	100 000	
electrical endurance (switching cycles)		
• at AC-23 A / at 690 V	6 000	
I2t value / with closed switch / at 690 V / for combination switch + gG fuse / maximum	21 kA2.s	
let-through I2t value / with closed switch / at 440 V / for combination switch + gG fuse / maximum	21 kA2.s	
operating frequency / maximum	50 1/h	
Voltage		
insulation voltage / rated value	690 V	
surge voltage resistance / rated value	6 kV	
Protection class		
protection class IP	IP40	
protection class IP / on the front	IP40	
Dissipation		
power loss [W]		
 for rated value of the current / at AC / in hot operating state / per pole 	4.5 W	
• per conductor / typical	5 W	
Current		
operational current		
• at 40 °C / rated value	63 A	
 at 45 °C / rated value 	63 A	
• at 50 °C / rated value	63 A	
• at 55 °C / rated value	63 A	
• at AC / rated value	63 A	

	40.4
at AC-23 A / at 400 V / rated value	43 A
at AC-21 / at 690 V / rated value	63 A
• at AC-21 A / at 240 V / rated value	63 A
at AC-21 A / at 440 V / rated value	63 A
operational current / of upstream fuse / rated value	63 A
let-through current / with closed switch	
 at 440 V / for combination switch + gG fuse / maximum 	6 kA
 at 690 V / for combination switch + gG fuse / maximum permissible 	6 kA
Main circuit	
operating power	
 at AC-23 A / at 240 V / rated value 	11 kW
 at AC-23 A / at 400 V / rated value 	22 kW
 at AC-23 A / at 440 V / rated value 	22 kW
 at AC-23 A / at 690 V / rated value 	19 kW
 at AC-3 / at 240 V / rated value 	11 kW
 at AC-3 / at 400 V / rated value 	19 kW
• at AC-3 / at 690 V / rated value	15 kW
operational current / rated value	63 A
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
number of NC contacts / for auxiliary contacts	0
number of NO contacts / for auxiliary contacts	0
operating voltage / of auxiliary contacts / at AC / maximum	500 V
continuous current / of the auxiliary contact / rated value	10 A
insulation voltage / of the auxiliary switch / rated value	500 V
Suitability	
suitability for use	
main switch	Yes
switch disconnector EMERGENCY OFF switch	Yes
	Yes
safety switch	Yes
maintenance/repair switch	Yes
Appearance	
color / of the actuating element	red
Product details	
product feature	
 can be locked into OFF position 	Yes
number of bracket locks / maximum	2
hasp thickness / of the bracket locks / minimum	4 mm
hasp thickness / of the bracket locks / maximum	6 mm
special product feature	Can be locked in zero position
product extension / optional	
motor drive	No
voltage trigger	No
Short circuit	
conditional short-circuit current / with line-side fuse protection	
• at 440 V / by gG fuse / rated value	10 kA
• at 690 V / by gG fuse / rated value	6 kA
according UL	
operational current / at AC / according to UL 508/UL 60947-4-1 / rated value	63 A
operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value	600 V
active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value	25
active power [hp] / at AC / at 600 V / according to UL 508/UL 60947-4-1 / rated value	30
	30 5 kA

to UL 508/UL 60947-4-1	
continuous current / of upstream fuse / according to UL / rated value	50 A
type of fuse / according to UL	RK5
Number	
number of connectable NC contacts / for auxiliary contacts / attachable / maximum	2
number of connectable NO contacts / for auxiliary contacts / attachable / maximum	4
number of connectable CO contacts / for auxiliary contacts / attachable / maximum	0
Connections	
AWG number / as coded connectable conductor cross section / solid	
• maximum	6
• minimum	14
type of connectable conductor cross-sections / for copper conductor	
• solid	1x (2.5 to 16 mm ²)
 finely stranded / with core end processing 	1x (2.516 mm ²)
• stranded	1x (2.5 to 16 mm ²)
type of connectable conductor cross-sections / for auxiliary contacts	
• solid	2x (0.75 2.5 mm²), 1x 4 mm²
 finely stranded / with core end processing 	2x (0.75 1.5 mm²), 1x 2.5 mm²
stranded	2x (0.75 2.5 mm²), 1x 4 mm²
type of electrical connection	
 for main current circuit 	box terminal
 for auxiliary contacts 	Box terminals
Requirements	
design of the fuse link	
 for short-circuit protection of the main circuit / required 	fuse gL/gG: 63 A
 for short-circuit protection of the auxiliary switch / required 	fuse gL/gG: 10 A
Mechanical Design	
height	60 mm
width	49 mm
depth	77 mm
fastening method	Built-in unit fixed-mounted version
fastening method	
 4-hole front mounting 	No
 front mounting with central attachment 	No
rail mounting	Yes
net weight	200 g
Environmental conditions	
ambient temperature / during operation	
• minimum	-25 °C
• maximum	55 °C
ambient temperature / during storage / minimum	-25 °C
General Product Approval	Declaration of Conformity

other

Miscellaneous

 Further information

 Information- and Downloadcenter (Catalogs, Brochures,...)

 http://www.siemens.com/lowvoltage/catalogs

 Industry Mall (Online ordering system)

 https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD3430-0TL13

 Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

 https://support.industry.siemens.com/cs/ww/en/ps/3LD3430-0TL13

 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

 http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD3430-0TL13

 CAx-Online-Generator

 http://www.siemens.com/cax

 Tender specifications

http://www.siemens.com/specifications

Ø