SIEMENS

Data sheet

3LD2517-1TL11



SENTRON, switch disconnector 3LD, main switch, 4-pole, lu: 63 A, operating power / at AC-23 A at 400 V: 22 kW, floor mounting with door coupling, defeatable knob-operated mechanism, black, 4-hole mounting of the handle

Model		
product brand name	SENTRON	
product designation	3LD Switch disconnector	
design of the product	Main switch	
display version / for switch position indicator manual operation	1 ON - 0 OFF	
design of the actuating element	selector switch	
design of handle	knob-operated mechanism, black	
type of the driving mechanism / motor drive	No	
General technical data		
number of poles	4	
type of device	fixed mounting	
type of switch	Floor mounting with door coupling	
size of switch disconnector	3	
mechanical service life (switching cycles) / typical	100 000	
electrical endurance (switching cycles)		
• at AC-23 A / at 690 V	6 000	
I2t value / with closed switch / at 690 V / for combination switch + gG fuse / maximum	21 kA2.s	
let-through I2t value / with closed switch / at 440 V / for combination switch + gG fuse / maximum	21 kA2.s	
operating frequency / maximum	50 1/h	
Voltage		
insulation voltage / rated value	690 V	
surge voltage resistance / rated value	6 kV	
Protection class		
protection class IP	IP65	
degree of protection NEMA rating	1, 3R, 4X, 12	
protection class IP / on the front	IP65	
Dissipation		
power loss [W]		
 for rated value of the current / at AC / in hot operating state / per pole 	4.5 W	
 per conductor / typical 	5 W	
Current		
operational current		
• at 40 °C / rated value	63 A	
• at 45 °C / rated value	63 A	
• at 50 °C / rated value	63 A	
• at 55 °C / rated value	63 A	

	CO A
• at AC / rated value	63 A
 at AC-23 A / at 400 V / rated value 	43 A
• at AC-21 / at 690 V / rated value	63 A 63 A
• at AC-21 A / at 240 V / rated value	
at AC-21 A / at 440 V / rated value	63 A 63 A
operational current / of upstream fuse / rated value	03 A
let-through current / with closed switch	6 kA
 at 440 V / for combination switch + gG fuse / maximum 	6 kA
 at 690 V / for combination switch + gG fuse / 	6 kA
maximum permissible	
Main circuit	
operating power	
 at AC-23 A / at 240 V / rated value 	11 kW
 at AC-23 A / at 400 V / rated value 	22 kW
 at AC-23 A / at 440 V / rated value 	22 kW
 at AC-23 A / at 690 V / rated value 	19 kW
 at AC-3 / at 240 V / rated value 	11 kW
 at AC-3 / at 400 V / rated value 	19 kW
 at AC-3 / at 690 V / rated value 	15 kW
operational current / rated value	63 A
Auxiliary circuit	
number of CO contacts / for auxiliary contacts	0
number of NC contacts / for auxiliary contacts	0
number of NO contacts / for auxiliary contacts	0
operating voltage / of auxiliary contacts / at AC / maximum	500 V
continuous current / of the auxiliary contact / rated value	10 A
insulation voltage / of the auxiliary switch / rated value	500 V
Suitability	
suitability for use	
main switch	Yes
switch disconnector	Yes
EMERGENCY OFF switch	No
safety switch	Yes
maintenance/repair switch	Yes
Appearance	
color / of the actuating element	black
Product details	
product feature	
can be locked into OFF position	Yes
number of bracket locks / maximum	3
hasp thickness / of the bracket locks / minimum	4 mm
hasp thickness / of the bracket locks / maximum	6 mm
product extension / optional	
motor drive	No
voltage trigger	No
Short circuit	
conditional short-circuit current / with line-side fuse	
protection	
 at 690 V / by gG fuse / rated value 	50 kA
according UL	
operational current / at AC / according to UL 508/UL	63 A
60947-4-1 / rated value	
operating voltage / at AC / at 50/60 Hz / according to UL 508/UL 60947-4-1 / rated value	600 V
active power [hp] / at AC / at 480 V / according to UL 508/UL 60947-4-1 / rated value	40
active power [hp] / at AC / at 600 V / according to UL 508/UL 60947-4-1 / rated value	50
short-time withstand current (SCCR) / at 600 V / according to UL 508/UL 60947-4-1	5 kA

continuous current / of upstream fuse / according to UL /	175 A
rated value	
type of fuse / according to UL	RK5
Number	
number of connectable NC contacts / for auxiliary contacts / attachable / maximum	3
number of connectable NO contacts / for auxiliary contacts / attachable / maximum	5
number of connectable CO contacts / for auxiliary contacts / attachable / maximum	0
Connections	
AWG number / as coded connectable conductor cross section / solid	
 maximum minimum 	6 14
type of connectable conductor cross-sections / for copper conductor	
• solid	1x (2,535mm²)
 finely stranded / with core end processing 	1x (2.516 mm ²)
stranded	1x (2,535mm ²)
type of connectable conductor cross-sections / for auxiliary contacts	
• solid	lateral auxiliary switch 2x (0,75 2,5mm ²), 1x 4mm ² ; front auxiliary switch 1x (0,75 2,5mm ²)
• finely stranded / with core end processing	lateral auxiliary switch 2x (0,75 1,5mm ²), 1x 2,5mm ² ; front auxiliary switch 1x 2,5mm ²
stranded	lateral auxiliary switch 2x (0,75 2,5mm ²), 1x 4mm ² ; front auxiliary switch 1x (0,75 2,5mm ²)
type of electrical connection	
 for main current circuit 	box terminal
 for auxiliary contacts 	connection terminals
Requirements	
design of the fuse link	
 for short-circuit protection of the main circuit / required 	fuse gL/gG: 63 A
 for short-circuit protection of the auxiliary switch / required 	fuse gL/gG: 10 A
Mechanical Design	
height	91 mm
width	84 mm
depth	395 mm
fastening method	Built-in unit fixed-mounted version
fastening method	
4-hole front mounting	Yes
 front mounting with central attachment 	No
rail mounting	Yes
net weight	634 g
Environmental conditions	
ambient temperature / during operation	
minimum	-25 °C
• maximum	-25 °C
ambient temperature / during storage / minimum	-25 °C
General Product Approval	
	Miscellaneous UL VDE
General Product Approval Declaration of Conformity	Test Certificates Marine / Shipping other

Subject to change without notice © Copyright Siemens

UK EAC



Special Test Certificate




Environmental Con**firmations**

other

Miscellaneous


Further information

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3LD2517-1TL11 Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3LD2517-1TL11 Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3LD2517-1TL11 **CAx-Online-Generator** http://www.siemens.com/cax **Tender specifications** http://www.siemens.com/specifications






a5.5



-CI



C