

VOLTAGE RANGE CURRENT 50 to 1000 Volts 4.0 Ampere


Features

- UL recognition, file #E313149
- Ldeal for automated placement
- · High surge current capability
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C

5

Mechanical Data

- · Package: DBS
- Molding compound meets UL 94 V-0 flammability rating, RoHS-compliant, Halogen free
- Terminals: Tin plated leads, solderable per J-STD-002 and JESD22-B102
- Polarity: As marked on body



Maximum Ratings and Electrical Characteristics

- Ratings at 25 [°]C ambient temperature unless otherwise specified
- Single Phase, half wave, 60Hz, resistive or inductive load
- For capacitive load derate current by 20%

TYPE NUMBER		SYMBO LS	DB 401S	DB 402S	DB 403S	DB 404S	DB 405S	DB 406S	DB 407S	UNITS	
Maximum Repetitive Peak Reverse Voltage		V_{RRM}	50	100	200	400	600	800	1000	Volts	
Maximum RMS Voltage		V _{RMS}	35	70	140	280	420	560	700	Volts	
Maximum DC Blocking Voltage		V_{DC}	50	100	200	400	600	800	1000	Volts	
Maximum Average Forward Rectified Current T _L =100℃		I _(AV)	4.0				Amp				
Peak Forward Surge Current 8.3mS single half sine wave superimposed on rated load (JEDEC method)		I _{FSM}	120					Amps			
Current squared time @1ms≤t<8.3ms Tj=25℃, Rating of per diode		l²t	63				A ² s				
Maximum Instantaneous Forward Voltage @ 4.0A		VF	1.1				Volts				
Maximum DC Reverse Current at Rated	T _A = 25℃		5.0 100					μΑ			
DC Blocking Voltage	T _A = 125℃	I _R									
Typical junction capacitance (NOTE 1)		Сл	30			pF					
Typical Thermal Pagistanes (Note 2)		R _{θJA}				68				°C/W	
Typical Thermal Resistance (Note 2)		Rejl	15			C/VV					
Operating Junction Temperature Range		T _J , T _{STG}			(-5	55 to +15	50)			$^{\circ}$ C	

Notes:

- 1. Measured at 1.0MHz and applied reverse voltage of 4.0 Volts.
- 2. Thermal Resistance test performed in accordance with JESD-51. Unit mounted on 15mm*12mm*1.6mm AL pad attach 195mm*110mm*10mm steel plate.
- 3. The typical data above is for reference only.





VOLTAGE RANGE


50 to 1000 Volts


CURRENT 4.0 Ampere


Ratings and Characteristic Curves (T_A=25°C unless otherwise noted)














VOLTAGE RANGE CURRENT 50 to 1000 Volts 4.0 Ampere


Package Outline Dimensions in inches (millimeters)

Outline Dimensions



Direc	n	nm	in		
Dim	min	max	min	max	
Α	6.20	6.50	.244	.256	
В	9.60	10.30	.378	.406	
С	5.00	5.20	.197	.205	
D	8.13	8.51	.320	.335	
Е	2.38	2.45	.093	.096	
F	0.98	1.13	.038	.044	
G	0.18	0.23	.007	.009	
Н	1.02	1.53	.040	.060	
I	0.05	0.20	.001	.007	
J	1.80	2.10	.070	.082	

Suggested pad layout




Dim	Min
P1	8.73
P2	5.12
Q1	2.22
Q2	1.2



VOLTAGE RANGE CURRENT 50 to 1000 Volts 4.0 Ampere


Packing Requirments

· PS black anti-static carrier tape packing



Specifications	Ao	Во	Ko	Ро	W	t1
DBS	8.64±0.10	9.85±0.10	2.60±0.10	4.00±0.1	16.0±0.10	0.30±0.02

• 13 "antistatic plastic reel




	DE) #0E T)/DE	13" Reel					
	DEVICE TYPE	Q'TY/REEL(pcs)	REEL/BOX	BOX/CARTOON	Q'TY/CARTON(pcs)		
Ī	DBS	3000	2	8	48000		



VOLTAGE RANGE CURRENT 50 to 1000 Volts 4.0 Ampere

Reflow Profile



	Reflow Condition	Pb-Free Assembly		
	Temperature Min.	+150°C		
Pre Heat	Temperature Max.	+200°C		
	Time(Min to Max)	60-180 secs.		
Average ram	p up rate(Liquidus Temp(T∟) to peak)	3°C/sec. Max.		
T _S (max) to T _L - Ramp-up Rate		3°C/sec. Max.		
Reflow	Temperature (T _L)(Liquidus)	+217°C		
	Temperature (T∟)	60-150 secs.		
Peak Temp (T _P)		+(260+0/-5)°C		
Time within 5°C of actual Peak Temp (T _P)		25 secs.		
	Ramp-down Rate	6°C/sec. Max.		
Time 25°C to peak Temp (T _P)		8 min. Max.		
	Do not exceed	+260°C		

SURFACE MOUNT GLASS PASSIVATED STANDARD RECTIFIER BRIDGE

DB401S THRU DB407S

VOLTAGE RANGE CURRENT 50 to 1000 Volts 4.0 Ampere

Disclaimer

The information presented in this document is for reference only. Chongqing changjie Electronic Technology Co., Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), Changjie or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website http:// www.czlangjie.com , or consult your nearest Langjie's sales office for further assistance.