SIEMENS

Data sheet

3SU1802-0NA00-2AB2



Enclosure for command devices 22 mm, round, enclosure material plastic, enclosure top part yellow, 2 control points plastic, B = Indicator light, red, LED 24 V AC/DC,screw terminal, label without inscription, A = EMERGENCY STOP, 40 mm, RONIS SB30, label with inscription: EMERGENCY STOP, 1 NO, 1 NC, screw terminal, floor mounting, 1xM20 each on top and bottom labels enclosed

product brand name	SIRIUS ACT	
product designation	Enclosures	
product type designation	3SU1	
equipment of commanding and signaling device	A = EMERGENCY-STOP mushroom pushbutton, 40 mm, with positive atching acc. to ISO 13850 and rotate-to-unlatch mechanism, B = ndicator light	
manufacturer's article number		
 of supplied contact module 	A1 = 3SU1400-2AA10-1CA0, A2 = 3SU1400-2AA10-1BA0	
 of supplied contact module at the command point A 1 	<u>3SU1400-2AA10-1CA0</u>	
 of supplied contact module at the command point A 2 	<u>3SU1400-2AA10-1BA0</u>	
 of supplied LED module 	B3 = 3SU1401-2BG20-1AA0	
 of supplied LED module at the command point B 	<u>3SU1401-2BB20-1AA0</u>	
 of the supplied holder 	A = 3SU1550-0AA10-0AA0, B = 3SU1550-0AA10-0AA0	
 of the supplied holder at the command point A 	<u>3SU1550-0AA10-0AA0</u>	
 of the supplied holder at the command point B 	<u>3SU1550-0AA10-0AA0</u>	
 of the supplied actuator 	A = 3SU1050-1HF20-0AA0	
 of the supplied actuator at the command point A 	<u>3SU1050-1HF20-0AA0</u>	
 of the supplied actuator at the command point B 	<u>3SU1051-6AA20-0AA0</u>	
 of supplied repeater 	B = 3SU1051-6AA20-0AA0	
 of supplied empty enclosure 	<u>3SU1802-0AA00-0AB2</u>	
 of supplied support terminal 	A4 = 3SU1400-4DA43-1AA0	
 of supplied support terminal at the command point A 	<u>3SU1400-4DA43-1AA0</u>	
 of supplied accessory 	A = 3SU1900-0AF16-0AA0, B = 3SU1900-0AF16-0AA0	
 of the supplied accessories at the command point A 	<u>3SU1900-0AF16-0AA0</u>	
 of the supplied accessories at the command point B 	<u>3SU1900-0AF16-0AA0</u>	
inclosure		
design of the housing	with recess for label	
shape of the enclosure front	rectangular	
material of the enclosure	plastic	
number of command points	2	
product component		
EMERGENCY STOP device	Yes	
protective collar	No	
color of the enclosure top part	yellow	
delivery state		
● as a kit	No	
pre-wired on strip terminal	No	
fastening method of the enclosure	Vertical	

Actuator	
design of the actuating element	Indicator light / EMERGENCY STOP mushroom pushbutton
suitability for use EMERGENCY OFF switch	Yes
product feature lockout	No
product extension optional light source	Yes
color of the actuating element	A = red / B = red
material of the actuating element	plastic
shape of the actuating element	round
number of contact modules	2
type of unlocking device	A = key-operated release / B = without
Front ring	
product component front ring	Yes
design of the front ring	Standard
material of the front ring	Metal, high gloss
color of the front ring	silver
Holder	
material of the holder	Plastic
Display	
number of LED modules	1
General technical data	
product function	
positive opening	Yes
EMERGENCY OFF function	Yes
EMERGENCY STOP function	Yes
protection class IP	IP66, IP67, IP69(IP69K)
degree of protection NEMA rating	1, 2, 3, 3R, 4, 4X, 12K, 13
shock resistance	
according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
according to IEC 60068-2-6	10 500 Hz: 5g
reference code according to IEC 81346-2	S
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A
continuous current of the DIAZED fuse link gG	10 A
Substance Prohibitance (Date)	10/01/2014
operating voltage	
• at AC	
— at 50 Hz rated value	24 24 V
— at 60 Hz rated value	24 24 V
• at DC rated value	24 24 V
Communication/ Protocol	
design of the interface for communication	without
Auxiliary circuit	
design of the contact of auxiliary contacts	Silver alloy
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
Connections/ Terminals	
type of electrical connection of modules and accessories	Screw-type terminal
type of electrical connection on enclosure	Cable routing above and below, both 1 x M20
tightening torque of the screws in the bracket	$1 \dots 1.2 \text{ N·m}$
tightening torque of fixing screws in the enclosure	1.5 1.7 N·m
cover	
tightening torque with screw-type terminals	0.8 0.9 N·m
Lamp	
light intensity	450 1 120 mcd
Ambient conditions	
ambient temperature	
during operation	-25 +70 °C
during storage	-40 +80 °C

environmental category during operation according to IEC 60721		3M6, 3S2, 3B2, 3K6 (with recordensation in operation p			
Installation/ mounting/ dimensions					
fastening method of modules and accessories		Floor mounting			
height		114 mm			
width		85 mm			
depth		109 mm			
shape of the installation opening		round	round		
Accessories					
number of labels		2			
marking of the name plate for command devices		A = "Emergency Stop" / B =	 without inscription 		
color of the label		A = black / B = black			
number of inscription plates		0			
Certificates/ approvals					
General Product Approval					
(Ch) (m)	<u>Confirmatio</u>	<u> </u>		гпг	
			VDE	CUL	
Declaration of Conformity	Test Certifica	utes	Marine / Shipping	CUL	
Declaration of Conformity CCC CCC CCC	Test Certifica Type Test Cer ates/Test Rep	rtific- Special Test Certific-	Marine / Shipping		
CE	Type Test Cer	rtific- Special Test Certific-	Marine / Shipping	ETTL Llovds Register Lis	
C E EG-Konf.	Type Test Cer	r <u>tific- Special Test Certific-</u> port <u>ate</u>	Marine / Shipping	Lovds Register Us	

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1802-0NA00-2AB2


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1802-0NA00-2AB2


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SU1802-0NA00-2AB2

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1802-0NA00-2AB2&lang=en







last modified:

1/26/2022 🖸